

#### **General Description**

The MAX8516/MAX8517/MAX8518 low-dropout linear regulators operate from input voltages as low as 1.425V and are able to deliver up to 1A of continuous output current with a maximum dropout voltage of only 200mV. The output voltage can be set from 0.5V to (V<sub>IN</sub> - 0.2V) and is 1.4% accurate over load and line variations, from 0°C to +85°C.

These regulators use small,  $1\mu F$  ceramic input capacitors and  $4.7\mu F$  ceramic output capacitors to deliver 1A output current. High bandwidth provides excellent transient response and limits the output voltage deviation to 45mV for a 20mA to 1A load step, with only a  $4.7\mu F$  ceramic output capacitor, and the voltage deviations can be reduced further by increasing the output capacitor.

Designed with an internal p-channel MOSFET pass transistor, the MAX8516/MAX8517/MAX8518 feature low 340µA (typ) supply current during dropout conditions. Soft-start reduces inrush current. Other features include a logic-controlled shutdown mode, short-circuit protection, and thermal-overload protection.

The MAX8517 features a power-OK (POK) output that transitions high when the regulator output is within ±10% of its nominal output voltage. The MAX8518 features a 150ms power-on reset output.

The parts are packaged in a 10-pin  $\mu$ MAX<sup>®</sup> package that includes an exposed pad for optimal power dispation.

#### **Applications**

- Servers
- Storage
- Networking
- Base Stations
- Optical Modules
- Post Regulators
- Notebooks
- PDAs
- ATE

µMAX is a registered trademark of Maxim Integrated Products, Inc.

## **Pin Configurations**

#### TOP VIEW EN 10 N.C. ΕN 10 N.C. ΕN 10 N.C. 9 9 OUT IN 2 OUT IN 2 9 OUT IN 2 MAX8516 MAX8517 MAX8518 8 OUT 3 8 OUT 3 3 8 OUT IN IN IN 7 7 FB N.C. 4 7 FB N.C. 4 FΒ POK 4 N.C. 5 GND N.C. 5 6 GND POR 5 6 GND μΜΑΧ μΜΑΧ μΜΑΧ

## 1.425V to 3.6V Input, 1A, 0.2V Dropout LDO Regulators

#### **Features**


- 1.425V to 3.6V Input Voltage Range
- Guaranteed 200mV Dropout at 1A Output Current
- ±1.4% Output Accuracy Over Load, Line, and Temperature (0°C to +85°C), ±0.6% Initial Accuracy
- Compatible with Ceramic Capacitors
- Fast Transient Response
- 320µA Operating Supply Current
- <25µA Shutdown Supply Current
- Short-Circuit Protection
- Thermal-Overload Protection
- Soft-Start Limits Inrush Current

#### **Ordering Information**

PART	TEMP RANGE	PIN-PACKAGE
MAX8516EUB	-40°C to +85°C	10 μMAX
MAX8517EUB	-40°C to +85°C	10 μMAX
MAX8517EUB/V+	-40°C to +85°C	10 μMAX
MAX8518EUB	-40°C to +85°C	10 μMAX

N Denotes an automotive qualified part.

### **Typical Operating Circuit**





<sup>+</sup>Denotes lead(Pb)-free/RoHS-compliant package.

# 1.425V to 3.6V Input, 1A, 0.2V Dropout LDO Regulators

## **Absolute Maximum Ratings**

IN, EN, POK (MAX8517), POR (MAX8518),	Operating Temperature Range	40°C to +85°C
FB to GND0.3V to +4.0V	Junction Temperature	+150°C
OUT to GND0.3V to (IN + 0.3V)	Storage Temperature Range	65°C to +150°C
Output Short-Circuit DurationContinuous	Lead Temperature (soldering, 10s)	+300°C
Continuous Power Dissipation	Soldering Temperature (soldering, 10s)	+240°C
$(T_A = +70^{\circ}C, EP \text{ soldered to PC board ground})$		
10-Pin μMAX (derate 10.3mW/°C above +70°C)824mW		

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

#### **Electrical Characteristics**

(Circuit of Figure 1.  $V_{IN}$  = +1.8V,  $V_{OUT}$  = +1.5V, EN = IN,  $I_{OUT}$  = 1mA,  $T_A$  = -40°C to +85°C, unless otherwise noted.) (Note 1)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS	
IN					-	
Input Voltage Range		1.425		3.600	V	
Input Undervoltage Lockout	V <sub>IN</sub> rising, 70mV hysteresis		1.32	1.35	1.38	V
OUT						
Output Voltage Range			0.5		3.4	V
Load Regulation	I <sub>OUT</sub> = 1mA to 1A			0.1		%/A
Line Regulation	V <sub>IN</sub> = 1.425V to 3.6V, V <sub>OUT</sub> = 1.225V	′, I <sub>OUT</sub> = 1mA	-0.15	0	+0.15	%/V
Dropout Voltage (V <sub>IN</sub> - V <sub>OUT</sub> )	V <sub>IN</sub> = 1.425V, I <sub>OUT</sub> = 1A, V <sub>FB</sub> = 480n	nV		100	200	mV
Current Limit	V <sub>IN</sub> = 3.6V, V <sub>OUT</sub> = 3V, V <sub>FB</sub> = 480mV	1	1.6	2	2.4	Α
Output Shutdown Leakage	V <sub>IN</sub> = 3.6V, V <sub>OUT</sub> = 0, V <sub>EN</sub> = 0			0.25	25	μΑ
FB	•				-	
	I <sub>OUT</sub> = 10mA, T <sub>A</sub> = +85°C	497	500	503		
FB Threshold Accuracy	$V_{OUT}$ = 1.225V to 3V, $V_{IN}$ = $V_{OUT}$ + 0.2V to 3.6V, $I_{OUT}$ = 1mA to 1A				507	mV
FB Input Bias Current	V <sub>FB</sub> = 0.5V, V <sub>IN</sub> = 3.6V		0.001	1	μΑ	
GND	•				-	
CND Complet Compant	V <sub>IN</sub> = 3.6V, V <sub>OUT</sub> = 3V, I <sub>OUT</sub> = 100m.		320			
GND Supply Current	Dropout, V <sub>IN</sub> = 3.6V, V <sub>FB</sub> = 480mV		340	600	μA	
GND Shutdown Current	V <sub>IN</sub> = 3.6V, EN = GND		0.25	25	μΑ	
POK (MAX8517 ONLY)						
POK Threshold	V <sub>FB</sub> moving out of regulation,	FB high	540	550	560	mV
	$V_{HYS} = 10$ mV, IN = 1.425V to 3.6V	FB low	440	450	460	IIIV
POK Output Voltage Low	V <sub>FB</sub> = 0.4V or 0.6V, I <sub>POK</sub> = 1mA		25	200	mV	
POK Output Current High	V <sub>POK</sub> = 3.6V		0.001	1	μΑ	
POK Fault Delay Time	From FB to POK	25	50	100	μs	

www.maximintegrated.com Maxim Integrated | 2

#### **Electrical Characteristics (continued)**

(Circuit of Figure 1.  $V_{IN}$  = +1.8V,  $V_{OUT}$  = +1.5V, EN = IN,  $I_{OUT}$  = 1mA,  $T_A$  = -40°C to +85°C, unless otherwise noted.) (Note 1)


PARAMETER	CONDITIONS			TYP	MAX	UNITS		
POR (MAX8518 ONLY)			,					
POR Reset Threshold	V <sub>FB</sub> falling, V <sub>HYS</sub> = 10mV, V <sub>IN</sub>	<sub>I</sub> = 1.425V to 3.6V	440	450	460	mV		
POR Output Voltage Low	V <sub>FB</sub> = 0.4V or 0.6V, I <sub>POR</sub> = 1n	nA		25	200	mV		
POR Output Current High	V <sub>POR</sub> = 3.6V			0.001	1	μA		
POR Rising Delay Time	From FB to POR					ms		
EN	EN							
Enable Input Threehold	V <sub>IN</sub> = 1.425V to 3.6V	EN rising			1.2	V		
Enable Input Threshold		EN falling	0.4					
Enable Input Bias Current	V <sub>EN</sub> = 0 or 3.6V				+1	μA		
THERMAL SHUTDOWN			·					
The area of Chartelesson There are also	Outrot on one#	T <sub>J</sub> rising		+165 +150		°C		
Thermal-Shutdown Threshold	Output on or off	T <sub>J</sub> falling						
OUTPUT TRANSIENT		·						
Load Transient	I <sub>OUT</sub> = 20mA to 1A to 20mA, t <sub>RISE</sub> = t <sub>FALL</sub> = 1µs			3		%		
Line Transient	$\delta V_{IN} = 0.5V$ , $t_{RISE} = t_{FALL} = 5\mu s$			3		%		

**Note 1:** Specifications to  $T_A = -40^{\circ}C$  are guaranteed by design, not production tested.

**Note 2:** Measurements at high current are pulse tested, such that the junction temperature is ambient temperature. Minimum supply voltage for output accuracy must be at least 1.425V.


### **Typical Operating Characteristics**


(Circuit of Figure 1,  $V_{IN}$  = +1.8V,  $V_{OUT}$  = +1.5V,  $I_{OUT}$  = 1A,  $C_{OUT}$  = 4.7 $\mu$ F,  $C_{IN}$  = 1 $\mu$ F,  $T_A$  = +25°C.)





## **Typical Operating Characteristics (continued)**


(Circuit of Figure 1,  $V_{IN}$  = +1.8V,  $V_{OUT}$  = +1.5V,  $I_{OUT}$  = 1A,  $C_{OUT}$  = 4.7 $\mu$ F,  $C_{IN}$  = 1 $\mu$ F,  $T_A$  = +25 $^{\circ}$ C.)


















## **Typical Operating Characteristics (continued)**


(Circuit of Figure 1,  $V_{IN}$  = +1.8V,  $V_{OUT}$  = +1.5V,  $I_{OUT}$  = 1A,  $C_{OUT}$  = 4.7 $\mu$ F,  $C_{IN}$  = 1 $\mu$ F,  $T_A$  = +25°C.)












## **Pin Description**

	PIN		NAME	DESCRIPTION	
MAX8516	MAX8517	MAX8518	INAIVIE	DESCRIPTION	
1	1	1	EN	Enable Input. Set low to place the device in low-current shutdown mode. Set high for normal operation.	
2, 3	2, 3	2, 3	IN	Regulator Input. $V_{\mbox{\scriptsize IN}}$ can range from +1.425V to +3.6V. Bypass with a 1µF or higher ceramic capacitor to GND.	
4, 5, 10	5, 10	4, 10	N.C.	No Connection. Pin 10 is internally pulled down to GND with a $10k\Omega$ resistor. Leave floating.	
6	6	6	GND	Ground	
7	7	7	FB	Feedback Pin. Connect to output through a voltage-divider to set the output.	
8, 9	8, 9	8, 9	OUT	Regulator Output. Bypass with a $4.7\mu F$ ceramic capacitor to GND (a smaller capacitor can be used if maximum load is less than 1A, i.e., $C_{OUT} = I_{OUT}$ (max) x ( $1\mu F/200mA$ ).	
_	4	_	POK	Power-OK Output (MAX8517 Only). Open-drain output. Connect to a positive supply with a pullup resistor. If not used, leave pin unconnected. See the <i>Detailed Description</i> .	
_	_	5	POR	Power-On Reset Output. Open-drain output. Connect to a positive supply with a pullup resistor. If not used, leave pin unconnected (see the <i>Detailed Description</i> for more details).	
	EP		GND	Exposed Pad on the Underside of the Package. Solder to the ground plane for proper heat dissipation.	

## **Functional Diagram**



www.maximintegrated.com Maxim Integrated | 6

#### **Detailed Description**

The MAX8516/MAX8517/MAX8518 are low-input, lowdropout, PMOS regulators capable of delivering up to 1A of output current with as little as 200mV of headroom from input to output. The PMOS output stage can be driven from input voltages down to +1.425V without sacrificing stability or transient performance. Since these regulators have a PMOS output device, supply current is not a significant function of load or input headroom.

#### **Internal P-Channel Pass Transistor**

The MAX8516/MAX8517/MAX8518 feature a  $100m\Omega$ (typ) p-channel MOSFET pass transistor. Unlike similar designs using PNP pass transistors, p-channel MOSFETs require no base drive, which reduces quiescent current. PNP-based regulators also waste considerable current in dropout when the pass transistor saturates and use high base-drive currents under large loads. The MAX8516/ MAX8517/MAX8518 do not suffer from these problems and consume only 340µA (typ) of guiescent current under heavy loads, as well as in dropout.

#### Short-Circuit/Thermal Fault Protection

The MAX8516/MAX8517/MAX8518 are fully protected from a short circuit at the output through current-limiting and thermal-overload circuitry. In the fault condition when the output is shorted to ground, the output current is limited to 2A. Under these conditions, the part quickly heats up. When the junction temperature reaches +165°C, the thermal-overload circuitry turns off the output, allowing the part to cool down. When the junction temperature cools to +150°C, the output turns back on and tries to reestablish regulation. Current limiting and thermal protection continue until the fault is removed. For continuous operation, do not exceed the absolute maximum junction-temperature rating of  $T_1 = +150$ °C.




Figure 1. Typical Application Circuit

#### **Output Voltage Selection**

The MAX8516/MAX8517/MAX8518 feature an adjustable output voltage from 0.5V to 3.4V, using two external resistors connected as a voltage-divider to FB as shown in Figure 1. The output voltage is set by the following equation:

$$V_{OUT} = V_{FB} \left( 1 + \frac{R1}{R2} \right)$$

where typically  $V_{FB} = 0.5V$ . Choose  $R2 \le 5k\Omega$  to optimize quiescent current, accuracy, and high-frequency powersupply rejection. To simplify resistor selection:

$$R1 = R2 \left( \frac{V_{OUT}}{V_{FB}} - 1 \right)$$

#### Soft-Start

Inherent soft-start limits inrush current. Peak inrush current is dependent on the value of COUT and can be calculated as follows:

$$I_{INRUSH} = I_{LOAD} + \left(\frac{C_{OUT}(\mu F)}{66}\right)$$

#### **Shutdown Mode**

The MAX8516/MAX8517/MAX8518 include an enable input. To shut down the device, pull EN to GND. For normal operation, connect the EN to IN. During shutdown, an internal  $10k\Omega$  resistor pulls down the output.

#### Power-OK (MAX8517 Only)

The MAX8517 features a power-OK (POK) output to indicate the status of the output. POK remains high when the regulator output is within ±10% of its nominal output voltage. If the output voltage falls or rises outside this range, POK transitions low. This open-drain output requires an external pullup resistor to IN. An internal delay circuit prevents POK from switching for 50µs (typ) after the trip threshold is initially reached. If the part is in shutdown mode, POK is low.

#### Power-On Reset (MAX8518 Only)

The MAX8518 features a power-on reset (POR) output that transitions high 140ms (typ) after the output has risen above 90% of its final value. This open-drain output requires an external pullup resistor to IN. If the part is in shutdown mode, falls below 90% of the nominal output voltage, or experiences a short-circuit or thermal fault, POR immediately transitions low.

## 1.425V to 3.6V Input, 1A, 0.2V Dropout LDO Regulators

#### **Operating Region and Power Dissipation**

The maximum power dissipation depends on the thermal resistance of the IC package and circuit board, the temperature difference between the die junction and ambient air, and the rate of airflow. The power dissipated in the device is  $P = I_{OUT} \times (V_{IN} - V_{OUT})$ .

The package features an exposed thermal pad on its underside. This pad lowers the thermal resistance of the package by providing a direct heat conduction path from the die to the PCB.

Additionally, the ground pins (GND) perform the dual function of providing an electrical connection to system ground and channeling heat away. Connect the exposed backside pad and GND to the system ground using a large pad or ground plane, or multiple vias to the ground plane layer.

#### **Applications Information**

## Capacitor Selection and Regulator Stability

Capacitors are required at the MAX8516/MAX8517/ MAX8518 inputs and outputs for stable operation over the full temperature range and with load currents up to 1A. Connect a 1µF capacitor between IN and ground and a 4.7µF capacitor with low equivalent series resistance (ESR) between OUT and ground for 1A output current. The input capacitor (ClN) lowers the source impedance of the input supply. If input-supply source impedance is high, place a larger input capacitor close to IN to prevent  $V_{\text{IN}}$  sagging due to load transients. Smaller output capacitors can be used for output currents less than 1A. Calculate  $C_{\text{OUT}}$  as follows:

 $C_{OUT} = I_{OUT(MAX)} \times (1\mu F / 200mA)$ 

#### Noise, PSRR, and Transient Response

The MAX8516/MAX8517/MAX8518 are designed to operate with low dropout voltages and low quiescent currents while still maintaining good noise, transient response, and AC rejection (see the Typical Operating Characteristics for a plot of Power-Supply Rejection Ratio (PSRR) vs. Frequency). When operating from noisy sources. improved supply-noise rejection and transient response can be achieved by increasing the values of the input and output bypass capacitors and through passive filtering techniques. The MAX8516/MAX8517/MAX8518 loadtransient response graphs (see the Typical Operating Characteristics) show two components of the output response: a DC shift from the output impedance due to the load current change, and the transient response. A typical transient overshoot for a step change in the load current from 20mA to 1A is 45mV. Use larger output ceramic capacitors greater than 4.7µF up to 50µF to attenuate the overshoot.

#### **Chip Information**

TRANSISTOR COUNT: 2849

PROCESS: BICMOS

# 1.425V to 3.6V Input, 1A, 0.2V Dropout LDO Regulators

### **Chip Information**

**TRANSISTOR COUNT: 2849** 

PROCESS: BiCMOS

## **Package Information**

For the latest package outline information and land patterns (footprints), go to <a href="www.maximintegrated.com/packages">www.maximintegrated.com/packages</a>. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE TYPE	PACKAGE CODE	DOCUMENT NO.		
10 μMAX	U10E+3	21-0109		

www.maximintegrated.com Maxim Integrated | 9

## 1.425V to 3.6V Input, 1A, 0.2V Dropout LDO Regulators

## **Revision History**

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	2/04	Initial release	_
1	4/04	Removed future product asterisks for MAX8517/MAX8518. Updated Electrical Characteristics and Pin Description.	1–3, 6
2	9/09	Added MAX8517 automotive package to Ordering Information.	1
3	4/16	Added lead-free designation	1, 9

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at www.maximintegrated.com.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.