


DS2105 SCSI Terminator


FEATURES

- Fully compliant with SCSI-1, Fast SCSI and Ultra SCSI
- Functionally compatible to the DS21S07A, targeted for high volume applications
- Provides active termination for nine signal lines
- Laser-trimmed 110 ohm termination resistors have 5% tolerance
- Low dropout voltage
- Power-down mode isolates termination resistors from the bus
- Fully supports actively negated SCSI signals
- Onboard thermal shutdown circuitry
- 16-pin plastic SOIC (DS2105)

PIN ASSIGNMENT



DS2105Z 16-PIN SOIC (150 MIL)



DS2105S 16-PIN SOIC (300 MIL)

DESCRIPTION

Fast SCSI and Ultra SCSI require the use of active terminations at both ends of every cable segment in a SCSI system with single—ended drivers and receivers. The DS2105 SCSI Terminator, which is fully compliant with these standards, enables the designer to gain the benefits of active termination: greater immunity to voltage drops on the TERMPWR (TERMination PoWeR) line, enhanced high–level noise immunity, intrinsic TERMPWR decoupling, and very low quiescent current


consumption. The DS2105, which integrates a regulator and nine precise switched 110 ohm termination resistors into a monolithic IC, is a functionally compatible version of the DS21S07A. With relaxed output current and termination tolerances, the DS2105 is intended for high volume applications which require active termination but not the high performance of the DS21S07A. The DS2105 is offered in both 300 mil and 150 mil SOIC packages.

FUNCTIONAL DESCRIPTION


The DS2105 consists of a bandgap reference, buffer amplifier, and nine termination resistors (Figure 1). The bandgap reference circuit produces a precise 2.55V level which is fed to a buffer amplifier. The buffer produces a 2.85V level and is capable of sourcing at least 24 mA into each of the termination resistors when the signal line is low (active). When the driver for a given signal line turns off, the terminator will pull the signal line to 2.85V (quiescent state). To handle actively negated SCSI signals, the buffer can sink 200 mA, and V_{RFF} will move less than 60 mV. When all lines settle in the quiescent state, the regulator will consume about 5 mA. When the DS2105 is put into power-down mode by bringing PD low, the power-down circuitry will turn off the transistors on each signal line. This will isolate the DS2105 from the signal lines and effectively remove it from the circuit. The power–down pin (\overline{PD}) has an internal 50K Ω pull–up resistor. To place the DS2105 into an active state, the \overline{PD} pin should be left open circuited.

To ensure proper operation, both the TERMPWR1 and TERMPWR2 pins must be connected to the SCSI bus TERMPWR line and both the VREF1 and VREF2 pins must be tied together externally. Each DS2105 requires a 4.7 μF capacitor connected between the VREF pins and ground. Figure 2 details a typical SCSI bus configuration. In an 8–bit wide SCSI bus arrangement ("A" Cable), two DS2105's would be needed at each end of the SCSI cable in order to terminate the 18 active signal lines. In a 16–bit wide SCSI bus arrangement ("P" Cable), three DS2105's would be needed at each end of the SCSI cable in order to terminate the 27 active signal lines.

DS2105 BLOCK DIAGRAM Figure 1



TYPICAL SCSI BUS CONFIGURATION Figure 2



NOTES:

- 1. C1 = 4.7 μ F tantalum C2 = 2.2 μ F tantalum or 4.7 μ F aluminum
- 2. If the DS2105 is to be embedded into a peripheral that will act as a target on a SCSI bus, it is recommended that TERMPWR be derived from the SCSI cable, not generated locally. In this configuration, if a power failure occurs in the peripheral, it will not affect the bus.
- 3. A high frequency bypass capacitor (0.1 μ F recommended) can be added in parallel to C1 for applications using fast rise/fall time drivers.

PIN DESCRIPTION Table 1

DS2105S PIN	DS2105Z PIN	SYMBOL	DESCRIPTION	
1	1	TERMPWR1	Termination Power 1. Should be connected to the SCSI TERMPWR line. Must be decoupled with either a 2.2 μ F or 4.7 μ F. See Figure 2.	
2	2	R1	Signal Termination 1. 110 ohm termination.	
3	3	R2	Signal Termination 2. 110 ohm termination.	
4	4	R3	Signal Termination 3. 110 ohm termination.	
5	5	R4	Signal Termination 4. 110 ohm termination.	
6	6	R5	Signal Termination 5. 110 ohm termination.	
7	7	VREF1	Reference Voltage 1. Must be externally connected directly to the VREF2 pin. Must be decoupled with a 4.7 μ F capacitor as shown in Figure 2.	
8	8	GND	Ground. Signal ground; 0.0V.	
9	9	TERMPWR2	Termination Power 2. Should be connected to the SCSI TERMPWR line. Must be decoupled with either a 2.2 μ F or 4.7 μ F. See Figure 2.	
10	11	R6	Signal Termination 6. 110 ohm termination.	
11	12	R7	Signal Termination 7. 110 ohm termination.	
12	13	R8	Signal Termination 8. 110 ohm termination.	
13	14	R9	Signal Termination 9. 110 ohm termination.	
15	15	VREF2	Reference Voltage 2. Must be externally connected directly to the VREF1 pin. Must be decoupled with a 4.7 μ F capacitor as shown in Figure 2.	
16	16	PD	Power Down. When tied low, the DS2105 enters a power–down mode. Contains an internal 50K pull–up. Strap low to deactivate the DS2105, leave open circuited to activate the DS2105.	
14	10	NC	No Connect. Do not connect any signal to this pin.	

ABSOLUTE MAXIMUM RATINGS* Voltage on Any Pin Relative to Ground -1.0V to +7.0V Operating Temperature 0°C to 70°C Storage Temperature -55°C to +125°C Soldering Temperature 260°C for 10 seconds

RECOMMENDED OPERATING CONDITIONS

(0°C to 70°C)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	NOTES
TERMPWR Voltage	V_{TP}	4.00		5.25	V	
PD Active	V _{PDA}	-0.3		+0.8	V	
PD Inactive	V _{PDI}	2.0		V _{TP} +0.3	V	

DC CHARACTERISTICS

(0°C to 70°C)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	NOTES
TERMPWR Current	I _{TP}			250	mA	1, 3
	I _{TP}		5	8	mA	1, 4
Power Down Current	I _{PD}		500		μΑ	1, 2, 5
Termination Resistance	R _{TERM}	110		118	ohm	1, 2
Die Thermal Shutdown	T _{SD}		150		°C	1
Power Down Termination Capacitance	C _{PD}		3.0	5.0	pF	1, 2, 5, 6
Input Leakage High	I _{IH}	-1.0			μΑ	1, 8
Input Leakage Low	I _{IL}			1.0	μΑ	1, 7

REGULATOR CHARACTERISTICS

(0°C to 70°C)

					١,	
PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	NOTES
Output Voltage	V _{REF}	2.7	2.85	3.0	V	1, 2
Drop Out Voltage	V_{DROP}		0.75	1.0	V	3, 6
Output Current	l _{OUT}			24.0	mA	9
Line Regulation	LI _{REG}		1.0	2.0	%	1, 4
Load Regulation	LO _{REG}		1.3	3.0	%	1, 2
Current Limit	I _{LIM}		350		mA	1
Sink Current	I _{SINK}	200			mA	1


NOTES:


- 1. 4.00V < TERMPWR < 5.25V.
- 2. 0.0V < signal lines < 3.0V.
- 3. All signal lines = 0.0V.
- 4. All signal lines open.
- 5. $\overline{PD} = 0.0V$.

^{*} This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operation sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.

- 6. Guaranteed by design; not production tested.
- 7. R_1 through R_9 only.
- 8. R_1 through R_9 and \overline{PD} .
- 9. V_{SIGNAL}=0.2V.


DS2105Z SCSI TERMINATOR 16-PIN SOIC (150 MIL)





PKG	16-PIN		
DIM	MIN	MAX	
A IN.	0.053	0.069	
MM	1.35	1.75	
A1 IN.	0.004	0.010	
MM	0.10	0.25	
A2 IN.	0.048	0.062	
MM	1.24	1.57	
b IN.	0.012	0.020	
MM	0.30	0.50	
C IN	0.007	0.011	
MM	0.17	0.28	
D IN.	0.386	0.393	
MM	9.80	9.98	
e IN.	0.050 BSC		
MM	1.27 BSC		
E1 IN.	0.150	0.158	
MM	3.81	4.01	
H IN.	0.230	0.244	
MM	5.84	6.20	
L IN.	0.016	0.050	
MM	0.40	0.89	
Θ	0°	8°	

DS2105S SCSI TERMINATOR 16-PIN SOIC (300 MIL)



The chamfer on the body is optional. If it is not present, a terminal 1 identifier must be positioned so that 1/2 or more of its area is contained in the hatched zone.

PKG	16-PIN			
DIM	MIN	MAX		
A IN.	0.094	0.105		
MM	2.38	2.68		
A1 IN.	0.004	0.012		
MM	0.102	0.30		
A2 IN.	0.089	0.095		
MM	2.26	2.41		
b IN.	0.013	0.020		
MM	0.33	0.51		
C IN	0.009	0.013		
MM	0.229	0.33		
D IN.	0.398	0.412		
MM	10.11	10.46		
e IN.	0.050 BSC			
MM	1.27 BSC			
E1 IN.	0.290	0.300		
MM	7.37	7.62		
H IN	0.398	0.416		
MM	10.11	10.57		
L IN	0.016	0.040		
MM	0.40	1.02		
Θ	0°	8°		