General Description

Applications

The MAX4901–MAX4905 switches feature negative signal capability that allows signals below ground to pass through without distortion. The MAX4901/MAX4902 are a dual SPST (single-pole/single-throw) and the MAX4903/MAX4904/MAX4905 are a single SPDT (single-pole/double-throw) configuration. These analog switches operate from a single +1.8V to +5.5V supply and have low 0.6 Ω on-resistance, making them ideal for switching audio signals.

The MAX4905 includes a comparator that can be used for headphone detection or mute/send key function. The MAX4902/MAX4904/MAX4905 have internal shunt resistors to automatically discharge any capacitance at the NO_ and NC connection points. This reduces click-andpop sounds that occur when switching audio signals between pre-charged points. A break-before-make feature and auto-discharge also help to reduce popping.

These SPST and SPDT switches are available in space-saving 8-pin TDFN and 9-bump UCSP™ packages and operate over the -40°C to +85°C extended temperature range.


Cell Phones	Notebook Computers
PDAs and Handheld Devices	MP3 Players

UCSP is a trademark of Maxim Integrated Products, Inc.

_ Features

- Distortion-Free Signal Throughput Down to V_{CC} - 5.5V
- Comparator for Headphone or Mute Detection (MAX4905)
- Clickless Switches with Internal Shunt Resistors (MAX4902/MAX4904/MAX4905)
- ♦ 0.6Ω (typ) Low On-Resistance (RON)
- ♦ 0.25Ω On-Resistance Flatness
- +1.8V to +5.5V Supply Voltage
- 0.04% THD

Pin Configurations TOP VIEW BUMPS ON BOTTOM MAX4901/MAX4902 MAX4901/MAX4902 1 2 3 1 2 3 1 2 4 0 0 0 0



Pin Configurations continued at end of data sheet.

Ordering Information/Selector Guide

		-		-	-	
PART	PIN-PACKAGE	TOP MARK	CONFIGURATION	COMPARATOR	SHUNT	PKG CODE
MAX4901EBL-T	1.5mm x 1.5mm 9 UCSP-9	AEU	2 x SPST	No	No	B9-1
MAX4901ETA-T	8 TDFN-8	AOW	2 x SPST	No	No	T833-2
MAX4902EBL-T	1.5mm x 1.5mm 9 UCSP-9	AEV	2 x SPST	No	Yes	B9-1
MAX4902ETA-T	8 TDFN-8	AOX	2 x SPST	No	Yes	T833-2
MAX4903EBL-T	1.5mm x 1.5mm 9 UCSP-9	AEY	1 x SPDT	No	No	B9-1
MAX4903ETA-T	8 TDFN-8	AOY	1 x SPDT	No	No	T833-2
MAX4904EBL-T	1.5mm x 1.5mm 9 UCSP-9	AEW	1 x SPDT	No	Yes	B9-1
MAX4904ETA-T	8 TDFN-8	AOZ	1 x SPDT	No	Yes	T833-2
MAX4905EBL-T	1.5mm x 1.5mm 9 UCSP-9	AEX	1 x SPDT	Yes	Yes	B9-1
MAX4905ETA-T	8 TDFN-8	APA	1 x SPDT	Yes	Yes	T833-2

Note: All devices operate over the -40°C to +85°C operating temperature range.

Maxim Integrated Products 1

For pricing, delivery, and ordering information, please contact Maxim/Dallas Direct! at 1-888-629-4642, or visit Maxim's website at www.maxim-ic.com.

ABSOLUTE MAXIMUM RATINGS

(All voltages referenced to GND.)

V _{CC} , IN_, CMP0.3V to +6.0V	
$COM_{, NO_{, NC} NC (V_{CC} - 6V) to (V_{CC} + 0.3V)$	
CMPO0.3V to (V _{CC} + 0.3V)	
Open-Switch Continuous Current NO_, NC	
(MAX4902/MAX4904/MAX4905)±30mA	
Closed-Switch Continuous Current COM_, NO_, NC±100mA	
Peak Current COM_, NO_, NC	
(Pulsed at 1ms, 50% duty cycle)±200mA	
Peak Current COM_, NO_, NC	
(Pulsed at 1ms, 10% duty cycle)±300mA	

Continuous Power Dissipation ($T_A = +70^{\circ}C$)
8-Pin TDFN (derate 18.2mW/°C above +70°C)1455mW
9-Bump UCSP (derate 5.2mW/°C above +70°C)412mW
ESD Method 3015.7±2kV
Operating Temperature Range40°C to +85°C
Junction Temperature+150°C
Storage Temperature Range65°C to +150°C
Lead Temperature (soldering, 10s)+300°C
Bump Temperature (soldering)
Infrared (15s)+220°C
Vapor Phase (60s)+215°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

(V_{CC} = +2.7V to +5.5V, T_A = -40°C to +85°C, unless otherwise noted. Typical values are at V_{CC} = +3.0V, T_A = +25°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS		MIN	ТҮР	MAX	UNITS
POWER SUPPLY	·						•
Power-Supply Range	V _{CC}			1.8		5.5	V
Supply Current	l+	$V_{CC} = 5.5V,$ $V_{IN} = 0V \text{ or } V_{CC}$	MAX4901- MAX4904		0.001	1	μA
			MAX4905		5	10	
ANALOG SWITCH							
Analog Signal Range	V _{NO} _V _{NC} , V _{COM} _	(Note 2)		V _{CC} - 5.5		VCC	V
		$V_{CC} = 2.7V, V_{NC} \text{ or } V_{NO}$	$T_A = +25^{\circ}C$		0.6	1.0	
On-Resistance	$B_{ON(NC)} = V_{CC} - 5.5V - 1V_0 1V_0$	= V _{CC} - 5.5V, -1V, 0, 1V, 2V, V _{CC} ; I _{COM} = 100mA	$T_A = T_{MIN}$ to T_{MAX}			1.2	Ω
		$V_{CC} = 2.7 V$, I_{NO} or	$T_A = +25^{\circ}C$		0.01	0.25	
On-Resistance Match Between Channels	ΔR_{ON}	I _{NC} = 100mA or V _{NO} _ (Notes 3, 4, 5)	$T_A = T_{MIN}$ to T_{MAX}			0.30	Ω
		$V_{CC} = 2.7V$, V_{NC} or V_{NO}	$T_A = +25^{\circ}C$		0.25	0.5	
On-Resistance Flatness	R _{FLAT}	$= V_{CC} - 5.5V, -1V, 0, 1V, 2V, V_{CC}; I_{COM} = 100mA $ (Notes 4, 6)	T _A = T _{MIN} to T _{MAX}			0.5	Ω

ELECTRICAL CHARACTERISTICS (continued)

(V_{CC} = +2.7V to +5.5V, T_A = -40°C to +85°C, unless otherwise noted. Typical values are at V_{CC} = +3.0V, T_A = +25°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS		MIN	ТҮР	MAX	UNITS	
Shunt Resistance	R _{SH}	I _{NO_} or I _{NC} = 10mA, V _{CC} = 2.7V (MAX4902/MAX4904/ MAX4905)	T _A = T _{MIN} to T _{MAX}		30	50	Ω	
			$T_A = +25^{\circ}C$	-6		+6		
NO_, NC Off-Leakage Current	INO_(OFF), INC (OFF)	or V _{NO} _ = -2.5V, +2.5V; V _{COM} _ = +2.5V, -2.5V (MAX4901/ MAX4903) (Notes 3, 7)	T _A = T _{MIN} to T _{MAX}	-50		+50	nA	
		$V_{CC} = 2.7V$, switch open;	$T_A = +25^{\circ}C$	-6		+6		
COM_ Off-Leakage Current	ICOM_(OFF)	V _{NC} or V _{NO} = -2.5V, +2.5V; V _{COM} = -2.5V, +2.5V (MAX4901) (Note 3)	$T_A = T_{MIN}$ to T_{MAX}	-50		+50	nA	
		$V_{CC} = 2.7V$, switch closed;	$T_A = +25^{\circ}C$	-6		+6		
COM_ On-Leakage Current	ICOM_(ON)	V_{NC} or V_{NO} = -2.5V, +2.5V, or unconnected; V_{COM} = -2.5V, +2.5V or unconnected (Note 3)	T _A = T _{MIN} to T _{MAX}	-50		+50	nA	
DYNAMIC CHARACTERISTICS	•		•				•	
Turn-On Time	ton				25	100	ns	
Turn-Off Time	tOFF	$V_{CC} = 2.7V, V_{NO_{-}} = 1.5V, V_{IN_{-}} = V_{CC} \text{ to } 0;$ $V_{NC} = 1.5V, V_{IN_{-}} = 0 \text{ to } V_{CC}; R_{L} = 50\Omega,$ $C_{L} = 5pF \text{ (Figure 1)}$			15	100	ns	
Des als Defense Males Times Delay		$V_{CC} = 2.7V, V_{NO} = 1.5V,$	$T_A = +25^{\circ}C$	2	10			
Break-Before-Make Time Delay (MAX4903/MAX4904/MAX4905)	t _{BBM}		T _A = T _{MIN} to T _{MAX}	1			ns	
Charge Injection	Q	V_{COM} = 0V, R_S = 0 Ω , C_L = 1.0r	nF (Figure 3)		125		рС	
Off-Isolation (Note 8)	V _{ISO}	f = 100kHz, V _{COM} = 1V _{RMS} , R _L = 50 Ω , C _L = 5pF (Figure 4)			-70		dB	
Crosstalk	V _{CT}	f = 100kHz, V _{COM} = 1V _{RMS} , R _L = 50Ω, C _L = 5pF (Figure 4)			-75		dB	
Power-Supply Rejection Ratio	PSRR	$ f = 10 kHz, V_{COM} = 1 V_{RMS}, \\ R_L = 50 \Omega, C_L = 5 pF $			60		dB	
On-Channel -3dB Bandwidth	BW	Signal = 0dBm, $R_L = 50\Omega$, $C_L = 5pF$ (Figure 4)			27		MHz	
Total Harmonic Distortion	THD	$f = 20Hz \text{ to } 20\text{kHz}, V_{COM} = 0.5V_{P-P},$ DC bias = 0, R _L = 32Ω			0.04		%	

MAX4901-MAX4905

ELECTRICAL CHARACTERISTICS (continued)

(V_{CC} = +2.7V to +5.5V, T_A = -40°C to +85°C, unless otherwise noted. Typical values are at V_{CC} = +3.0V, T_A = +25°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
NO_, NC Off-Capacitance	C _{NO_(OFF)} C _{NC(OFF)}	f = 1MHz, V _{COM} = 0.5V _{P-P} , DC bias = 0 (Figure 5)		40		pF
COM On-Capacitance	C _{COM_(ON)}	f = 1MHz, V _{COM} = 0.5V _{P-P} , DC bias = 0 (Figure 5)		200		pF
DIGITAL I/O (IN_)			•			
	N	V _{CC} = 2.7V to 3.6V	1.4			V
Input Logic-High Voltage	VIH	V _{CC} = 4.2V to 5.5V	2.0			V
Input Logic-Low Voltage	VIL	V _{CC} = 2.7V to 3.6V			0.5	V
		$V_{CC} = 4.2V$ to 5.5V			0.8	
Input Leakage Current	I _{IN}	$V_{IN} = 0V \text{ or } V_{CC}$	-1		+1	μA
COMPARATOR (MAX4905)						
Comparator Threshold				V _{CC} / 3		V
Comparator Output-High Voltage		ISOURCE = 1mA	V _{CC} - 0.4V			V
Comparator Output-Low Voltage		I _{SINK} = 1mA			0.4	V
Comparator Input Leakage		V _{CMP} - = 0 to 2.7V	-100		+100	nA
Comparator Switching Time		V_{CC} = 2.7V, V_{CMP-} = 0V to V_{CC} , from 50% of V_{CMP-} to 50% of V_{CMPO}		1	2	μs

Note 1: UCSP and TDFN parts are 100% tested at TA = +25°C only, and guaranteed by design over the specified temperature range.

Note 2: Signals on COM_, NO_, or NC exceeding V_{CC} are clamped by internal diodes. Limit forward-diode current to maximum current rating.

Note 3: Guaranteed by design.

Note 4: I_{COM} for UCSP is 10mA.

Note 5: $\Delta RON = RON(MAX) - RON(MIN)$.


Note 6: Flatness is defined as the difference between the maximum and minimum value of on-resistance as measured over the specified analog signal ranges.

Note 7: The MAX4902/MAX4904/MAX4905 have an internal shunt resistor when, in off-state, will determine off-current.


Note 8: Off-Isolation = 20log10 (VCOM / VNO), VCOM = output, VNO = input to off switch.

 $(T_A = +25^{\circ}C, V_{CC} = 3.0V, unless otherwise noted.)$


Typical Operating Characteristics



MAX4901-MAX4905



MAX4901-MAX4905





1 5 5

-40

-15

35

60

85

10

TEMPERATURE (°C)


_Pin Description (MAX4901/MAX4902 Dual-SPST Switches)

P	PIN		PIN NAME		FUNCTION
TDFN	UCSP	NAME	FUNCTION		
1	B1	V _{CC}	Positive Supply-Voltage Input. Bypass V_{CC} to GND with a 0.1 μF capacitor as close to V_{CC} as possible.		
2	A1	COM1	Analog Switch 1, Common Terminal		
_	B2	N.C.	No Connection. Leave N.C. unconnected.		
3	A2	NO1	Analog Switch 1, Normally Open Terminal. NO1 (MAX4902) has a shunt resistor to GND when the switch is in open position.		
4	A3	IN1	Digital Control Input for Analog Switch 1. A logic high on IN1 connects COM1 to NO1 and a logic low opens the switch.		
5	B3	GND	Ground		
6	C3	IN2	Digital Control Input for Analog Switch 2. A logic high on IN2 connects COM2 to NO2 and a logic low opens the switch.		
7	C2	NO2	Analog Switch 2, Normally Open Terminal. NO2 has a shunt resistor to GND when the switch is in open position (MAX4902).		
8	C1	COM2	Analog Switch 2, Common Terminal		
EP	_	EP Exposed Pad. Connect exposed pad to GND.			

Pin Description (MAX4903/MAX4904/MAX4905 SPDT Switches)

P	PIN		PIN NAME		FUNCTION
TDFN	UCSP	NAME	FUNCTION		
1	A1	Vcc	Positive Supply-Voltage Input. Bypass V_{CC} to GND with a 0.1 μF capacitor as close to V_{CC} as possible.		
2	A2	NO	Analog Switch, Normally Open Terminal. NO has a shunt resistor to GND when the switch is in open position (MAX4904/MAX4905).		
3	A3	IN	Digital Control Input. Logic low on IN connects COM to NC and logic high connects COM to NO.		
4	B2	N.C.	No Connection. Leave N.C. unconnected (MAX4903/MAX4904).		
4	DZ	CMPO	Comparator Output (MAX4905)		
5	B3	GND	Ground		
6	C3	N.C.	No Connection. Leave N.C. unconnected (MAX4903/MAX4904).		
0	03	CMP-	Comparator Input (MAX4905)		
7	C2	NC	Analog Switch, Normally Closed Terminal. NC has a shunt resistor to GND when the switch is in open position (MAX4904/MAX4905).		
8	B1	COM	Analog Switch, Common Terminal		
_	C1	N.C.	No Connection. Leave N.C. unconnected (MAX4903/MAX4904/MAX4905)		
EP	_	EP Exposed Pad. Connect exposed pad to GND.			

Typical Operating Circuit



Detailed Description

The MAX4901–MAX4905 are low on-resistance, low-voltage, dual-SPST and single-SPDT analog switches that operate from a +1.8V to +5.5V supply and are fully specified for nominal 3.0V applications. The devices feature a negative signal capability that allows signals below ground to pass through without distortion and have break-before-make switching (MAX4903/ MAX4904/MAX4905).

The MAX4905 features a comparator that can be used for headphone or mute detection. The comparator threshold is internally generated to be approximately 1/3 of V_{CC}. The MAX4902/MAX4904/MAX4905 feature an internal shunt resistor to discharge any capacitance at NO_ and NC connection points. This reduces the click-and-pop sounds that occur when switching audio signals.

Applications Information

Digital Control Inputs

The MAX4901–MAX4905 logic inputs accept up to +5.5V, regardless of supply voltage. For example, with a +3.3V supply, IN_ can be driven low to GND and high to +5.5V, allowing for mixing of logic levels in a system. Driving IN_ rail-to-rail minimizes power consumption. For a +1.8V supply voltage, the logic thresholds are 0.5V (low) and 1.4V (high). For a +5V supply voltage, the logic thresholds are 0.8V (low) and 2.0V (high).

Analog Signal Levels

The on-resistance of the MAX4901–MAX4905 changes very little for analog input signals across the entire supply-voltage range (see the *Typical Operating Characteristics*). The switches are bidirectional.

The MAX4901–MAX4905 pass signals as low as V_{CC} - 5.5V, including signals below ground with minimal distortion. Note that there are shunt resistors on NO_ and NC when they are unconnected to COM_ for the MAX4902/MAX4904/MAX4905.

Comparator (MAX4905)

The MAX4905 includes a comparator that can be used for mute and headphone detection functions. The positive terminal of the comparator is internally set to V_{CC} / 3. When the negative terminal (CMP-) is below the threshold, the comparator output (CMPO) is a logic high.

The comparator threshold of V_{CC} / 3 allows for detection of headphones because headphone audio signals are typically biased to V_{CC} / 2.

Shunt Resistor (MAX4902/MAX4904/MAX4905)

The 50 Ω shunt resistors on the MAX4902/MAX4904/ MAX4905 automatically discharge any capacitance at the NC or NO_ terminals when they are unconnected to COM_. This reduces audio click-and-pop sounds that occur when switching between audio sources.



Audible clicks and pops are caused when a step DC voltage is switched into the speaker. By automatically discharging the side that is not connected, any residual DC voltage is removed, thereby reducing the clicks and pops.

Power-Supply Sequencing and Overvoltage Protection


Caution: Do not exceed the absolute maximum ratings because stresses beyond the listed ratings may cause permanent damage to the device.


Proper power-supply sequencing is recommended for all CMOS devices. Always apply V_{CC} before applying analog signals, especially if the analog signal is not current-limited.

UCSP Applications Information

For the latest application details on UCSP construction, dimensions, tape carrier information, PC board techniques, bump-pad layout, and recommended reflow temperature profile, as well as the latest information on reliability testing results, refer to the Application Note: UCSP—A Water-Level Chip-Scale Package on Maxim's web site at www.maxim-ic.com/ucsp.

Pin Configurations/Functional Diagrams/Truth Tables





 \leq


Cı

V_{OUT}

Test Circuits/Timing Diagrams

0.9 x V_{OUT}

t_{BBM}



LOGIC

INPUT

IN

GND

-

CL INCLUDES FIXTURE AND STRAY CAPACITANCE.




Figure 3. Charge Injection

_Test Circuits/Timing Diagrams (continued)




Figure 4. -3dB Bandwidth, Off-Isolation, and Crosstalk





Figure 5. Channel Off-/On-Capacitance

Chip Information

PROCESS: BICMOS


Package Information

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information, go to **www.maxim-ic.com/packages**.)



Package Information (continued)

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information, go to **www.maxim-ic.com/packages**.)



Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600 _

© 2006 Maxim Integrated Products

MAXIM is a registered trademark of Maxim Integrated Products, Inc.