General Description

The MAX98300 evaluation kit (EV kit) is a fully assembled and tested circuit board that uses the MAX98300 filterless Class D amplifier to drive a speaker in portable audio applications. The EV kit comes with a MAX98300 IC in an 8-pin TDFN package. Designed to operate from a 2.6V to 5.5V DC power supply, the EV kit is capable of delivering 2.6W into a 4 Ω load. The EV kit accepts differential or single-ended input signals.

Features

 Demonstrates Industry-Leading Quiescent Current

1.1mA (PVDD = 5V), 0.78mA (PVDD = 3.7V)

- Filterless Operation Passes Radiated Emissions with Up to 60cm of Speaker Cable
- ♦ 2.6V to 5.5V Single-Supply Operation
- ♦ 2.6W Mono Class D Output
- Selectable Gain Control
- Differential or Single-Ended Input
- Low-Power Shutdown Input
- Fully Assembled and Tested

Ordering Information

| | PART | TYPE |
|--|--------------------|--------|
| | MAX98300EVKIT+TDFN | EV Kit |
| | | |

+Denotes lead(Pb)-free and RoHS compliant.

Component List

| DESIGNATION | QTY | DESCRIPTION | | | |
|---|--|--|--|--|--|
| MINIMAL COMP | MINIMAL COMPONENTS FOR CUSTOMER DESIGN | | | | |
| C1 | C1 0.1µF ±10%, 16V X7R centric C1 1 capacitor (0603) Murata GRM188R71C104 | | | | |
| $\begin{tabular}{ c c c c c } \hline C2 & 1 & 10\mu F \pm 10\%, 10V X5R ceramic \\ capacitor (0805) \\ Murata GRM219R61A106K \\ \hline C5, C6 & 2 & 1\mu F \pm 10\%, 10V X5R ceramic \\ capacitors (0603) \\ Murata GRM188R61A105K \\ \hline U1 & 1 & Mono Class D amplifier \\ (8 TDFN-EP^*) \\ Maxim MAX98300ETA+ \\ (Top Mark: ADB) \\ \hline \end{tabular}$ | | | | | |
| | | capacitors (0603) | | | |
| | | (8 TDFN-EP*) Maxim MAX98300ETA+ | | | |
| OPTIONAL CON EVALUATION | OPTIONAL COMPONENTS FOR CUSTOMER EVALUATION | | | | |
| C3, C4 0 Not installed, ceramic capaci (0603) | | Not installed, ceramic capacitors (0603) | | | |
| C7-C11 | C7-C11 5 0.22µF ±10%, 25V X7R cer capacitors (0603) Murata GRM188R71E224K | | | | |

| DESIGNATION | QTY | DESCRIPTION |
|---|-----|---|
| FB1, FB2 | 2 | $0\Omega \pm 5\%$ resistors (0805) |
| JU1 | 1 | 3-pin header |
| JU2 | 1 | 2-pin header |
| JU3 | 1 | 4-way 5-pin header |
| L1, L2 | 0 | Not installed, inductors Recommended: TOKO #A916CY-220M |
| OUT+ | 1 | Standard PCB test point, red |
| OUT- | 1 | Standard PCB test point, white |
| R1, R2 | 2 | 22Ω ±1% resistors (0603) |
| , | | 100k Ω ±5% resistors (0603) |
| | | Shunts (JU1, JU2, JU3) |
| _ | 1 | PCB: MAX98300 EVALUATION KIT+ (TDFN) |

*EP = Exposed pad.

M/IXI/M

Maxim Integrated Products 1

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim's website at www.maxim-ic.com.

Evaluates: MAX98300 in a TDFN

| SUPPLIER | PHONE | WEBSITE |
|--|--------------|-----------------------------|
| Murata Electronics North America, Inc. | 770-436-1300 | www.murata-northamerica.com |
| TOKO America, Inc. | 847-297-0070 | www.tokoam.com |

Note: Indicate that you are using the MAX98300ETA+ when contacting these component suppliers.

_Quick Start

Recommended Equipment

- MAX98300 EV kit (TDFN)
- 2.6V to 5.5V, 2A DC supply
- 4Ω speaker
- Mono audio signal source

Procedure

The EV kit is fully assembled and tested. Follow the steps below to verify board operation. **Caution: Do not turn on the power supply until all connections are completed.**

- 1) Verify that shunts are installed as follows:
 - JU1: Pins 1-2 (device enabled)

JU2: Installed (single-ended input)

JU3: Pins 1-5 (0dB gain)

- 2) Connect the power-supply positive and negative outputs to the PVDD and PGND PCB pads on the EV kit, respectively.
- 3) Verify that the audio source output is disabled.
- 4) Connect the mono audio source between the INPUT+ and INPUT- pads on the EV kit.
- 5) Connect the speaker across the OUT+ and OUT- test points.
- 6) Set the power-supply output to 5V.
- 7) Enable the power-supply output.
- 8) Enable the audio source.
- 9) Verify that the speaker is playing the audio source signal.

_Detailed Description of Hardware

Component Suppliers

The MAX98300 EV kit features the MAX98300 filterless Class D amplifier IC, which is designed to drive a mono speaker in portable audio applications. The EV kit comes with a MAX98300 IC in an 8-pin TDFN package. The EV kit operates from a DC power supply that provides 2.6V to 5.5V and 2A of current. The EV kit accepts a differential or single-ended audio input. The audio input source is amplified to drive 2.6W into a 4 Ω speaker.

Jumper JU1 enables or disables the speaker amplifier. Jumper JU2 configures the EV kit inputs for single-ended or differential operation. The amplifier overall gain can be set between 0dB and +12dB using jumper JU3. The EV kit provides a set of differential outputs. The device outputs (OUT+, OUT-) can be connected directly to a speaker load without any filtering and up to 60cm of cable. However, filter components can be added to ease evaluation. See the *Output Filtering Options* section for additional information.

Shutdown

Jumper JU1 enables or disables the audio speaker amplifier. See Table 1 for jumper JU1 configuration.

Table 1. Shutdown (JU1)

| SHUNT POSITION | SHDN PIN | AMPLIFIER |
|-------------------|-------------------|-----------|
| 1-2* | Connected to PVDD | Enabled |
| 2-3 | Connected to PGND | Disabled |

*Default position.

Filterless Output

The EV kit's filterless outputs (OUT+, OUT-) can be connected directly to a speaker load without any filtering. Use the OUT+ and OUT- test points to connect a speaker directly to the device outputs. Inductors L1 and L2 are not installed for maximum efficiency.

Output Filtering Options

To ease evaluation, the EV kit is shipped with inductorbased output filters. To use the inductor-based output filters, install inductors L1 and L2 (provided with the EV kit).

The device passes CE EN55022B regulations with up to 60cm of speaker cable and no filtering. However, ferrite-bead filters can be used to achieve further attenuation of radiated emissions. To install the ferrite-bead filters, verify that filter inductors L1 and L2 are not installed. Next, replace shorting resistors FB1 and FB2 with 0805 or smaller ferrite beads and install filter capacitors on the C3 and C4 pads. The speaker wire should be connected to the OUT+ and OUT- test points.

Table 3. Gain Setting (JU3)

| SHUNT POSITION | GAIN PIN | MAXIMUM GAIN (dB) |
|-------------------|------------------------------|----------------------|
| 1-2 | Connected to PVDD through R3 | +9 |
| 1-3 | Connected to PVDD | +12 |
| 1-4 | Connected to PGND through R4 | +3 |
| 1-5* | Connected to PGND | 0 |
| Open | Not connected | +6 |

*Default position.

Input Mode

Jumper JU2 provides the option to select between a differential or single-ended input mode for the EV kit. See Table 2 for jumper JU2 configuration.

Gain Setting

The EV kit maximum signal gain can be configured to five different settings. Jumper JU3 selects the overall gain for the EV kit. See Table 3 for jumper JU3 configuration.

Filtered Output

Audio analyzers typically cannot accept pulse-widthmodulated (PWM) signals at their inputs. Therefore, the EV kit features a lowpass filter at its outputs to ease evaluation. Install inductors L1 and L2 (provided with the EV kit) and use the filtering output posts (FOUT+, FOUT-) to connect the filtered PWM outputs to the audio analyzer. The default lowpass filter at the EV kit outputs is optimized for an 8Ω speaker.

Table 2. Input Mode (JU2)

| SHUNT POSITION | INPUT- PCB PAD | INPUT MODE |
|-------------------|--|-----------------------|
| Installed* | Connected to PGND | Single-ended input |
| Not installed | Connected to a user-supplied negative differential input | Differential input |

*Default position.




Figure 1. MAX98300 Customer Design Schematic (TDFN)

MAX98300 Evaluation Kit (TDFN)




Figure 2. MAX98300 EV Kit Schematic (TDFN)




Figure 3. MAX98300 EV Kit (TDFN) Component Placement Guide—Component Side




Figure 4. MAX98300 EV Kit (TDFN) PCB Layout—Component Side




Figure 5. MAX98300 EV Kit (TDFN) PCB Layout—Solder Side

Revision History

| REVISION | REVISION | DESCRIPTION | PAGES |
|----------|----------|-----------------|---------|
| NUMBER | DATE | | CHANGED |
| 0 | 7/10 | Initial release | — |

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600 _

© 2010 Maxim Integrated Products

Maxim is a registered trademark of Maxim Integrated Products, Inc.

7