# **Power Management IC**

## **General Description**

The MAX77826 is a subpower management IC for the latest 3G/4G smartphones and tablets. The MAX77826 contains a high-efficiency BUCK regulator, a BUCK BOOST regulator and 15 LDOs to power up peripherals. The MAX77826 also provides power on/off control logic and an I<sup>2</sup>C serial interface to program individual regulator output voltages and on/off control for complete flexibility.

The linear regulators support a remote cap feature and provide greater than 70dB PSRR and less than 45 $\mu$ V<sub>RMS</sub> noise.

The MAX77826 features I<sup>2</sup>C-compatible, 2-wire serial interface that comprises a bidirectional serial data line (SDA) and a serial clock line (SCL). The MAX77826 supports SCL clock rates up to 3.4MHz.

## **Applications**

 GSM, GPRS, EDGE, CDMA WCDMA, and LTE Smartphones and Tablets

Ordering Information appears at end of data sheet.

### **Benefits and Features**

- Compact Total Solution Size Allows More Peripheral Devices in Smartphones and Tablets
  - 3A High-Efficiency BUCK Regulator
    - DVS (Dynamic Voltage Scaling) Through HS I<sup>2</sup>C
    - ±1% (typ) Output Voltage DC Accuracy
    - · Low Power Mode
  - · 2A BUCK BOOST Regulator
  - · 15 Linear Regulators with Remote Cap
    - 3 NMOS LDOs (V<sub>OUT</sub> Range: 0.6V to 2.1875V with 12.5mV Step)
    - 1 x 150mA
    - 1 x 450mA
    - 1 x 600mA
  - 6 PMOSLV LDOs (V<sub>OUT</sub> Range: 0.8V to 3.975V with 25mV Step)
    - 3 x 150mA
    - 3 x 300mA
  - 6 PMOSLS LDOs (V<sub>OUT</sub> Range: 0.8V to 3.975V with 25mV Step)
    - 3 x 150mA
    - 3 x 300mA
  - ±1.5% Typical Output Voltage DC Accuracy
  - 70dB PSRR at 1kHz
  - Low Power Mode with 2µA (typ) for all LDOs
- Simple Management of Power-Up/Down Sequence, Output Voltage Setting, and Fault Detection
  - High-Speed (Up to 3.4MHz) I<sup>2</sup>C Serial Interface



# **Absolute Maximum Ratings**

SYS, V <sub>IO</sub> , INL1, INL2, INL3,	LDO1, LDO2 to GND0.3V to (V <sub>INL1</sub> + 0.3V)
INL4, INL5 to GND0.3V to +6.0V	LDO3 to GND0.3V to (V <sub>INL2</sub> + 0.3V)
INB to PGNDB0.3V to +6.0V	LDO4, LDO5, LDO6, LDO7, LDO8,
INBB, OUTBB to PGNDBB0.3V to +6.0V	LDO9 to GND0.3V to (V <sub>INL3</sub> + 0.3V)
PGNDB, PGNDBB to GND0.3V to +0.3V	LDO10, LDO11 to GND0.3V to (V <sub>INL4</sub> + 0.3V)
IRQB, CE, SDA, SCL to GND0.3V to (V <sub>VIO</sub> + 0.3V)	LDO12, LDO13, LDO14,
FB_B, ENBB, ENB, ENL12,	LDO15 to GND0.3V to (V <sub>INL5</sub> + 0.3V)
REFBYP to GND0.3V to (V <sub>SYS</sub> + 0.3V)	LXB Continuous RMS Current (Note 1)3A
FB_BB to PGNDBB0.3V to (V <sub>OUTBB</sub> + 0.3V)	LXBB1/LXBB2 Continuous RMS Current (Note 1)3.3A
LXB to PGNDB0.3V to (V <sub>INB</sub> + 0.3V)	Operating Temperature Range40°C to +85°C
LXBB1 to PGNDBB	Junction Temperature+150°C
LXBB2 to PGNDBB0.3V to (V <sub>OUTBB</sub> + 0.3V)	Storage Temperature Range65°C to +150°C
	Soldering Temperature (reflow)+260°C

Note 1: LX\_ node has internal clamp diodes to PGND\_ and INB\_. Applications that give forward bias to these diodes should ensure that the total power loss does not exceed IC's package power dissipation limits.

# **Package Thermal Characteristics (Note 2)**

WLP

Junction-to-Ambient Thermal Resistance (θ<sub>JA</sub>) .......37°C/W

**Note 2:** Package thermal resistances were obtained using the method described in JEDEC specification JESD51-7, using a four-layer board. For detailed information on package thermal considerations, refer to <a href="https://www.maximintegrated.com/thermal-tutorial">www.maximintegrated.com/thermal-tutorial</a>.

### **General Electrical Characteristics**

( $V_{SYS} = V_{IN} = +3.7V$ ,  $V_{IO} = 1.8V$ ,  $T_A = -40^{\circ}C$  to  $+85^{\circ}C$ , unless otherwise noted.)

VPARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Shutdown Supply Current	I <sub>SHDN_SYS</sub>	CE = low		2.5	10	μA
Standby Current	I <sub>Q_SYS</sub>	CE = high and all regulators are off		35		μA
Shutdown V <sub>IO</sub> Current	I <sub>SHDN_VIO</sub>	All regulators are off		0		μA
No Load Supply Current 1	I <sub>NO_LOAD1</sub>	BUCK is on in normal mode (no switching) 60			μА	
No Load Supply Current 2	I <sub>NO_LOAD2</sub>	BUCK and BUCK BOOST are on in normal mode (no switching)	120		μА	
No Load Supply Current 3	I <sub>NO_LOAD3</sub>	All regulators are on in normal mode (no switching)		400	700	μА
V <sub>SYS</sub> UNDERVOLTAGE LOCKO	JT					
V <sub>SYS</sub> Undervoltage Lockout	V <sub>UVLO_R</sub>	V <sub>SYS</sub> rising	2.375	2.50	2.625	V
Threshold	V <sub>UVLO_F</sub>	V <sub>SYS</sub> falling (default)		2.05		V
REFERENCE						
REFBYP Output Voltage			0.786	0.80	0.814	V
REFBYP Supply Rejection		2.7V ≤ V <sub>SYS</sub> ≤ 5.5V		0.2		mV/V

# **General Electrical Characteristics (continued)**

(V<sub>SYS</sub> = V<sub>IN</sub> = +3.7V, V<sub>IO</sub> = 1.8V, T<sub>A</sub> = -40°C to +85°C, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS		MIN	TYP	MAX	UNITS
THERMAL SHUTDOWN							
Thermal Shutdown Threshold	T <sub>SHDN</sub>	T <sub>J</sub> rising, 15°C hyst	eresis		+165		°C
Thermal Interrupt at +120°C	T <sub>120</sub>	T <sub>J</sub> rising, 15°C hyst	eresis		+120		°C
Thermal Interrupt at +140°C	T <sub>140</sub>	T <sub>J</sub> rising, 15°C hyst	eresis		+140		°C
LOGIC AND CONTROL INPUTS							
Input Low Level	V <sub>IL</sub>	ENB, ENBB, ENL12	$V_{SYS} \le 4.5V$ $T_A = +25^{\circ}C$			0.4	V
		CE	T <sub>A</sub> = +25°C			0.3 x V <sub>VIO</sub>	
Input High Level	V <sub>IH</sub>	ENB, ENBB, ENL12	$V_{SYS} \le 4.5V$ $T_A = 25^{\circ}C$	1.2			V
	- 111	CE	T <sub>A</sub> = +25°C	0.7 x V <sub>VIO</sub>			
Logic Input Lockago Current	1	CE	T <sub>A</sub> = +25°C	-1		+1	^
Logic Input Leakage Current	I <sub>LEAK</sub>	$(0V < V_{IO} < 1.8V)$	T <sub>A</sub> = +85°C		0.1		μA
IRQB Output Low Voltage	V <sub>OL</sub>	I <sub>SINK</sub> = 1mA				0.4	V
IDOD Output High Lookers		\/ - F F\/	T <sub>A</sub> = +25°C	-1		+1	
IRQB Output High Leakage	lozh	V <sub>IO</sub> = 5.5V	T <sub>A</sub> = +85°C	0.1			μA
INTERNAL PULLDOWN RESISTA	ANCE		•				
ENB, ENBB, ENL12	R <sub>PD</sub>	Pulldown resistor to GND		400	800	1600	kΩ

# **I<sup>2</sup>C Electrical Characteristics**

(V<sub>SYS</sub> = V<sub>IN</sub>\_ = +3.7V, V<sub>IO</sub> = 1.8V, T<sub>A</sub> = -40 $^{\circ}$ C to +85 $^{\circ}$ C, unless otherwise noted.) (Note 5)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
POWER SUPPLY						
VIO Voltage	V <sub>VIO</sub>		1.7		3.6	V
SDA AND SCL I/O STAGES						
SCL, SDA Input High Voltage	V <sub>IH</sub>		0.7 x V <sub>VIC</sub>	)		V
SCL, SDA Input Low Voltage	V <sub>IL</sub>				0.3 x V <sub>VIO</sub>	V
SCL, SDA Input Hysteresis	V <sub>HYS</sub>			0.05 x V <sub>VIO</sub>		V
SCL, SDA Input Current	II	V <sub>IO</sub> = 3.7V	-10		+10	μA
SDA Output Low Voltage	V <sub>OL</sub>	I <sub>SINK</sub> = 20mA			0.4	V
SCL, SDA Pin Capacitance	Cl			10		pF
Output Fall Time from V <sub>IO</sub> to 0.3 x V <sub>IO</sub>	t <sub>OF</sub>				120	ns
I <sup>2</sup> C-COMPATIBLE INTERFACE T	IMING (STAN	DARD, FAST, AND FAST MOD	E PLUS) (Note	3)		
Clock Frequency	fscl				1000	kHz
Hold Time (REPEATED) START Condition	t <sub>HD;STA</sub>		0.26			μs
CLK Low Period	t <sub>LOW</sub>		0.5			μs
CLK High Period	t <sub>HIGH</sub>		0.26			μs
Setup Time REPEATED START Condition	t <sub>SU;STA</sub>		0.26			μs
DATA Hold Time	t <sub>HD:DAT</sub>		0			μs
DATA Setup Time	t <sub>SU;DAT</sub>		50			ns
Setup Time for STOP Condition	t <sub>SU;STO</sub>		0.26			μs
Bus-Free Time Between STOP and START	t <sub>BUF</sub>		0.5			μs
Capacitive Load for Each Bus Line	C <sub>B</sub>				550	pF
Maximum Pulse Width of Spikes That Must Be Suppressed by the Input Filter				50		ns

# I<sup>2</sup>C Electrical Characteristics (continued)

(V<sub>SYS</sub> = V<sub>IN</sub> = +3.7V, V<sub>IO</sub> = 1.8V, T<sub>A</sub> = -40°C to +85°C, unless otherwise noted.) (Note 5)

DADAMETED	OVMDOL	CONDITIONS	(	C <sub>B</sub> = 100p	F	С	<sub>B</sub> = 400p	F	
PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	UNITS
I <sup>2</sup> C-COMPATIBLE INTERFA	ACE TIMING (H	IS MODE)				'			
Clock Frequency	f <sub>SCL</sub>				3.4			1.7	MHz
Set-Up Time REPEATED START Condition	t <sub>SU;STA</sub>		160			160			ns
Hold Time (REPEATED) START Condition	t <sub>HD;STA</sub>		160			160			ns
CLK Low Period	t <sub>LOW</sub>		160			320			ns
CLK High Period	t <sub>HIGH</sub>		60			120			ns
DATA Setup time	t <sub>SU:DAT</sub>		10			10			ns
DATA Hold Time	t <sub>HD:DAT</sub>			35			75		ns
SCL Rise Time (Note 3)	t <sub>RCL</sub>	T <sub>A</sub> = +25°C	10		40	20		80	ns
Rise Time of SCL Signal After a REPEATED START Condition and After an Acknowledge Bit (Note 3)	<sup>t</sup> rCL1	T <sub>A</sub> = +25°C	10		80	20		160	ns
SCL Fall Time (Note 3)	t <sub>fCL</sub>	T <sub>A</sub> = +25°C	10		40	20		80	ns
SDA Rise Time (Note 3)	t <sub>rDA</sub>	T <sub>A</sub> = +25°C			80			160	ns
SDA Fall Time (Note 3)	t <sub>fDA</sub>	T <sub>A</sub> = +25°C			80			160	ns
Set-Up Time for STOP Condition	tsu;sto		160			160			ns
Capacitive Load for Each Bus Line	C <sub>B</sub>				100			400	pF
Maximum Pulse Width of Spikes That Must Be Suppressed by the Input Filter				10			10		ns

# **BUCK Electrical Characteristics**

 $(V_{SYS} = V_{INB} = +3.7V, V_{FB\_B} = V_{OUT} = 1.25V, T_A = -40^{\circ}C \text{ to } +85^{\circ}C, \text{ typical values are at } T_A = +25^{\circ}C, \text{ unless otherwise noted.}) \text{ (Note 4)}$ 

PARAMETER	CON	IDITIONS	MIN	TYP	MAX	UNITS		
Input Voltage Range	Parametric		2.6		5.5	V		
Shutdown Supply Current (Note 3)				0.1		μА		
Supply Quiescent Current	No switching,	Normal mode		22		μΑ		
(Note 3)	No load	Low power mode		8		μ, ,		
Output Voltage Range	I <sup>2</sup> C-programmable 6.25m <sup>1</sup>	/ step	0.5		1.8	V		
Output Voltage Accuracy	V <sub>INB</sub> = 2.6V to 4.5V, V <sub>OUT</sub> = 1.25V, no load	PWM mode, T <sub>A</sub> = +25°C Low power mode	-1.0 -3.0		+1.0	- %		
Line Regulation	V <sub>INB</sub> = 2.6V to 4.5V			0.200		%/V		
Load Regulation (Note 3)	V <sub>OUT</sub> = 1.25V			0.125		%/A		
Transient Load Response, VDROOP (Note 3)		ges from 0A to 1.5A in 6μs, <sub>-</sub> = 0.47μH		-50		mV		
Soft-Start Slew Rate			14		mV/μs			
	RAMP[1:0] = 00b (default)		12.5					
Output Voltage Ramp-Up Slew Rate	RAMP[1:0] = 01b			25		70)//::0		
	RAMP[1:0] = 10b	RAMP[1:0] = 10b				mV/μs		
	RAMP[1:0] = 11b			100				
Maximum Output Current	Normal mode		3000			m A		
Maximum Output Current	Low power mode			10		mA		
Peak Current Limit			3.30	4.25	5.50	А		
Valley Current Limit				3.825		Α		
Negative Current Limit				1.000		Α		
N-FET Zero-Crossing Threshold	Skip mode			20		mA		
Switching Frequency			1.8	2	2.2	MHz		
Turn-On Delay Time	EN signal to LX switching	with bias ON		30		μs		
HS PMOS RDSON	$V_{INB}$ = 3.7V, INB to LX, IL	<sub>X</sub> = 200mA		60		mΩ		
LS NMOS RDSON	V <sub>INB</sub> = 3.7V, LX to PGNDI	3, I <sub>LX</sub> = 200mA		35		mΩ		
Output Active Discharge Resistance	Output disabled, resistance	Output disabled, resistance from FB_B to PGNDB				Ω		
LX Leakage	V <sub>LXB</sub> = 5.5V or 0V	T <sub>A</sub> = +25°C	-1	0.1	+1	11.4		
LA Lounago	V <sub>LXB</sub> = 5.5V or 0V T <sub>A</sub> = +85°C			1		μA		
POWER-OK COMPARATOR			1					
Output POK Trip Level	V <sub>OUT</sub> POK rising threshol	d		90		%		
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> switche	s		5		%		

# **BUCK BOOST Electrical Characteristics**

 $(V_{INBB}$  = +3.7V,  $V_{OUTBB}$  = +3.5V,  $T_A$  = -40°C to +85°C, typical values are at  $T_A$  = +25°C, unless otherwise noted.) (Note 5)

PARAMETER		CONDIT	IONS	MIN	TYP	MAX	UNITS
GENERAL							
Operating Input Voltage Range	Supplied from V	SYS		2.6		5.5	V
Shutdown Supply Current	V <sub>INBB</sub> = 5.5V,		T <sub>A</sub> = +25°C		0.01		
Shutdown Supply Current	V <sub>OUTBB</sub> = 0V		T <sub>A</sub> = +85°C		1		μA
Input Cumply Current	Enabled, no	HSKIP mod	de (no switching)		60		μA
Input Supply Current	load	FPWM mo	de (switching)		9		mA
Active Discharge Resistance							Ω
Thermal Shutdown	T <sub>A</sub> rising, 20°C h	nysteresis			+165		°C
H-BRIDGE							
Maximum Output Current (Note 6)	V <sub>INBB</sub> = 3.0V, V <sub>0</sub>	2000			mΛ		
Maximum Output Current (Note 6)	V <sub>INBB</sub> = 2.6V, V <sub>0</sub>	OUTBB = 3.5	V	1500			mA
Default Output Voltage	No load, BB_VO		3.5		V		
	BB_VOUT[6:0] = 0x48, no load		PWM mode	-1.0		+1.0	%
Output Voltage Accuracy			HSKIP mode T <sub>A</sub> = +25°C	-1.0		+4.0	
Output Voltage Range	I <sup>2</sup> C programmab	2.6		4.1875	V		
Line Regulation	V <sub>INBB</sub> = 2.6V to	5.5V			0.200		%/V
Load Regulation (Note 3)	V <sub>OUTBB</sub> = 3.5V				0.125		%/A
Transient Load Response, V <sub>DROOP</sub> (Note 3)	V <sub>INBB</sub> = 3.8V, V <sub>0</sub> I <sub>OUT</sub> changes fro ACTUAL = 47μF	om 10mA to	V, 1A in 10µs, C <sub>OUT</sub> _		-100		mV
		BB_OV	'P_TH[1:0] = 01b		110		
Output Overvoltage Threshold	With respect to	BB_OV	P_TH[1:0] = 10b		115		%
Carpat Overvoltage Tilloshera	V <sub>OUTBB</sub>	BB_OV (default	(P_TH[1:0] = 11b i)		120		,,
Cuitabina Francisco	2-phase BUCK of	or BOOST m	ode	1.6	1.8	2.0	NAL I-
Switching Frequency	3-phase mode				0.9		MHz
LVDD4 LVDD01 L O	V <sub>LXBB1/2</sub> = 0V o		T <sub>A</sub> = +25°C		0.1	1	μA
LXBB1, LXBB2 Leakage Current	$V_{OUTBB} = 5.5V,$ $V_{INBB} = 5.5V$		T <sub>A</sub> = +85°C		0.2		
LXBB1/2 Current Limit				3.5	4.5	5.5	Α
PMOS On-Resistance	I <sub>LXBB</sub> = 100mA,	per switch			65		mΩ
NMOS On-Resistance	I <sub>LXBB</sub> = 100mA, per switch				55		mΩ

# **BUCK BOOST Electrical Characteristics (continued)**

 $(V_{INBB}$  = +3.7V,  $V_{OUTBB}$  = +3.5V,  $T_{A}$  = -40°C to +85°C, typical values are at  $T_{A}$  = +25°C, unless otherwise noted.) (Note 5)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
Minimum Effective Output Capacitance	0μA < I <sub>OUT</sub> < 2000mA 16		μF		
Turn-On Delay Time	om ENBB asserting to LXBB Switching with bias on 6			μs	
Soft-Start Time	V <sub>OUTBB</sub> = 3.5V, I <sub>OUT</sub> = 10mA		40		μs
POWER-OK COMPARATOR					
Output POK Trip Level	V <sub>OUTBB POK</sub> rising threshold		80		%
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> switches		5		%

## **LDO Electrical Characteristics**

LDO NO.	TYPE	V <sub>OUT</sub> RANGE (V)	STEP SIZE (mV)	I <sub>OUT</sub> (max, mA)	DEFAULT V <sub>OUT</sub> (V)	DEFAULT ON/OFF	INPUT PIN	C <sub>OUT</sub> (µF)
1	NMOS	0.6–2.1875	12.5	600	1.0	Off	INL1	4.7
2	NMOS	0.6–2.1875	12.5	150	1.0	Off	INL1	1
3	NMOS	0.6–2.1875	12.5	450	1.0	Off	INL2	4.7
4	PMOSLV	0.8–3.975	25	300	1.5	Off	INL3	4.7
5	PMOSLV	0.8–3.975	25	300	1.8	Off	INL3	4.7
6	PMOSLV	0.8–3.975	25	150	1.8	Off	INL3	2.2
7	PMOSLV	0.8–3.975	25	300	1.8	Off	INL3	4.7
8	PMOSLV	0.8–3.975	25	150	1.8	Off	INL3	2.2
9	PMOSLV	0.8–3.975	25	150	1.8	Off	INL3	2.2
10	PMOSLS	0.8–3.975	25	300	2.8	Off	INL4	2.2
11	PMOSLS	0.8–3.975	25	150	2.8	Off	INL4	2.2
12	PMOSLS	0.8–3.975	25	300	3.3	Off	INL5	2.2
13	PMOSLS	0.8–3.975	25	300	3.3	Off	INL5	2.2
14	PMOSLS	0.8–3.975	25	150	3.3	Off	INL5	2.2
15	PMOSLS	0.8–3.975	25	150	3.3	Off	INL5	2.2

Note: LDO12 can also be enabled/disabled by external logic inputs, ENL12.

# **LDO1 (600mA NMOS)**

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 4.7 \mu\text{F}, C_{REFBYP} = 100 n\text{F}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CONDIT	TIONS	MIN	TYP	MAX	UNITS
	V <sub>INLx</sub> must be lower than or e	equal to V <sub>SYS</sub>	V <sub>OUT</sub>		V <sub>SYS</sub>	
Input Voltage Range	V <sub>SYS</sub>		2.6		5.5	V
	(Note 7)		1.5			
	Normal mode, no load			2		
Input Supply Current	Low power mode, no load			2		μA
	Shutdown		< 0.1			
	Normal mode, no load			30		
System Supply Current	Low power mode, no load		4		μA	
	Shutdown	Shutdown				]
	Minimum V <sub>OUT</sub> , Lx_VOUT[6:		0.6			
Output Voltage Programming	Maximum V <sub>OUT</sub> , Lx_VOUT[6:0] = 7'h7F			2.1875		V
	Least significant step size			0.0125		]
Output Voltage Accuracy	$V_{SYS} \ge V_{OUT} + 1.5V$ $(V_{SYSMIN} = 2.6V),$ $V_{INLx} = V_{OUT} + 0.3V$ to $V_{SYS}$	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>	-2		+2	%
		Low power mode I <sub>OUT</sub> = 0.1mA to 5mA	-5		+5	70
Maximum Output Current	Normal mode	600				
(Note 8)	Low power mode		5			mA
Lood Domilation	V <sub>SYS</sub> ≥ V <sub>OUT</sub> + 1.5V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>		0.5		%
Load Regulation	(V <sub>SYSMIN</sub> = 2.6V)	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA		0.5		70
	V <sub>SYS</sub> ≥ V <sub>OUT</sub> + 1.5V	Normal mode		0.05		
Line Regulation	$(V_{SYSMIN} = 2.6V),$ $I_{OUT} = 0.1mA$	Low power mode		0.05		%/V
Drangut Valtage	Normal mode, I <sub>OUT</sub> = I <sub>MAX</sub> ,	V <sub>SYS</sub> - V <sub>OUT</sub> = 2.5V		60	150	
Dropout Voltage	$V_{DO} = V_{INLx} - V_{OUT}$	V <sub>SYS</sub> - V <sub>OUT</sub> = 1.5V		100		mV
Output Current Limit	V <sub>OUT</sub> = 90% of	Normal mode		900	1800	mΛ
Oulbul Current Limit		Low power mode		10		mA
Output Capacitance for Stability	DCR < 200mΩ, ESL < 20nH	(Note 9)	2.35	4.7		μF

# LDO1 (600mA NMOS) (continued)

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 4.7 \mu\text{F}, C_{REFBYP} = 100 n\text{F}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CONDIT	IONS	MIN	TYP	MAX	UNITS
	Named	V <sub>SYS</sub> = 2.7V, V <sub>INLx</sub> = 1.2V, V <sub>OUT</sub> = V <sub>OUTMIN</sub>		30		
Output Noise	Normal mode, f = 10Hz to 100kHz, I <sub>OUT</sub> = 10% of I <sub>MAX</sub>	V <sub>SYS</sub> = 2.7V, V <sub>INLx</sub> = 1.8V, V <sub>OUT</sub> = 1.0V		60		μV <sub>RMS</sub>
		$V_{SYS} = V_{INLx} = 5.5V,$ $V_{OUT} = V_{OUTMAX}$		60		
Power Supply Rejection	Normal mode, f = 1kHz, I <sub>OUT</sub>	= 30mA		70		dB
Output Load Transient	Normal mode, $V_{SYS} = 3.7V$ , $V_{INLx} = 1.8V$ , $V_{OUT} = 1.0V$ ,	C <sub>OUT</sub> = 4.7µF		±5		- %
$(\Delta V/V_{OUT})$	I <sub>OUT</sub> = 1mA to ½ x I <sub>MAX</sub> to 1mA, t <sub>RISE</sub> = t <sub>FALL</sub> = 1μs	C <sub>OUT</sub> = 10μF		±3		70
Output line Transient	Normal mode, V <sub>OUT</sub> = 1.0V,	$V_{SYS} = V_{INLx} = 3.7V \text{ to}$ 3.2V to 3.7V		5		- mV
Output Line Transient	I <sub>OUT</sub> = 1mA, t <sub>RISE</sub> = t <sub>FALL</sub> = 5μs	V <sub>SYS</sub> = 3.7V, V <sub>INLx</sub> = 1.8V to 1.5V to 1.8V		5		
Output Startup Ramp Rate	10% to 90%			30		mV/μs
Turn-On Delay Time	From Lx_EN = 1 to output risi 300µs prior to LDO being ena	9		5		μs
Output Overshoot during Startup Overshoot				50		mV
Output Active Discharge Resistance	(Note 10)			100		Ω
Thermal Shutdown	T <sub>J</sub> rising			165		- °C
Thermal Shuldown	T <sub>J</sub> falling			150		
POWER-OK COMPARATOR						
Output POK Trip Level	Rising edge, V <sub>OUT</sub> when V <sub>PC</sub>	oK switches		87.5		%
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> switches			5		%

# **LDO2 (150mA NMOS)**

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu F, C_{OUT} = 1.0 \mu F, C_{REFBYP} = 100 nF, T_A = -40 ^{\circ}C \ to \ +85 ^{\circ}C, unless otherwise noted.) \ (Note 5)$ 

PARAMETER	CONE	DITIONS	MIN	TYP	MAX	UNITS
	V <sub>INLx</sub> must be lower than or	equal to V <sub>SYS</sub>	V <sub>OUT</sub>		V <sub>SYS</sub>	
Input Voltage Range	V <sub>SYS</sub>		2.6		5.5	V
	(Note 7)		1.5			
	Normal mode, no load			2		
Input Supply Current	Low power mode, no load			2		μA
	Shutdown			< 0.1		
	Normal mode, no load			25		
System Supply Current	Low power mode, no load			3		μA
	Shutdown		< 0.1			
	Minimum V <sub>OUT</sub> , Lx_VOUT[		0.6			
Output Voltage Programming	Maximum V <sub>OUT</sub> , Lx_VOUT[6:0] = 7'h7F			2.1875		
	Least significant step size			0.0125		
Output Voltage Accuracy	$V_{SYS} = V_{OUT} + 1.5V$ $(V_{SYSMIN} = 2.6V),$	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>	-2		+2	%
	$V_{INLx} = V_{OUT} + 0.3V$ to $V_{SYS}$	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA	-5		+5	70
Maximum Output Current	Normal mode		150			
(Note 8)	Low power mode		5			mA
Land Danidation	V <sub>SYS</sub> ≥ V <sub>OUT</sub> + 1.5V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>		0.5		
Load Regulation	(V <sub>SYSMIN</sub> = 2.6V)	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA		0.5		%
	V <sub>SYS</sub> ≥ V <sub>OUT</sub> + 1.5V	Normal mode		0.05		
Line Regulation	$(V_{\text{SYSMIN}} = 2.6V),$ $I_{\text{OUT}} = 0.1\text{mA}$	Low power mode		0.05		%/V
	Normal mode,	V <sub>SYS</sub> - V <sub>OUT</sub> = 2.5V		60	150	
Dropout Voltage	$I_{OUT} = I_{MAX},$ $V_{DO} = V_{INLx} - V_{OUT}$	V <sub>SYS</sub> - V <sub>OUT</sub> = 1.5V		100		- mV
Output Current Limit	V <sub>OUT</sub> = 90% of V <sub>OUT</sub>	Normal mode		225	450	- mA
Output Current Limit		Low power mode		10		
Output Capacitance for Stability	DCR < 200mΩ, ESL < 20nF	I (Note 9)	0.5	1.0		μF

# LDO2 (150mA NMOS) (continued)

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 1.0 \mu\text{F}, C_{REFBYP} = 100 n\text{F}, T_A = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CONDI	TIONS	MIN	TYP	MAX	UNITS
		$V_{SYS} = 2.7V,$ $V_{INLx} = 1.2V,$ $V_{OUT} = V_{OUTMIN}$		30		
Output Noise	Normal mode, f = 10Hz to 100kHz, I <sub>OUT</sub> = 10% of I <sub>MAX</sub>	V <sub>SYS</sub> = 2.7V, V <sub>INLx</sub> = 1.8V, V <sub>OUT</sub> = 1.0V		60		μV <sub>RMS</sub>
		$V_{SYS} = V_{INLX} = 5.5V,$ $V_{OUT} = V_{OUTMAX}$		60		
Power Supply Rejection	Normal mode, f = 1kHz, I <sub>OUT</sub>	= 30mA		70		dB
Output Load Transient	Normal mode, V <sub>SYS</sub> = 3.7V, V <sub>INLx</sub> = 1.8V, V <sub>OUT</sub> = 1.0V,	C <sub>OUT</sub> = 1.0μF		±5		- %
(ΔV/V <sub>OUT</sub> )	$I_{OUT}$ = 1mA to ½ x $I_{MAX}$ to 1mA, $t_{RISE}$ = $t_{FALL}$ = 1µs	C <sub>OUT</sub> = 10μF		±3		%
	Normal mode, V <sub>OUT</sub> = 1.0V,	V <sub>SYS</sub> = V <sub>INLx</sub> = 3.7V to 3.2V to 3.7V	5	m\/		
Output Line Transient	I <sub>OUT</sub> = 1mA, t <sub>RISE</sub> = t <sub>FALL</sub> = 5μs	V <sub>SYS</sub> = 3.7V, V <sub>INLx</sub> = 1.8V to 1.5V to 1.8V		5		- mV
Output Startup Ramp Rate	10% to 90%			30		mV/μs
Turn-On Delay Time	From Lx_EN = 1 to output risi 300µs prior to LDO being ena			5		μs
Output Overshoot During Startup Overshoot				50		mV
Output Active Discharge Resistance	(Note 10)	(Note 10)		100		Ω
T <sub>J</sub> rising			165		°C	
Thermal Shutdown	T <sub>J</sub> falling			150		
POWER-OK COMPARATOR						
Output POK Trip Level	Rising edge, V <sub>OUT</sub> when V <sub>PO</sub>	Rising edge, V <sub>OUT</sub> when V <sub>POK</sub> switches				%
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> switches			5		%

# **LDO3 (450mA NMOS)**

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 4.7 \mu\text{F}, C_{REFBYP} = 100 n\text{F}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CONDIT	IONS	MIN	TYP	MAX	UNITS
	V <sub>INLx</sub> must be lower than or ed	ual to V <sub>SYS</sub>	V <sub>OUT</sub>		V <sub>SYS</sub>	
Input Voltage Range	V <sub>SYS</sub>		2.6		5.5	V
	(Note 7)					
	Normal mode, no load			2		
Input Supply Current	Low power mode, no load			2		μA
	Shutdown			< 0.1		
	Normal mode, no load			25		
System Supply Current	Low power mode, no load			3		μA
	Shutdown			< 0.1		
	Minimum V <sub>OUT</sub> , Lx_VOUT[6:0]	= 7'h00		0.6		
Output Voltage Programming	Maximum V <sub>OUT</sub> , Lx_VOUT[6:0	i] = 7'h7F		2.1875		V
	Least significant step size		0.0125			
Output Voltage Accuracy	V <sub>SYS</sub> ≥ V <sub>OUT</sub> + 1.5V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>	-2		+2	- %
		Low power mode I <sub>OUT</sub> = 0.1mA to 5mA	-5		+5	70
Maximum Output Current	Normal mode		450			
(Note 8)	Low power mode		5			mA
Load Decidation	V <sub>SYS</sub> ≥ V <sub>OUT</sub> + 1.5V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>		0.5		%
Load Regulation	(V <sub>SYSMIN</sub> = 2.6V)	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA		0.5		70
	V <sub>SYS</sub> ≥ V <sub>OUT</sub> + 1.5V	Normal mode		0.05		
Line Regulation	$(V_{SYSMIN} = 2.6V),$ $I_{OUT} = 0.1mA$	Low power mode		0.05		%/V
Dropout Voltage	Normal Mode, I <sub>OUT</sub> = I <sub>MAX</sub> ,	V <sub>SYS</sub> - V <sub>OUT</sub> = 2.5V		60	150	
	$V_{DO} = V_{INLx} - V_{OUT}$	V <sub>SYS</sub> - V <sub>OUT</sub> = 1.5V		100		mV
Output Current Limit	V <sub>OUT</sub> = 90% of V <sub>OUT</sub>	Normal mode		675	1350	mA
Output Outroitt Littit	(TARGET)	Low power mode		10		111/1
Output Capacitance for Stability	DCR < 200mΩ, ESL < 20nH (Note 9)		2.35	4.7		μF

# LDO3 (450mA NMOS) (continued)

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu F, C_{OUT} = 1.0 \mu F, C_{REFBYP} = 100 nF, T_A = -40 ^{\circ}C \ to \ +85 ^{\circ}C, unless otherwise noted.) \ (Note 5)$ 

PARAMETER	(	CONDIT	IONS	MIN	TYP	MAX	UNITS
			V <sub>SYS</sub> = 2.7V, V <sub>INLx</sub> = 1.2V, V <sub>OUT</sub> = V <sub>OUTMIN</sub>	30			
Output Noise	Normal mode, $f = 10$ Hz to $100$ kHz, $I_{OUT} = 10\%$ of $I_{MAX}$ $V_{SYS} = 2.7$ V, $V_{INLX} = 1.8$ V, $V_{OUT} = 1.0$ V		V <sub>INLx</sub> = 1.8V,		60		μV <sub>RMS</sub>
			V <sub>SYS</sub> = V <sub>INLx</sub> = 5.5V, V <sub>OUT</sub> = V <sub>OUTMAX</sub>		60		
Power-Supply Rejection	Normal mode, f = 1kHz	., I <sub>OUT</sub> =	: 30mA		70		dB
Output Load Transient	Normal mode, V <sub>SYS</sub> = V <sub>INLx</sub> = 1.8V, V <sub>OUT</sub> = 1		C <sub>OUT</sub> = 4.7μF		±5		0/
(ΔV/V <sub>OUT</sub> )	$OLIT = 1 \text{mA to } \frac{1}{2} \times I_{MAX} \text{ to}$		C <sub>OUT</sub> = 10µF		±3		%
	Normal mode, V <sub>OUT</sub>	V <sub>SYS</sub> = 3.7V	= V <sub>INLx</sub> = 3.7V to 3.2V to	5		- mV	
Output Line Transient	= 1.2V, $I_{OUT}$ = 1mA, $I_{RISE}$ = $I_{FALL}$ = 5 $\mu$ s $I_{SYS}$ = 3.7V, $I_{INLX}$ = 1.8V to 1.5V to 1.8V			5			
Output Startup Ramp Rate	10% to 90%				30		mV/μs
Turn-On Delay Time	From Lx_EN = 1 to out 300µs prior to LDO bei	•			5		μs
Output Overshoot during Startup Overshoot					50		mV
Output Active Discharge Resistance	(Note 10)	(Note 10)			100		Ω
The arms of Chartelesses	T <sub>J</sub> rising		165		- °C		
Thermal Shutdown	T <sub>J</sub> falling			150			
POWER-OK COMPARATOR	POWER-OK COMPARATOR					-	
Output POK Trip Level	Rising edge, V <sub>OUT</sub> whe	en V <sub>POk</sub>	switches		87.5		%
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> swite	ches			5		%

# LDO4, LDO5 and LDO7 (300mA PMOSLV)

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 4.7 \mu\text{F}, C_{REFBYP} = 100 \text{nF}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CON	NDITIONS	MIN	TYP	MAX	UNITS
Input Voltage Range	V <sub>INLx</sub> must be lower than	or equal to V <sub>SYS</sub>	1.7		V <sub>SYS</sub>	V
	Normal mode, no load			15		
Input Supply Current	Low power mode, no load	Low power mode, no load		1.5		μA
	Shutdown	Shutdown		< 0.1		
	Normal mode, no load			3		
System Supply Current	Low power mode, no load	1		0.3		μA
	Shutdown			< 0.1		
	Minimum V <sub>OUT</sub> , Lx_VOU			0.8		
Output Voltage Programming	Maximum VOUT, Lx_VOL	JT[6:0] = 7'h7F		3.975		V
	Least significant step size	)		0.025		
Output Voltage Accuracy	V <sub>INLx</sub> = V <sub>OUT</sub> + 0.3V to	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>	-2		+2	0/
	V <sub>SYS</sub>	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA	-5		+5	%
Maximum Output Current	Normal mode		300	5		^
(Note 8)	Low power mode		5			mA
Lood Downlotion	V - V . 0.2V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>		0.5		0/
Load Regulation	$V_{INLx} = V_{OUT} + 0.3V$	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA		0.5		%
Line Demulation	$V_{INLx} = V_{OUT} + 0.3V$ to	Normal mode		0.05		0/ 0./
Line Regulation	V <sub>SYS</sub> , I <sub>OUT</sub> = 0.1mA	Low power mode		0.05		%/V
December 11	Normal mode, V <sub>SYS</sub> = 3.7V,	V <sub>INLx</sub> = 3.7V		60	150	
Dropout Voltage	$I_{OUT} = I_{MAX},$ $V_{DO} = V_{INLx} - V_{OUT}$	V <sub>INLx</sub> = 1.7V		100		mV
	V <sub>OUT</sub> = 90% of	Normal mode		600	1120	
Output Current Limit	V <sub>OUT</sub> (TARGET)	Low power mode		40		mA
Output Capacitance for Stability	DCR < 200mΩ, ESL < 20nH (Note 9)		2.35	4.7		μF

# LDO4, LDO5 and LDO7 (300mA PMOSLV) (continued)

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 4.7 \mu\text{F}, C_{REFBYP} = 100 \text{nF}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CON	IDITIONS	MIN	TYP	MAX	UNIT
		V <sub>SYS</sub> = V <sub>INLx</sub> = 2.7V, V <sub>OUT</sub> = V <sub>OUTMIN</sub>		25		
Output Noise		V <sub>SYS</sub> = V <sub>INLx</sub> = 2.7V, V <sub>OUT</sub> = 1.0V		30		
	Normal mode, f = 10Hz to 100kHz, I <sub>OUT</sub> = 10% of I <sub>MAX</sub>	$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = 2.0V$		40		μV <sub>RMS</sub>
	1001 1070 OF HWIAX	V <sub>SYS</sub> = V <sub>INLx</sub> = 3.7V, V <sub>OUT</sub> = 3.0V		60		
		V <sub>SYS</sub> = V <sub>INLx</sub> = 5.5V, V <sub>OUT</sub> = V <sub>OUTMAX</sub>		60		
Power Supply Rejection	Normal mode, f = 1kHz, I <sub>0</sub>	<sub>DUT</sub> = 30mA		70		dB
Output Load Transient $V_{SYS} = V_{OUT} = I_{OUT} = I_$	Normal mode, V <sub>SYS</sub> = V <sub>INLx</sub> = 3.7V, V <sub>OUT</sub> = default,	C <sub>OUT</sub> = 4.7μF		±5		- %
	$I_{OUT}$ = 1mA to ½ x $I_{MAX}$ to 1mA, t <sub>RISE</sub> = t <sub>FALL</sub> = 1µs	C <sub>OUT</sub> = 10μF		±3		70
0.4-41: -	Normal mode, V <sub>OUT</sub> = 1.2V,	V <sub>SYS</sub> = V <sub>INLx</sub> = 3.7V to 3.2V to 3.7V	5		>/	
Output Line Transient	$I_{OUT} = 1 \text{mA},$ $t_{RISE} = t_{FALL} = 5 \mu \text{s}$	V <sub>SYS</sub> = 3.7V, V <sub>INLx</sub> = 2.0V to 1.7V to 2.0V				- mV
Output Startup Ramp Rate	10% to 90%			30		mV/μs
Turn-On Delay Time	From Lx_EN = 1 to output 300µs prior to LDO being	t rising, REFBYP enabled > enabled		5		μs
Output Over-shoot during Startup Over-shoot				50		mV
Output Active Discharge Resistance	(Note 10)	(Note 10)		100		Ω
Thermal Shutdown	T <sub>J</sub> rising			+165		°C
memai ShuluUWII	T <sub>J</sub> falling			+150		
POWER-OK COMPARATOR						
Output POK Trip Level	Rising edge, V <sub>OUT</sub> when	V <sub>POK</sub> switches		87.5		%
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> switched	es		3		%

# LDO6, LDO8, and LDO9 (150mA PMOSLV)

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 2.2 \mu\text{F}, C_{REFBYP} = 100 n\text{F}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CONDIT	IONS	MIN	TYP	MAX	UNITS
Input Voltage Range	V <sub>INLx</sub> must be lower than or e	qual to V <sub>SYS</sub>	1.7		V <sub>SYS</sub>	V
	Normal mode, no load			15		
Input Supply Current	Low power mode, no load			1.5		μA
	Shutdown			< 0.1		
	Normal mode, no load			3		
System Supply Current	Low power mode, no load			0.3		μA
	Shutdown			< 0.1		
	Minimum V <sub>OUT</sub> , Lx_VOUT[6:0	0] = 7'h00		0.8		
Output Voltage Programming	Maximum V <sub>OUT</sub> , Lx_VOUT[6:	0] = 7'h7F		3.975		V
	Least significant step size			0.025		
Output Voltage Accuracy	V <sub>INLx</sub> = V <sub>OUT</sub> + 0.3V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>	-2		+2	<b>%</b>
	to V <sub>SYS</sub>	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA,	-5			70
Maximum Output Current	Normal mode		150			
(Note 8)	Low power mode		5			- mA
Land Danislation	V =V +0.0V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>		0.5		
Load Regulation	$V_{INLx} = V_{OUT} + 0.3V$	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA		0.5		- %
Li Bushe	$V_{INLx} = V_{OUT} + 0.3V$ to	Normal mode		0.05		0/ 0/
Line Regulation	V <sub>SYS</sub> , I <sub>OUT</sub> = 0.1mA	Low power mode		0.05		- %/V
Dropout Voltage	Normal mode, V <sub>SYS</sub> = 3.7V, I <sub>OUT</sub> = I <sub>MAX</sub> ,	V <sub>INLx</sub> = 3.7V		60	150	- mV
Diopout voltage	$V_{DO} = V_{INLx} - V_{OUT}$	V <sub>INLx</sub> = 1.7V		100		1110
Output Current Limit	V <sub>OUT</sub> = 90% of	Normal mode		300	560	- mA
Output Ourient Liniit	Vout(target)	Low power mode		40		111/4
Output Capacitance for Stability	DCR < 200mΩ, ESL < 20nH (Note 9)		1.1	2.2		μF

# LDO6, LDO8, and LDO9 (150mA PMOSLV) (continued)

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 2.2 \mu\text{F}, C_{REFBYP} = 100 n\text{F}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CONDIT	TIONS	MIN	TYP	MAX	UNITS
		$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = V_{OUTMIN}$		25		
Output Noise		$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = 1.0V$		30		
	Normal mode, f = 10Hz to 100kHz, I <sub>OUT</sub> = 10% of I <sub>MAX</sub>	$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = 2.0V$		40		μV <sub>RMS</sub>
	Wild	$V_{SYS} = V_{INLx} = 3.7V,$ $V_{OUT} = 3.0V$		60		
		$V_{SYS} = V_{INLx} = 5.5V,$ $V_{OUT} = V_{OUTMAX}$		60		
Power Supply Rejection	Normal mode, f = 1kHz, I <sub>OUT</sub>	= 30mA		70		dB
Output Load Transient	Normal mode,  V <sub>SYS</sub> = V <sub>INLx</sub> = 3.7V,  V <sub>OLIT</sub> = default,	C <sub>OUT</sub> = 2.2μF		±5		- %
$I_{OUT} = 1$	I <sub>OUT</sub> = 1mA to ½ x IMAX to 1mA, t <sub>RISE</sub> = t <sub>FALL</sub> = 1μs	C <sub>OUT</sub> = 10μF		±3		70
Output Line Transient	Normal mode, V <sub>OUT</sub> = 1.2V,	V <sub>SYS</sub> = V <sub>INLx</sub> = 3.7V to 3.2V to 3.7V		5		- mV
Output Line Transient	$I_{OUT} = 1 \text{mA},$ $t_{RISE} = t_{FALL} = 5 \mu \text{s}$	V <sub>SYS</sub> = 3.7V, V <sub>INLx</sub> = 2.0V to 1.7V to 2.0V				
Output Startup Ramp Rate	10% to 90%			30		mV/μs
Turn-On Delay Time	From Lx_EN = 1 to output risi 300µs prior to LDO being ena			5		μs
Output Overshoot During Startup Overshoot				50		mV
Output Active Discharge Resistance	(Note 10)	(Note 10)				Ω
Thermal Shutdown	T <sub>J</sub> rising			+165		- °C
THEIMAI SHUUUWH	T <sub>J</sub> falling			+150		
POWER-OK COMPARATOR						
Output POK Trip Level	Rising edge, V <sub>OUT</sub> when V <sub>PO</sub>	OK switches		87.5		%
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> switches			3		%

# **LDO11, LDO14 and LDO15 (150mA PMOSLS)**

 $(V_{SYS} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 2.2 \mu\text{F}, C_{REFBYP} = 100 \text{nF}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CON	DITIONS	MIN	TYP	MAX	UNITS
Innut Valtage Dange	V <sub>INLx</sub>		2.6		5.5	V
Input Voltage Range	V <sub>SYS</sub>		2.6		5.5	V
	Normal mode, no load	pad		15		
Input Supply Current	Low power mode, no load			4		μA
	Shutdown			< 0.1		
	Normal mode, no load			3.25		
System Supply Current	Low power mode, no load			0.85		μA
	Shutdown			< 0.1		
	Minimum V <sub>OUT</sub> , Lx_VOU	Γ[6:0] = 7'h00		0.8		
Output Voltage Programming	Maximum V <sub>OUT</sub> , Lx_VOU	T[6:0] = 7'h7F		3.975		V
	Least significant step size			0.025		
Output Voltage Accuracy	$V_{INLx} = V_{OUT} + 0.3V$ to	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>	-2		+2	0/
	V <sub>SYS</sub>	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA	-5		+5	- %
Maximum Output Current	Normal mode		150			A
(Note 8)	Low power mode		5			mA
Lond Pogulation	V = V + 0.2V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>		0.5		%
Load Regulation	$V_{INLx} = V_{OUT} + 0.3V$	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA		0.5		70
Line Degulation	$V_{INLx} = V_{OUT} + 0.3V$ to	Normal mode		0.05		%/V
Line Regulation	$V_{SYS}$ , $I_OUT = 0.1mA$	Low power mode		0.05		70/ V
Dropout Voltage	Normal mode, $V_{SYS} = V_{INLx} = 3.7V$ , $I_{OUT} = I_{MAX}$ , $V_{DO} = V_{INLx} - V_{OUT}$			100	200	mV
Output Current Limit	V <sub>OUT</sub> = 90% of	Normal mode		300	560	m: ^
Output Current Limit	V <sub>OUT</sub> (TARGET)	Low power mode		40		mA
Output Capacitance for Stability	DCR < 200mΩ, ESL < 20r	nH (Note 9)	0.6	2.2		μF

# LDO11, LDO14 and LDO15 (150mA PMOSLS) (continued)

 $(V_{SYS} = V_{INLx} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 2.2 \mu\text{F}, C_{REFBYP} = 100 n\text{F}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CON	DITIONS	MIN	TYP	MAX	UNITS
		$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = V_{OUTMIN}$		25		
		$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = 1.0V$		30		
Output Noise	Normal mode, f = 10Hz to 100kHz, I <sub>OUT</sub> = 10% of I <sub>MAX</sub>	$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = 2.0V$		40		μV <sub>RMS</sub>
	OUT 1311 ST INIAX	$V_{SYS} = V_{INLx} = 3.7V,$ $V_{OUT} = 3.0V$		60		
		$V_{SYS} = V_{INLx} = 5.5V,$ $V_{OUT} = V_{OUTMAX}$		60		
Power Supply Rejection	Normal mode, f = 1kHz, I <sub>C</sub>	<sub>OUT</sub> = 30mA		70		dB
Output Load Transient	$(\Delta)/(\Delta)$ $=$ default, $1_{OUT} =$	C <sub>OUT</sub> = 2.2μF		±5		%
$(\Delta V/V_{OUT})$ $1mA$	$t_{RISE} = t_{FALL} = 1 \mu s$	C <sub>OUT</sub> = 10µF		±3		70
Output Line Transient	Normal mode, V <sub>INLx</sub> = 3.7 V <sub>OUT</sub> = default, I <sub>OUT</sub> = 1m			5		mV
Output Startup Ramp Rate	10% to 90%			30		mV/µs
Turn-On Delay Time	From Lx_EN = 1 to output 300µs prior to LDO being	rising, REFBYP enabled > enabled		5		μs
Output Overshoot During Startup Overshoot				50		mV
Output Active Discharge Resistance	(Note 10)			100		Ω
The word Chutdeur	T <sub>J</sub> rising			165		°C
Thermal Shutdown	T <sub>J</sub> falling			150		
POWER-OK COMPARATOR						
Output POK Trip Level	Rising edge, V <sub>OUT</sub> when \	/ <sub>POK</sub> switches		87.5		%
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> switche	S		3		%

# LDO10, LDO12 and LDO13 (300mA PMOSLS)

 $(V_{SYS} = +3.7V, C_{SYS} = 1.0 \mu\text{F}, C_{OUT} = 2.2 \mu\text{F}, C_{REFBYP} = 100 \text{nF}, T_{A} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}, unless otherwise noted.}) \text{ (Note 5)}$ 

PARAMETER	CON	DITIONS	MIN	TYP	MAX	UNITS
Innut Valtage Denge	V <sub>INLx</sub>		2.6		5.5	V
Input Voltage Range	V <sub>SYS</sub>		2.6		5.5	]
	Normal mode, no load			15		
Input Supply Current	Low power mode, no load			4		μA
	Shutdown	utdown				1
	Normal mode, no load			3.25		
System Supply Current	Low power mode, no load			0.85		μA
	Shutdown			< 0.1		]
	Minimum V <sub>OUT</sub> , Lx_VOUT	[6:0] = 7'h00		0.8		
Output Voltage Programming	Maximum V <sub>OUT</sub> , Lx_VOU	Γ[6:0] = 7'h7F		3.975		V
	Least significant step size			0.025		
Output Voltage Accuracy	$V_{INLx} = V_{OUT} + 0.3V$ to	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>	-2		+2	0/
	V <sub>SYS</sub>	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA	-5		+5	5
Maximum Output Current	Normal mode	-	300			- mA
(Note 8)	Low power mode		5	5		
Lord Domitation	V =V +0.2V	Normal mode I <sub>OUT</sub> = 0.1mA to I <sub>MAX</sub>		0.5		0/
Load Regulation	$V_{INLx} = V_{OUT} + 0.3V$	Low power mode I <sub>OUT</sub> = 0.1mA to 5mA		0.5		- %
1: 5 1.6	$V_{INLx} = V_{OUT} + 0.3V$ to	Normal mode		0.05		0/0/
Line Regulation	V <sub>SYS</sub> , I <sub>OUT</sub> = 0.1mA	Low power mode		0.05		%/V
Dropout Voltage	Normal mode, V <sub>SYS</sub> = V <sub>INLx</sub> = 3.7V, I <sub>OUT</sub> = I <sub>MAX</sub> , V <sub>DO</sub> = V <sub>INLx</sub> - V <sub>OUT</sub>			100	200	mV
0.41.0	V <sub>OUT</sub> = 90% of	Normal mode		600	1120	
Output Current Limit	Vout(target)	Low power mode		40		mA
Output Capacitance for Stability	DCR < 200mΩ, ESL < 20nH (Note 9)		0.6	2.2		μF


## LDO10, LDO12 and LDO13 (300mA PMOSLS) (continued)

 $(V_{SYS}$  = +3.7V,  $C_{SYS}$  = 1.0 $\mu$ F,  $C_{OUT}$  = 2.2 $\mu$ F,  $C_{REFBYP}$  = 100nF,  $T_A$  = -40 $^{\circ}$ C to +85 $^{\circ}$ C, unless otherwise noted.) (Note 5)

PARAMETER	CONI	DITIONS	MIN TYP	MAX	UNITS
		$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = V_{OUTMIN}$	25		
Output Noise		$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = 1.0V$	30	30	
	Normal mode, f = 10Hz to 100kHz, I <sub>OUT</sub> = 10% of I <sub>MAX</sub>	$V_{SYS} = V_{INLx} = 2.7V,$ $V_{OUT} = 2.0V$	40		μV <sub>RMS</sub>
	OUT TO ST IMAX	$V_{SYS} = V_{INLx} = 3.7V,$ $V_{OUT} = 3.0V$	60		
		$V_{SYS} = V_{INLx} = 5.5V,$ $V_{OUT} = V_{OUTMAX}$	60		
Power Supply Rejection	Normal mode, f = 1kHz, I <sub>O</sub>	UT = 30mA	70		dB
Output Load Transient (ΔV/V <sub>OUT</sub> )	Normal mode,  V <sub>SYS</sub> = V <sub>INLx</sub> = 3.7V,  V <sub>OUT</sub> = default, I <sub>OUT</sub> =	C <sub>OUT</sub> = 2.2µF	±5		- %
	1mA to ½ x I <sub>MAX</sub> to 1mA, t <sub>RISE</sub> = t <sub>FALL</sub> = 1µs	C <sub>OUT</sub> = 10μF	±3		70
Output Line Transient	Normal mode, V <sub>INLx</sub> = 3.7\ default, I <sub>OUT</sub> = 1mA, t <sub>RISE</sub>		5		mV
Output Startup Ramp Rate	10% to 90%		30		mV/μs
Turn-On Delay Time	From Lx_EN = 1 (or ENL12 REFBYP enabled > 300µs	2 = high) to output rising, prior to LDO being enabled	5		μs
Output Overshoot During Startup Overshoot			50		mV
Output Active Discharge Resistance	(Note 10)		100		Ω
Thermal Shutdown	T <sub>J</sub> rising		+165		°C
Thermal Shuldown	T <sub>J</sub> falling	T <sub>J</sub> falling			
POWER-OK COMPARATOR					
Output POK Trip Level	Rising edge, V <sub>OUT</sub> when V	Rising edge, V <sub>OUT</sub> when V <sub>POK</sub> switches			%
Output POK Hysteresis	V <sub>OUT</sub> when V <sub>POK</sub> switches	3	3		%

- Note 3: Guaranteed by design. Not production tested.
- Note 4: 100% production tested at  $T_A = +25$ °C, limits over the operating range are guaranteed by design.
- **Note 5:** Limits are 100% production tested at T<sub>A</sub> = +25°C. Limits over the operating temperature range are guaranteed through correlation using statistical quality control methods.
- Note 6: The maximum output current spec is not directly tested. Instead, it is guaranteed by LX NMOS current limit test.
- **Note 7:** For NMOS LDOs,  $V_{SYS}$  must be at least 1.5V above  $V_{OUT}$  ( $V_{SYS} \ge V_{OUT} + 1.5V$ ).
- Note 8: The maximum output current is guaranteed by the output voltage accuracy tests.
- **Note 9:** For stability, guaranteed by design and not production tested.
- Note 10: There is an n-channel MOSFET in series with the output active discharge resistance. This NMOS requires V<sub>SYS</sub> > 1.2V to be enhanced.

# **Pin Configurations**




# **Pin Description**

PIN	NAME	FUNCTION
C4	CE	Active-High Chip Enable Input. When CE = high (standby), the I <sup>2</sup> C interface is enabled and regulators are ready to be turned on. When CE = low (shutdown), all regulators are turned off and all Type-O registers are reset to their POR default values.
D5	ENB	Active-High BUCK External Enable Input. An $800k\Omega$ internal pull-down resistance to the GND. If this pin is not used, leave it floating.
E6	ENBB	Active-High BUCK BOOST External Enable Input. An $800k\Omega$ internal pulldown resistance to the GND. If this pin is not used, leave it unconnected.
E4	ENL12	Active-High LDO12 External Enable Input. An $800k\Omega$ internal pulldown resistance to the GND. If this pin is not used, leave it unconnected.
В3	FB_B	BUCK Output Voltage Feedback
E5	FB_BB	BUCK BOOST Output Voltage Feedback
E7	GND	Ground
A1, A2	INB	BUCK Input. Bypass to PGNDB with a 10µF capacitor.
F7, G7	INBB	BUCK BOOST Input

# **Pin Description (continued)**

PIN NAME		FUNCTION		
B4	INL1	Input for LDO1 and 2. Bypass to GND with a 4.7µF capacitor.		
B5	INL2	Input for LDO3. Bypass to GND with a 1µF capacitor.		
C7	INL3	Input for LDO4, 5, 6, 7, 8, and 9. Bypass to GND with a 4.7µF capacitor.		
F2	INL4	Input for LDO10 and 11. Bypass to GND with a 4.7µF capacitor.		
F1	INL5	Input for LDO12, 13, 14, and 15. Bypass to GND with a 4.7µF capacitor.		
E3	IRQB	Interrupt Output. A $100k\Omega$ external pullup resistor to $V_{IO}$ is required.		
B1, B2	LXB	BUCK Switching Node		
F6, G6	LXBB1	BUCK BOOST Switching Node 1		
F4, G4	LXBB2	BUCK BOOST Switching Node 2		
A4	LDO1	LDO1 (600mA NMOS) Output. Bypass to GND with a 4.7µF capacitor.		
C6	LDO2	LDO2 (150mA NMOS) Output. Bypass to GND with a 1µF capacitor.		
A5	LDO3	LDO3 (450mA NMOS) Output. Bypass to GND with a 4.7µF capacitor.		
D7	LDO4	LDO4 (300mA PMOSLV) Output. Bypass to GND with a 4.7µF capacitor.		
B7	LDO5	LDO5 (300mA PMOSLV) Output. Bypass to GND with a 4.7µF capacitor.		
A7	LDO6	LDO6 (150mA PMOSLV) Output. Bypass to GND with a 2.2µF capacitor.		
A6	LDO7	LDO7 (300mA PMOSLV) Output. Bypass to GND with a 4.7µF capacitor.		
B6	LDO8	LDO8 (150mA PMOSLV) Output. Bypass to GND with a 2.2µF capacitor.		
D6	LDO9	LDO9 (150mA PMOSLV) Output. Bypass to GND with a 2.2µF capacitor.		
G1	LDO10	LDO10 (300mA PMOSLS) Output. Bypass to GND with a 2.2µF capacitor.		
G2	LDO11	LDO11 (150mA PMOSLS) Output. Bypass to GND with a 2.2µF capacitor.		
D1	LDO12	LDO12 (300mA PMOSLS) Output. Bypass to GND with a 2.2µF capacitor.		
E1	LDO13	LDO13 (300mA PMOSLS) Output. Bypass to GND with a 2.2µF capacitor.		
E2	LDO14	LDO14 (150mA PMOSLS) Output. Bypass to GND with a 2.2µF capacitor.		
D2	LDO15	LDO15 (150mA PMOSLS) Output. Bypass to GND with a 2.2µF capacitor.		
F3, G3	OUTBB	BUCK BOOST Output		
C1, C2	PGNDB	BUCK Power GND		
F5, G5	PGNDBB	BUCK BOOST Power GND		
C5	REFBYP	LDO Reference Bypass Node. Connect a 0.1µF Cap to GND.		
D4	SCL	I <sup>2</sup> C Clock Input. High Impedance in Off State. A $1.5$ kΩ $\sim$ 2.2kΩ of pullup resistor to VIO is required.		
D3	SDA	I <sup>2</sup> C Data I/O. High Impedance in Off State. A 1.5kΩ–2.2kΩ of pullup resistor to $V_{IO}$ is required.		
A3	SYS	System (Battery) Voltage Input. Bypass to GND with a 1µF capacitor.		
C3	V <sub>IO</sub>	IO Supply Voltage Input. Bypass to GND with a 0.1µF capacitor.		

# **Block Diagram**



## **Detailed Description**

### **Top System Management**

### **System Faults**

The MAX77826 monitors the system for the following faults: global thermal, local thermal shutdown, and undervoltage lockout.

#### **Global Thermal Fault**

The MAX77826 has a centralized thermal protection circuit which monitors temperature on the die. If the die temperature exceeds +165°C (T<sub>SHDN</sub>), a thermal shutdown event initiates, and the MAX77826 enters its global shutdown state.

In addition to the +165°C threshold, there are two additional comparators that trip at +120°C and +140°C. Interrupts are generated in the event the die temperature reaches +120°C or +140°C.

There is a 15°C thermal hysteresis. After the thermal shutdown, if the die temperature reduces by 15°C, the thermal shutdown bus deasserts.

#### **Local Thermal Shutdown**

If any of the BUCK BOOST or LDOs reach the thermal shutdown threshold, the MAX77826 shuts down the corresponding block locally. If the temperature goes below a threshold, that block goes back to normal operation.

#### **Undervoltage Lockout**

When  $V_{SYS}$  falls below  $V_{UVLO\_F}$  (typ 2.05V), the MAX77826 enters its undervoltage lockout (UVLO) mode. UVLO forces the MAX77826 to a dormant state until the source voltage is high enough to allow the MAX77826 to be securely functional. I<sup>2</sup>C does not function and the Type-O register contents are reset to their default values in UVLO mode. UVLO rising threshold is set to 2.5V by an OTP option.

#### Chip Enable (CE)

A logic-high on CE pin puts the MAX77826 into standby mode (enabled). In standby mode, all user registers are accessible through  $I^2C$  so that the host processor can

overwrite the default output voltages of regulators and each regulator can be enabled by either I<sup>2</sup>C or the GPIO input if applicable.

When the CE pin goes high, the MAX77826 turns on the top-level bias circuitry, and it takes typically 85 $\mu$ s to settle. As soon as the top-level bias is ready, BUCK BOOST is ready to be turned on. However, BUCK and LDOs require additional 85 $\mu$ s (typ) for REFBYP to settle. Total, it takes 170 $\mu$ s (85 $\mu$ s + 85 $\mu$ s) for REFBYP to settle from CE = high. In the worst-case scenario, it can take up to 230 $\mu$ s. Once REFBYP is ready, all the regulators are allowed to be tuned on through I2C or the ENx pins. In case the regulars are enabled before the bias circuitry is ready, the regulators require longer time to startup.

When CE pin is pulled low, the MAX77826 goes into shutdown mode (disabled) and turns off all the regulators regardless of ENx pins. This event also resets all Type-O registers to their POR default values.

#### **Immediate Shutdown Events**

The following events initiate immediate shutdown: thermal protection (T $_{\rm J}$  > +165°C), V $_{\rm SYS}$  < V $_{\rm SYS}$  UVLO falling threshold (V $_{\rm UVLO\_F}$ ), V $_{\rm IO}$  < V $_{\rm IO}$  OK threshold (VTH VIO OK)

The events in this category are associated with potentially hazardous system states. Powering down the host processor and resetting all Type-O registers help mitigate any issues that can occur due to these potentially hazardous conditions. Note that the MAX77826 cannot be enabled until the junction temperature drops below +150°C in case thermal protection caused the immediate shutdown.

#### **Operating Mode (OPMD)**

Each regulator (BUCK, BUCK BOOST, and LDO) has independent register bits to control its operating mode. These bits determines on/off operation during initial startup, output enable control, and sleep mode operation based on the enable control logic of each regulator. The POR default values of output enable bits (x\_EN) are 0 (output off).

### **Enable Control Logic1**

BUCK, BUCK BOOST, and LDO12 have independent I<sup>2</sup>C enable bits and dedicated GPIO enable pins (ENB, ENBB, and ENL12). As shown in Table 1, regulators can be turned on/off by ENx or I<sup>2</sup>C control bits.

### **Enable Control Logic 2**

LDO1-LDO11 and LDO13-LDO15 have independent I<sup>2</sup>C enable bits. As shown in Table 2, regulators can be turned on/off by the I2C control bits.

### **Reset Conditions**

### **System Reset**

When V<sub>SYS</sub> voltage drops below its POR threshold (≈1.55V), all Type-S1 registers are reset to their POR default values.

#### **Off Reset**

Off reset occurs by any power-off events. This condition resets all Type-O registers to their POR default values.

**Table 1. Enable Control Logic 1 Truth Table** 

CE	ENx	B_EN BB_EN L12_EN	B_LPM L12_LPM	OPERATING MODE
Low	х	х	х	Device off
High	Low	0	х	Output off
High	High	х	1	Output on (low power mode*)
High	High	х	0	Output on
High	х	1	1	Output on (low power mode*)
High	х	1	0	Output on

<sup>\*</sup>The BUCK BOOST regulator does not have a low power mode.

# **Table 2. Enable Control Logic 2 Truth Table**

CE Lx_EN		Lx_LPM OPERATING MO	
Low	Х	х	Device off
High	0	х	Output off
High	1	1	Output on (low power mode)
High	1	0	Output on

#### **Interrupt and Mask**

IRQB pin is used to indicate to the host processor that the status on the MAX77826 has changed. IRQB signal is asserted whenever one or more interrupts are triggered. The host processor reads the interrupt source register (ADDR 0x00) and the interrupt registers as indicated by the interrupt source register in order to see the cause of interrupt event.

Each interrupt register can be read at a time. IRQB pin goes high (cleared) as soon as the read sequence finishes. If an interrupt is captured during the read sequence, IRQB pin is held low. Note that the interrupt source register is cleared when the corresponding interrupt registers are read by the host processor.

Each interrupt can be masked (disabled) by setting the corresponding interrupt mask register bit. In case an interrupt mask bit is set (masked), the corresponding interrupt bit is not supposed to be set even when the interrupt condition is met. As a result, the IRQB pin stays high for this event. If the mask bit is cleared for an active interrupt, the corresponding interrupt bit is set to pull the IRQB pin low.




Figure 1. Enable Control Logic 1




Figure 2. Enable Control Logic 2

### **BUCK Regulator**

The MAX77826 includes a 3A current-mode BUCK regulator. In normal operation, BUCK consumes only 22µA quiescent current. In low power mode, the quiescent current is decreased to 8µA with reduced load capability.

The summary of features is:

- 3A of maximum output current rating
- 2.6V to 5.5V input voltage range
- Output voltage range from 0.50V to 1.80V in 6.25mV steps
- ±1% (typ) output voltage DC accuracy
- 2MHz (typ) switching frequency
- Automatic SKIP/PWM or forced PWM modes
- > 90% peak efficiency
- Programmable slew rate for increasing output voltage settings

#### **Operating Mode Control**

The operating mode bit resides in the top level that controls the enable/disable state of BUCK through the B\_EN register and also controls the operating mode (low power or normal mode) through the B\_LPM register.

### **SKIP/Forced PWM Operation**

In normal operating mode, BUCK automatically transitions from SKIP mode to fixed frequency operation as load current increases. For operating modes where lowest output ripple is required, forced PWM switching behavior can be enabled by writing 1 to B\_FPWM bit.

### **Low Power Mode Operation**

In low power mode, the quiescent current is reduced from  $22\mu A$  to  $8\mu A$ . The output current is limited to 10mA. It is not recommended to adjust the output voltage in low power mode. The regulator does not automatically enter/exit low power mode. The host processor needs to control low power mode operation in times of known low power states through the  $I^2C$  serial interface.

#### Startup and Soft-Start

When starting up BUCK regulator, the bias circuitry must be enabled and provided with adequate time to settle. The bias circuitry is guaranteed to settle within 250µs, at which time, the BUCK regulators' power-up sequences can commence. Note that attempting to implement a power-up sequence before BIASOK signal is generated results in all enabled regulators starting up at the same time.

The BUCK regulator supports starting into a prebiased output. For example, if the output capacitor has an initial voltage of 0.4V when the regulator is enabled, the regulator gradually increases the capacitor voltage to the required target voltage such as 1.0V. This is unlike other regulators without the start into prebias feature in which they can force the output capacitor voltage to 0V before the soft-start ramp begins.

The BUCK regulator has a soft-start rate of 14mV/ $\mu$ s. The controlled soft-start rate and BUCK regulator current limit (I<sub>LIMP</sub>) limit the input inrush current to the output capacitor (I<sub>INRUSH</sub>). I<sub>INRUSH</sub> = min (I<sub>LIMP</sub> and C<sub>OUT</sub> x dv/dt). Note that the input current of BUCK regulator is lower than the inrush current to the output capacitor by the ratio of output to input voltage.

#### **Output Voltage Setting**

The output voltage is programmable from 0.50V to 1.80V in 6.25mV steps to allow fine adjustment to the processor supply voltage under light load conditions to minimize power loss within the processor. The default output voltage is set by an OTP option at the factory. The default output voltage can be overwritten by changing the contents in B\_VOUT[7:0] register prior to enabling the regulator. The output voltage can also be adjusted during normal operation.

### **Changing Output Voltage While Operating**

In a typical smartphone or tablet application, there are several power domains in which the operating frequency of the processor increases or decreases (DVFS). When the operating frequency needs to be changed, it is expected that BUCK regulator responds to a command to change the output voltages to new target values quickly. The high peak current limit, coupled with low inductance and small output capacitance, allows the BUCK regulator to respond to a positive step change in output voltage and settle to the new target value quickly. The BUCK regulator provides programmable ramp-up slew rates to accommodate different requirements.

For a negative step change in output voltage, the settling time is not critical. In forced PWM mode (either B\_FPWM bit or B\_FSRAD bit is enabled), the negative inductor current through NMOS discharges energy from the output capacitor to help the output voltage decrease to the new target value faster. In skip mode, negative inductor current is not allowed so that the output voltage settling time is dependent on the load current and the output capacitance.

### **Output Voltage Slew Rate Control**

The BUCK regulator supports programmable slew rate control feature when increasing and decreasing the output voltage. The ramp-up slew rate can be set to  $12.5 \text{mV/}\mu\text{s}$ ,  $25 \text{mV/}\mu\text{s}$ ,  $50 \text{mV/}\mu\text{s}$  or  $100 \text{mV/}\mu\text{s}$  independently through the B\_RAMP[1:0] bits, while the ramp-down slew rate is fixed to  $6.25 \text{mV/}\mu\text{s}$ .

### **Output Active Discharge Resistance**

BUCK provides an internal  $100\Omega$  resistor for output active discharge function. If the active discharge function is enabled (B\_AD = 1), the internal resistor discharges the energy stored in the output capacitor to GND whenever the regulator is disabled.

Either the regulator remains enabled or the active discharge function is disabled (B\_AD = 0), the internal resistor is disconnected from the output. If the active discharge function is disabled, the output voltage decays at a rate that is determined by the output capacitance and the load current when the regulator is turned off.

#### **Inductor Selection**

BUCK is optimized for a  $0.47\mu H$  inductor. The lower the inductor DCR, the higher BUCK efficiency is. Users need to trade off inductor size with DCR value and choose a suitable inductor for BUCK.

### **Input Capacitor Selection**

The input capacitor,  $C_{IN}$ , reduces the current peaks drawn from the battery or input power source and reduces switching noise in the IC. The impedance of  $C_{IN}$  at the switching frequency should be kept very low. Ceramic capacitors with X5R or X7R dielectrics are highly rec-

ommended due to their small size, low ESR, and small temperature coefficients. For most applications, a  $10\mu F$  capacitor is sufficient.

### **Output Capacitor Selection**

The output capacitor,  $C_{OUT}$ , is required to keep the output voltage ripple small and to ensure regulation loop stability.  $C_{OUT}$  must have low impedance at the switching frequency. Ceramic capacitors with X5R or X7R dielectric are highly recommended due to their small size, low ESR, and small temperature coefficients. Due to the unique feedback network, the output capacitance can be very low. The recommended minimum output capacitance for BUCK is  $22\mu F$ .

### **BUCK BOOST Regulator**

The MAX77826 BUCK BOOST regulator utilizes a four-switch H-bridge configuration to realize BUCK, BUCK BOOST, and BOOST operating modes. In this way, this topology maintains output voltage regulation when the input voltage is greater than, equal to, or less than the output voltage. The MAX77826 BUCK BOOST is ideal in Li-ion battery powered applications, providing 2.6V to 4.1875V output voltage and up to 2A output current across the input voltage range. High switching frequency and a unique control algorithm allow the smallest solution size, low output noise, and highest efficiency across a wide input voltage and output current range.

The MAX77826 BUCK BOOST regulator typically generates a 3.50V output voltage. The input current limit is set to 3.5A (typ) to guarantee delivery of 2A at 3.50V from 3.0V input. Internal soft-start limits the inrush current at startup.

Table 3. Suggested Inductors for BUCK

MANUFACTURER	SERIES	NOMINAL INDUCTANCE (µH)	DC RESISTANCE (typ, mΩ)	CURRENT RATING (A) -30% (△L/L)	CURRENT RATING (A) ΔT = +40°C RISE	DIMENSIONS L x W x H (mm)
Semco	CIGT201610G MR47MNE	0.47	35	4.0	2.9	2.0 x 1.6 x 1.0
Toko	DFE201610-H -R47N	0.47	37	3.5	3.5	2.0 x 1.6 x 1.0




Figure 3. BUCK BOOST Block Diagram

### **H-Bridge Controller**

The H-bridge architecture operates at 3MHz fixed frequency with a pulse width modulated (PWM), current mode control scheme. This topology is in a cascade of a BOOST regulator and a BUCK regulator using a single inductor and output capacitor. BUCK, BUCK BOOST, and BOOST stages are 100% synchronous for highest efficiency in portable applications.

There are three phases implemented with the H-bridge switch topology, as shown in Figure 4:

Φ1 switch period (Phase 1: P1 = on, N2 = on) stores energy in the inductor, ramping up the inductor current at a rate proportional to the input voltage divided by inductance;  $V_{INRB/I}$ .

 $\Phi$ 2 switch period (Phase 2: P1 = on, N3 = on) ramps the inductor current up or down, depending on the differential voltage across the inductor, divided by inductance;  $\pm (V_{INBB} - V_{OUTBB})/L$ .

 $\Phi$ 3 switch period (Phase 3: N1 = on, N3 = on) ramps down the inductor current at a rate proportional to the output voltage divided by inductance, -V<sub>OUTBB</sub>/L.




Figure 4. BUCK BOOST Switching Intervals

2-Phase BUCK topology is utilized when  $V_{INBB} > V_{OUTBB}$ . A switching cycle is completed in one clock periods. Switch period  $\Phi 2$  is followed by switch period  $\Phi 3$ , resulting in an inductor current waveform similar to Figure 5.

3-Phase BUCK topology is utilized when V<sub>INBB</sub> > V<sub>OUTBB</sub> and 2-Phase BUCK cannot support V<sub>O</sub>. Switch period is:  $\Phi 1 \rightarrow \Phi 2 \rightarrow \Phi 3$ . Switch period  $\Phi 1$  is fixed. This results in an inductor current waveform similar to Figure 6.

2-Phase BOOST topology is utilized when  $V_{INBB}$  <  $V_{OUTBB}$ . A switching cycle is completed in one clock periods. Switch period  $\Phi 1$  is followed by switch period  $\Phi 2$ , resulting in an inductor current waveform similar to Figure 7.

3-Phase BOOST topology is utilized when  $V_{INBB}$  <  $V_{OUTBB}$  and 2-Phase BOOST cannot support  $V_O$ . Switch period is:  $\Phi 1 \rightarrow \Phi 2 \rightarrow \Phi 3$ . Switch period  $\Phi 3$  is fixed. This results in an inductor current waveform similar to Figure 8.

#### **Inductor Selection**

BUCK BOOST is optimized for a 1µH inductor. The lower the inductor DCR, the higher BUCK BOOST efficiency is.




Figure 5. 2-Phase BUCK Switching Current Waveforms




Figure 6. 3-Phase BUCK Switching Current Waveforms When V<sub>INBB</sub> > V<sub>OUTBB</sub>

Users need to trade off inductor size with DCR value and choose a suitable inductor for BUCK BOOST.

The input capacitor,  $C_{IN}$ , reduces the current peaks drawn from the battery or input power source and reduces switching noise in the IC. The impedance of  $C_{IN}$  at the switching frequency should be kept very low. Ceramic capacitors with X5R or X7R dielectrics are highly recommended due to their small size, low ESR, and small temperature coefficients. For most applications, a  $10\mu F$  capacitor is sufficient.

### **Output Capacitor Selection**

The output capacitor,  $C_{OUT}$ , is required to keep the output voltage ripple small and to ensure regulation loop stability.  $C_{OUT}$  must have low impedance at the switching frequency. Ceramic capacitors with X5R or X7R dielectric are highly recommended due to their small size, low ESR, and small temperature coefficients. Due to the unique feedback network, the output capacitance can be very low. The recommended minimum output capacitance for BUCK BOOST is  $47\mu F$ .




Figure 7. 2-Phase BOOST Mode Switching Current Waveform




Figure 8. BOOST Mode Switching Current Waveforms When  $V_{INBB} < V_{OUTBB}$ 

# Table 4. Suggested Inductors for BUCK BOOST

MANUFACTURER	SERIES	NOMINAL INDUCTANCE (µH)	DC RESISTANCE (typ, mΩ)	CURRENT RATING (A) -30% (∆L/L)	CURRENT RATING (A) ∆T = +40°C RISE	DIMENSIONS L x W x H (mm)
TDK	TFM201610GHM -1R0MTAA	1.0	50	3.8	3.0	2.0 x 1.6 x 1.0

### **Linear Regulators**

The MAX77826 provides 15 low dropout linear regulators including 3 NMOS LDOs, 6 PMOSLV LDOs, and 6 PMOSLS LDOs. Each of these regulators draws  $27\mu A/18\mu A$  (NMOS/PMOS) of quiescent current in normal operating mode and <  $5\mu A$  in low power mode. PMOSLV LDOs allow input voltages as low as 1.7V for optimized system efficiency.

All regulators can be operated in low power mode that supports up to 5mA of maximum load current.

The summary of features is:

- 3 NMOS LDOs (V<sub>OUT</sub> range: 0.6V to 2.1875V with 12.5mV step)
  - 1 x 150mA
  - 1 x 450mA
  - 1 x 600mA
- 6 PMOSLV LDOs (V<sub>OUT</sub> range: 0.8V to 3.975V with 25mV step)
  - 3 x 150mA
  - 3 x 300mA
- 6 PMOSLS LDOs (V<sub>OUT</sub> range: 0.8V to 3.975V with 25mV step)
  - 3 x 150mA
  - 3 x 300mA
  - ±1.5% typical Output Voltage DC Accuracy
  - 70dB PSRR at 1kHz

#### **LDO Reference**

The MAX77826 has a single LDOREF bias rail. LDOREF is enabled or disabled along with the central bias block (SBIA) so that LDOREF is ready whenever any LDO turns on. It has a very low quiescent current of 2µA typical.

#### **Operating Mode Control**

The operation mode bits for each LDO reside in the top level that controls the enable/disable state for each LDO through the Lx\_EN signal and also controls the operation modes (low power or normal mode) for each LDO through the Lx\_LPM signal.

#### **Low Power Mode**

In low power mode, the quiescent current of each LDO is reduced from  $27\mu A/18\mu A$  (NMOS/PMOS) to less than  $5\mu A.$  The output current of each LDO is limited to 5mA if operating in low power mode. Each LDO can be individually enabled to operate in low power mode.

### **Soft-Start and Dynamic Voltage Change**

When a regulator is enabled, the output voltage ramps to the final voltage at the slew rate of  $30\text{mV/}\mu\text{s}$ . The  $30\text{mV/}\mu\text{s}$  ramp rate results in around 30mA inrush current with a  $1.0\mu\text{F}$  output capacitor under no load condition. For a 1.8V LDO ramping from 0V, the output voltage regulation is achieved within  $60\mu\text{s}$ . The soft-start ramp rate is also the rate of change at the output when switching dynamically between two output voltages without disabling. The soft-start circuitry of LDOs supports starting into a prebiased output.

### **Output Active Discharge**

Each LDO provides an internal  $100\Omega$  resistor for output active discharge function. If the active discharge function is enabled (Lx\_AD = 1), the internal resistor discharges the energy stored in the output capacitor to GND whenever the regulator is disabled.

Either the regulator remains enabled or the active discharge function is disabled ( $Lx\_AD = 0$ ), the internal resistor is disconnected from the output. If the active discharge function is disabled, the output voltage decays at a rate that is determined by the output capacitance and the load current when the regulator is turned off.

#### **Thermal Considerations**

In most applications, the MAX77826 does not dissipate much heat because of its high efficiency. However, in applications where the MAX77826 runs with heavy loads at high ambient temperature, the junction temperature can exceed the maximum operating temperature. In case the junction temperature reaches approximately +165°C, the thermal overload protection triggers. The maximum power dissipation of the MAX77826 depends on the thermal resistance of the IC package and PCB. The power dissipated in the device is:

$$P_D = P_{OUT} x (1/\eta - 1)$$

where  $\eta$  is the efficiency of the regulator and  $P_{OUT}$  is the output power delivered to the load.

The maximum allowed power dissipation is:

$$P_{MAX} = (T_{JMAX} - T_A)/\theta_{JA}$$

 $T_{JMAX}$  -  $T_A$  is the temperature difference between the maximum rated junction temperature and the ambient temperature,  $\theta_{JA}$  is the thermal resistance between the junction and the ambient.

### **Serial Interface**

The I<sup>2</sup>C-compatible, 2-wire serial interface is used for regulator on/off control, setting output voltages, and other functions. See the Register Map for details.

The I<sup>2</sup>C serial bus consists of a bidirectional serial-data line (SDA) and a serial clock (SCL). I2C is an open-drain bus. SDA and SCL require pullup resistors (500 $\Omega$  or greater). Optional  $24\Omega$  resistors in series with SDA and SCL help to protect the device inputs from high voltage spikes on the bus lines. Series resistors also minimize crosstalk and undershoot on bus lines.

### **System Configuration**

I2C bus is a multimaster bus. The maximum number of devices that can attach to the bus is only limited by bus capacitance.

The figure above shows an example of a typical I<sup>2</sup>C system. A device on I<sup>2</sup>C bus that sends data to the bus in called a transmitter. A device that receives data from the bus is called a receiver. The device that initiates a data transfer and generates SCL clock signals to control the data transfer is a master. Any device that is addressed by the master is considered a slave. When the MAX77826 I<sup>2</sup>C-compatible interface is operating in normal mode, it is a slave on I2C bus, and it can be both a transmitter and a receiver.

#### **Bit Transfer**

One data bit transfers for each SCL clock cycle. The data on SDA must remain stable during the high portion of SCL clock pulse. Changes in SDA while SCL is high are control signals (START and STOP conditions).

### **START and STOP Conditions**

When the I<sup>2</sup>C serial interface is inactive, SDA and SCL idle high. A master device initiates communication by issuing a START condition. A START condition is a highto-low transition on SDA with SCL high. A STOP condition is a low-to-high transition on SDA, while SCL is high.

A START condition from the master signals the beginning of a transmission to the MAX77826. The master terminates transmission by issuing a NOT ACKNOWLEDGE followed by a STOP condition.

A STOP condition frees the bus. To issue a series of commands to the slave, the master can issue REPEATED START (Sr) commands instead of a STOP command to maintain control of the bus. In general, a REPEATED START command is functionally equivalent to a regular START command.

When a STOP condition or incorrect address is detected. the MAX77826 internally disconnects SCL from the I2C serial interface until the next START condition, minimizing digital noise and feedthrough.




Figure 9. Functional Logic Diagram for Communications Controller




Figure 10. I<sup>2</sup>C Bit Transfer




Figure 11. START and STOP Conditions

### **Acknowledge**

Both the I<sup>2</sup>C bus master and MAX77826 (slave) generate acknowledge bits when receiving data. The acknowledge bit is the last bit of each 9-bit data packet. To generate an ACKNOWLEDGE (A), the receiving device must pull SDA low before the rising edge of the acknowledge-related clock pulse (ninth pulse) and keep it low during the high period of the clock pulse. To generate a NOT-ACKNOWLEDGE (nA). the receiving device allows SDA to be pulled high before the rising edge of the acknowledge-related clock pulse and leaves it high during the high period of the clock pulse.

Monitoring the acknowledge bits allows for detection of unsuccessful data transfers. An unsuccessful data transfer occurs if a receiving device is busy or if a system fault has occurred. In the event of an unsuccessful data transfer, the bus master should reattempt communication at a later time.

#### **Slave Address**

The I<sup>2</sup>C slave address of the MAX77826 is shown in Table 5.

In general, the clock signal generation for the I<sup>2</sup>C bus is the responsibility of the master device. The I2C specification allows slow slave devices to alter the clock signal by holding down the clock line. The process in which a slave device holds down the clock line is typically called clock stretching. The MAX77826 does not use any form of clock stretching to hold down the clock line.

### **General Call Address**

The MAX77826 does not implement I2C specification general call address. If the MAX77826 sees the general call address (00000000b), it does not issue an ACKNOWLEDGE (A).

## **Table 5. Power Management Slave** Address

SLAVE	SLAVE	SLAVE	
ADDRESS	ADDRESS	ADDRESS	
(7 bit)	(Write)	(Read)	
110 0000	0xC0 (1100 0000)		

### **Communication Speed**

The MAX77826 provides an I<sup>2</sup>C 3.0-compatible (3.4MHz) serial interface.

- I<sup>2</sup>C revision 3-compatible serial communications channel
  - 0Hz to 100kHz (standard mode)
  - 0Hz to 400kHz (fast mode)
  - 0Hz to 1MHz (fast mode plus)
  - 0Hz to 3.4MHz (high-speed mode)
  - Does not utilize I<sup>2</sup>C clock stretching

Operating in standard mode, fast mode and fast mode plus do not require any special protocols. The main consideration when changing the bus speed through this range is the combination of the bus capacitance and pullup resistors. Higher time constants created by the bus capacitance and pullup resistance (C x R) slow the bus operation. Therefore, when increasing bus speeds the pullup resistance must be decreased to maintain a reasonable time constant. Refer to the Pullup Resistor Sizing section of I<sup>2</sup>C revision 3.0 specification for detailed guidance on the pullup resistor selection. In general for bus capacitances of 200pF, a 100kHz bus needs 5.6kΩ pullup resistors, a 400kHz bus needs about a 1.5kΩ pullup resistors, and a 1MHz bus needs  $680\Omega$  pullup resistors. Note that the pullup resistor dissipates power when the opendrain bus is low. The lower the value of the pullup resistor, the higher the power dissipation is (V2/R).

Operating in high-speed mode requires some special considerations. For the full list of considerations, refer to the I2C 3.0 specification. The major considerations with respect to the MAX77826 are:

- The I<sup>2</sup>C bus master uses current source pullups to shorten the signal rise times.
- The I<sup>2</sup>C slave must use a different set of input filters on its SDA and SCL lines to accommodate for the higher bus speed.
- The communication protocols need to utilize the highspeed master code.




Figure 12. Slave Address Byte Example for Power Block

At power-up and after each STOP condition, the MAX77826 inputs filters are set for standard mode, fast mode, or fast mode plus (i.e., 0Hz to 1MHz). To switch the input filters for high-speed mode, use the high-speed master code protocols that are described in <u>Communication Protocols</u> section.

#### **Communication Protocols**

The MAX77826 supports both writing and reading from its registers. Table **TBD** shows the I<sup>2</sup>C communication protocols for each functional block. The power block uses the same communications protocols.

### Writing to a Single Register

<u>Figure 13</u> shows the protocol for the I<sup>2</sup>C master device to write one byte of data to the MAX77826. This protocol is the same as the SMBus specification's write byte protocol. The write byte protocol is as follows:

- 1) The master sends a START command (S).
- 2) The master sends the 7-bit slave address followed by a write bit  $(R/\overline{W} = 0)$ .
- 3) The addressed slave asserts an ACKNOWLEDGE (A) by pulling SDA low.
- 4) The master sends an 8-bit register pointer.

- 5) The slave acknowledges the register pointer.
- 6) The master sends a data byte.
- 7) The slave updates with the new data
- 8) The slave acknowledges or does not acknowledges the data byte. The next rising edge on SDA loads the data byte into its target register and the data becomes active.
- 9) The master sends a STOP condition (P) or a RE-PEATED START condition (Sr). Issuing a P ensures that the bus input filters are set for 1MHz or slower operation. Issuing a REPEATED START (Sr) leaves the bus input filters in their current state.

### **Writing to Sequential Registers**

<u>Figure 14</u> shows the protocol for writing to a sequential registers. This protocol is similar to the write byte protocol, except the master continues to write after it receives the first byte of data. When the master is done writing, it issues a STOP or REPEATED START. The writing to sequential registers protocol is as follows:

- The master sends a START command (S).
- 2) The master sends the 7-bit slave address followed by a write bit  $(R/\overline{W} = 0)$ .




Figure 13. Writing to a Single Register with Write Byte Protocol

- The addressed slave asserts an ACKNOWLEDGE (A) by pulling SDA LOW.
- 4) The master sends an 8-bit register pointer.
- 5) The slave acknowledges the register pointer.
- 6) The master sends a data byte.
- 7) The slave acknowledges the data byte. The next rising edge on SDA loads the data byte into its target register, and the data becomes active.
- 8) Steps 6 and 7 are repeated as many times as the master requires.
- During the last acknowledge related clock pulse, the master can issue an ACKNOWLEDGE (A) or a NOT ACKNOWLEDGE (nA).
- 10) The master sends a STOP condition (P) or a RE-PEATED START condition (Sr). Issuing a P ensures that the bus input filters are set for 1MHz or slower operation. Issuing a REPEATED START (Sr) leaves the bus input filters in their current state.




Figure 14. Writing to Sequential Registers X to N

#### Writing Multiple Bytes using Register-Data Pairs

Figure 15 shows the protocol for I2C master device to write multiple bytes to the MAX77826 using register-data pairs. This protocol allows I2C master device to address the slave only once and then send data to multiple registers in a random order. Registers can be written continuously until the master issues a STOP condition. The multiple byte register-data pair protocol is as follows:

- 1) The master sends a START command.
- 2) The master sends the 7-bit slave address followed by a write bit.
- 3) The addressed slave asserts an ACKNOWLEDGE (A) by pulling SDA low.

- 4) The master sends an 8-bit register pointer.
- 5) The slave acknowledges the register pointer.
- 6) The master sends a data byte.
- 7) The slave acknowledges the data byte. The next rising edge on SDA loads the data byte into its target register and the data becomes active.
- 8) Steps 4 to 7 are repeated as many times as the master requires.
- 9) The master sends a STOP condition. During the rising edge of the stop related SDA edge, the data byte that was previously written is loaded into the target register and becomes active.




Figure 15. Writing to Multiple Registers with Multiple Byte Register-Data Pairs Protocol

#### Reading from a Single Register

The I<sup>2</sup>C master device reads one byte of data to the MAX77826. This protocol is the same as SMBus specification's read byte protocol. The read byte protocol is as follows:

- 1) The master sends a START command (S).
- 2) The master sends the 7-bit slave address followed by a write bit  $(R/\overline{W} = 0)$ .
- 3) The addressed slave asserts an ACKNOWLEDGE (A) by pulling SDA low.
- 4) The master sends an 8-bit register pointer.
- 5) The slave acknowledges the register pointer.
- 6) The master sends a REPEATED START command (Sr).
- 7) The master sends the 7-bit slave address followed by a read bit  $(R/\overline{W} = 1)$ .
- 8) The addressed slave asserts an ACKNOWLEDGE (A) by pulling SDA low.
- The addressed slave places 8 bit of data on the bus from the location specified by the register pointer.
- 10) The master issues a NOT ACKNOWLEDGE (nA).
- 11) The master sends a STOP condition (P) or a RE-PEATED START condition (Sr). Issuing a P ensures that the bus input filters are set for 1MHz or slower operation. Issuing a REPEATED START (Sr) leaves the bus input filters in their current state.

Note that every time MAX77826 receives a STOP, its register pointer is set to 0x00. If reading register 0x00 after a STOP has been issued, steps 1 to 6 in the above algorithm can be skipped.

#### **Reading from Sequential Registers**

Figure 16 shows the protocol for reading from sequential registers. This protocol is similar to the read byte protocol except the master issues an ACKNOWLEDGE (A) to signal the slave that it wants more data. When the master has all the data it requires, it issues a NOT ACKNOWLEDGE (nA) and a STOP (P) to end the transmission. The continuous read from sequential registers protocol is as follows:

- 1) The master sends a START command (S).
- 2) The master sends the 7-bit slave address followed by a write bit  $(R/\overline{W} = 0)$ .
- The addressed slave asserts an ACKNOWLEDGE (A) by pulling SDA LOW.

- 4) The master sends an 8-bit register pointer.
- 5) The slave acknowledges the register pointer.
- 6) The master sends a REPEATED START command (Sr).
- 7) The master sends the 7-bit slave address followed by a read bit  $(R/\overline{W} = 1)$ .
- 8) The addressed slave asserts an ACKNOWLEDGE (A) by pulling SDA low.
- 9) The addressed slave places 8 bit of data on the bus from the location specified by the register pointer.
- 10) The master issues an ACKNOWLEDGE (A) signaling the slave that it wishes to receive more data.
- 11) Steps 9 to 10 are repeated as many times as the master requires. Following the last byte of data, the master must issue a NOT ACKNOWLEDGE (nA) to signal that it wishes to stop receiving data.
- 12) The master sends a STOP condition (P) or a RE-PEATED START condition (Sr). Issuing a STOP (P) ensures that the bus input filters are set for 1MHz or slower operation. Issuing a REPEATED START (Sr) leaves the bus input filters in their current state.

Note that every time the MAX77826 receives a STOP its register pointer is set to 0x00. If reading register 0x00 after a STOP has been issued, steps 1 to 6 in the above algorithm can be skipped.

#### **Engaging HS-Mode for Operation up to 3.4MHz**

<u>Figure 17</u> shows the protocol for engaging HS mode operation. HS mode operation allows for a bus operating speed up to 3.4MHz. The engaging HS mode protocol is as follows:

- Begin the protocol while operating at a bus speed of 1MHz or lower.
- 2) The master sends a START command (S).
- The master sends the 8-bit master code of 00001xxxb where xxxb are don't care bits.
- The addressed slave issues a NOT ACKNOWL-EDGE (nA).
- 5) The master may now increase its bus speed up to 3.4MHz and issue any read/write operation.
- 6) The master may continue to issue high-speed read/ write operations until a STOP (P) is issued. Issuing a STOP (P) ensures that the bus input filters are set for 1MHz or slower operation. After a STOP has been issued, steps 1 to 6 in the above algorithm may be skipped.




Figure 16. Reading Continuously from Sequential Registers with X to N




Figure 17. Engaging HS Mode

#### **PMIC Registers**

#### **Register Reset Conditions**

**Type-S1:** Registers are reset when V<sub>SYS</sub> < POR (≈1.55V)

**Type-O:** Registers are reset when  $V_{SYS} < V_{UVLO} OR V_{IO} < V_{TH_VIO_OK} OR CE = LOW$ 

MAX77826

Register Map I<sup>2</sup>C Slave Address (W/R): 0xC0/0xC1

RESET	00×0	00×0	00×0	00×0	00×0	0×07	0x03	0xFF	0xFF	0×07	I	I	I	I		0×00
BITO	TOPSYS	TJCT_ 140C	LD01_ POKn	LD09_ POKn	BB_OCP	TOPSYS	TJCT_ 140C_M	LD01_ POKn_M	LD09_ POKn_M	BB_ OCP_M	TJCT_ 140C	LD01_ POKn	LD09_ POKn	BB_ OCP		L1_ LPM
BIT1	REG_ INT	TJCT_ 120C	LD02_ POKn	LDO10_ POKn	BB_ OVP	REG_ INT_M	TJCT_ 120C_M	LD02_ POKn_M	LDO10_ POKn_M	BB_ OVP_M	TJCT_ 120C	LD02_ POKn	LDO10_ POKn	BB_ OVP		L1_EN
BIT2	BB_INT	RSVD	LD03_ POKn	LDO11_ POKn	BB_POKn	BB_ INT_M	RSVD	LD03_ POKn_M	LDO11_ POKn_M	BB_ POKn_M	RSVD	LD03_ POKn	LD011_ POKn	BB_ POKn		L2_LPM
BIT3	RSVD	RSVD	LD04_ POKn	LDO12_ POKn	RSVD	RSVD	RSVD	LD04_ POKn_M	LDO12_ POKn_M	RSVD	RSVD	LD04_ POKn	LD012_ POKn	RSVD		L2_EN
BIT4	RSVD	RSVD	LD05_ POKn	LDO13_ POKn	RSVD	RSVD	RSVD	LDO5_ POKn_M	LDO13_ POKn_M	RSVD	RSVD	LDO5_ POKn	LDO13_ POKn	RSVD		L3_LPM
BIT5	RSVD	RSVD	LDO6_ POKn	LDO14_ POKn	RSVD	RSVD	RSVD	LDO6_ POKn_M	LDO14_ POKn_M	RSVD	RSVD	LDO6_ POKn	LDO14_ POKn	RSVD		L3_EN
BIT6	RSVD	RSVD	LDO7_ POKn	LDO15_ POKn	RSVD	RSVD	RSVD	LDO7_ POKn_M	LDO15_ POKn_M	RSVD	RSVD	LDO7_ POKn	LD015_ POKn	RSVD		L4_LPM
BIT7	RSVD	RSVD	LD08_ POKn	B_POKn	RSVD	RSVD	RSVD	LDO8_ POKn_M	B_ POKn_M	RSVD	RSVD	LD08_ POKn	B_POKn	RSVD		L4_EN
R/W	œ	R/C	R/C	R/C	R/C	W.W.	% ₩	W.W.	W.W.	W.W.	œ	œ	œ	œ		XX W
RESET	Type-O	Type-S1	Type-S1	Type-S1	Type-S1	Type-O	Type-O	Type-O	Type-O	Type-O	Type-O	Type-O	Type-O	Type-O		Туре-О
NAME	INT_SRC	SYS_INT	REG_ INT1	REG_ INT2	BB_ INT	INT_ SRC_M	TOPSYS INTM	REG_ INT1_M	REG_ INT2_M	BB_ INT_M	TOPSYS_ STAT	REG_ STAT1	REG_ STAT2	BB_ STAT	RSVD	LDO_ OPMD1
ADDR	00×0	0x01	0x02	0x03	0x04	0x05	90×0	0x07	0x08	60×0	0x0A	0x0B	0x0C	0x0D	0x0E-	0x10

Register Map (continued)
12C Slave Address (W/R): 0xC0/0xC1 (continued)

[																	
	RESET VALUE	00×0	00×0	0000	00×0		0xA0	0xA0	0xA0	0x9C	0xA8	0xA8	0xA8	0xA8	0xA8	0XD0	0XD0
	BITO	L5_ LPM	L9_ LPM	L13_ LPM	B_ LPM												
	BIT1	L5_EN	L9_EN	L13_ EN_	B_EN												
	BIT2	L6_LPM	L10_LPM	L14_LPM	RSVD												
	BIT3	L6_EN	L10_EN	L14_EN	BB_EN		L1_VOUT[6:0]	L2_VOUT[6:0]	L3_VOUT[6:0]	L4_VOUT[6:0]	L5_VOUT[6:0]	L6_VOUT[6:0]	L7_VOUT[6:0]	L8_VOUT[6:0]	L9_VOUT[6:0]	L10_VOUT[6:0]	L11_VOUT[6:0]
	BIT4	L7_LPM	L11_LPM	L15_LPM	RSVD		7	 	L3	L4	F	P7	L7	R9	F3	L1	L1
	BIT5	L7_EN	L11_EN	L15_EN	RSVD												
	BIT6	L8_LPM	L12_ LPM	RSVD	RSVD												
	BIT7	L8_EN	L12_EN	RSVD	RSVD		L1_AD	L2_AD	L3_AD	L4_AD	L5_AD	L6_AD	L7_AD	L8_AD	L9_AD	L10_AD	L11_AD
١	R/W	W.W.	W.W.	W.W.	W.W.		W.W.	R/W	R/W	W/A	R/W	R/W	R/W	R/W	W.W.	W.W.	W.W.
	RESET TYPE	Type-O	Type-O	Type-O	Type-O		Type-O	Type-O									
	NAME	LDO_ OPMD2	LDO_ OPMD3	LDO_ OPMD4	B_BB_ OPMD	RSVD	LDO1_ CFG	LD02_ CFG	LD03_ CFG	LDO4_ CFG	LDO5_ CFG	LD06_ CFG	LDO7_ CFG	LDO8_ CFG	LD09_ CFG	LDO10_ CFG	LDO11 _CFG
	ADDR	0x11	0x12	0x13	0x14	0x15- 0x1F	0x20	0x21	0x22	0x23	0x24	0x25	0x26	0x27	0x28	0x29	0x2A

Register Map (continued)
I<sup>2</sup>C Slave Address (W/R): 0xC0/0xC1 (continued)

ADDR	NAME	RESET TYPE	R/W	BIT7	ВІТ6	BIT5	BIT4	ВІТЗ	BIT2	BIT1	BIT0	RESET VALUE
0x2B	LDO12 _CFG	Type-O	R/W	L12_AD			L1	L12_VOUT[6:0]				0xE4
0x2C	LDO13_ CFG	Type-O	R/W	L13_AD			L1	L13_VOUT[6:0]				0xE4
0x2D	LDO14_ CFG	Type-O	R/W	L14_AD			L1	L14_VOUT[6:0]				0xE4
0x2E	LDO15_ CFG	Type-O	R/W	L15_AD			L1	L15_VOUT[6:0]				0xE4
0x2F	RSVD											
0x30	BUCK_ CFG	Type-O	W.W.	B_RAMP[1:0]	P[1:0]	RSVD	RSVD	B_AD	B_FPWM	RSVD	B_ FSRADE	60×0
0x31	BUCK_ VOUT	Type-O	R/W				B_VOUT[7:0]	[0:2]1				0x78
0x32	BB_CFG	Type-O	R/W	RSVD	RSVD	BB_OVP	BB_OVP_TH[1:0]	BB_AD	BB_ HSKIP	BB_ FPWM	RSVD	0x3C
0x33	BB_ VOUT	Type-O	R/W	RSVD			BE	BB_VOUT[6:0]				0x48
0x34- 0x3F	RSVD											
0x40	BUCK_ SS_FREQ	Type-O	R/W	RSVD	RSVD	RSVD	B_SS	RSVD	В	B_FREQ[2:0]	]	0x04
0x41	UVLO_ FALL	Type-O	R/W	RSVD	RSVD	RSVD	RSVD	RSVD	RSVD	UVLO	UVLO_F[1:0]	0×01
0x42- 0xFF	RSVD											

INT\_SRC

## **Interrupt Source Register**

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x00			
0x00	R		TIPE. O	RESET VALUE. 0X00			
BIT	NAME	POR		DESCRIPTION			
7:3	RSVD	0000 0					
2	BB_INT	0	1: Interrupt even	t on BUCK BOOST is detected.			
1	REG_INT	0	1: Interrupt event on BUCK or LDOs is detected.				
0	TOPSYS_INT	0	1: Interrupt even	t on TOPSYS is detected.			

# TOPSYS\_INT

## **TOPSYS Interrupt Register**

ADDRESS	MODE		TYPE: S1	RESET VALUE: 0x00		
0x01	R/C		TIPE. 31	RESET VALUE: 0X00		
BIT	NAME	POR		DESCRIPTION		
7:2	RSVD	0000 00				
1	TJCT_120C	0	1: Junction temperature (TJCT ) is higher than +120°C.			
0	TJCT_140C	0	1: Junction temp	erature (TJCT ) is higher than +140°C.		

## **REG\_INT1**

## **Regulators Interrupt Register1**

ADDRESS	MODE		TYPE: S1	DECET VALUE, 0::00		
0x02	R/C		1176: 31	RESET VALUE: 0x00		
BIT	NAME	POR		DESCRIPTION		
7	LDO8_POKn	0	1: LDO8 POKn is	s triggered.		
6	LDO7_POKn	0	1: LDO7 POKn is	s triggered.		
5	LDO6_POKn	0	1: LDO6 POKn is triggered.			
4	LDO5_POKn	0	1: LDO5 POKn is triggered.			
3	LDO4_POKn	0	1: LDO4 POKn is	s triggered.		
2	LDO3_POKn	0	1: LDO3 POKn is triggered.			
1	LDO2_POKn	0	1: LDO2 POKn is triggered.			
0	LDO1_POKn	0	1: LDO1 POKn is	s triggered.		

REG\_INT2
Regulators Interrupt Register2

ADDRESS	MODE		TYPE: S1	RESET VALUE: 0x00		
0x03	R/C		TIPE. SI	RESET VALUE. 0X00		
BIT	NAME	POR		DESCRIPTION		
7	B_POKn	0	1: BUCK POKn i	s triggered.		
6	LDO15_POKn	0	1: LDO15 POKn	is triggered.		
5	LDO14_POKn	0	1: LDO14 POKn is triggered.			
4	LDO13_POKn	0	1: LDO13 POKn is triggered.			
3	LDO12_POKn	0	1: LDO12 POKn	is triggered.		
2	LDO11_POKn	0	1: LDO11 POKn is triggered.			
1	LDO10_POKn	0	1: LDO10 POKn is triggered.			
0	LDO9_POKn	0	1: LDO9 POKn is	s triggered.		

# BB\_INT BUCK BOOST Interrupt Register

ADDRESS	MODE		TYPE: S1	RESET VALUE: 0x00	
0x04	R/C		TIPE. SI	RESET VALUE. 0X00	
BIT	NAME	POR		DESCRIPTION	
7:3	RSVD	0000 0			
2	BB_POKn	0	1: BUCK BOOST	POKn is triggered.	
1	BB_OVP	0	1: BUCK BOOST OVP is triggered.		
0	BB_OCP	0	1: BUCK BOOST	OCP is triggered.	

# INT\_SRC\_M Interrupt Source Mask Register

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x07		
0x05	R/W		111 2. 0	NEGET VALUE: 0X07		
BIT	NAME	POR		DESCRIPTION		
7:3	RSVD	0000 0				
2	BB_INT_M	1		BOOST interrupt events. OOST interrupt events.		
1	REG_INT_M	1	0: Enable REG interrupt events. 1: Mask REG interrupt events.			
0	TOPSYS_INT_M	1		YS interrupt events. S interrupt events.		

TOPSYS\_INT\_M
TOPSYS Interrupt Mask Register

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x03		
0x05	R/W		TIPE. O	RESET VALUE. 0x03		
BIT	NAME	POR		DESCRIPTION		
7:2	RSVD	0000 00				
1	TJCT_120C_M	1	0: Enable TJCT_120 interrupt. 1: Mask TJCT_120 interrupt.			
0	TJCT_140C_M	1	0: Enable TJCT_ 1: Mask TJCT_1			

# REG\_INT1\_M Regulators Interrupt Mask Register 1

ADDRESS	MODE		TYPE: O	RESET VALUE: 0×FF		
0x07	R/W		TIPE. O	RESET VALUE. UXFF		
BIT	NAME	POR		DESCRIPTION		
7	LDO8_POKn_M	1	0: Enable LDO8 1: Mask LDO8 P	·		
6	LDO7_POKn_M	1	0: Enable LDO7 1: Mask LDO7 P	·		
5	LDO6_POKn_M	1	0: Enable LDO6 1: Mask LDO6 P	·		
4	LDO5_POKn_M	1	0: Enable LDO5 POKn interrupt.  1: Mask LDO5 POKn interrupt.			
3	LDO4_POKn_M	1	0: Enable LDO4 POKn interrupt. 1: Mask LDO4 POKn interrupt.			
2	LDO3_POKn_M	1	0: Enable LDO3 POKn interrupt. 1: Mask LDO3 POKn interrupt.			
1	LDO2_POKn_M	1	0: Enable LDO2 POKn interrupt. 1: Mask LDO2 POKn interrupt.			
0	LDO1_POKn_M	1	0: Enable LDO1 1: Mask LDO1 P	•		

REG\_INT2\_M
Regulators Interrupt Mask Register 2

ADDRESS	MODE		TYPE: O	DESET VALUE, OVER		
0x08	R/W		TIPE: 0	RESET VALUE: 0xFF		
BIT	NAME	POR		DESCRIPTION		
7	B_POKn_M	1	0: Enable BUCK 1: Mask BUCK F	·		
6	LDO15_POKn_M	1	0: Enable LDO15 1: Mask LDO15	5 POKn interrupt. POKn interrupt.		
5	LDO14_POKn_M	1	0: Enable LDO14 1: Mask LDO14	4 POKn interrupt. POKn interrupt.		
4	LDO13_POKn_M	1	0: Enable LDO13 POKn interrupt. 1: Mask LDO13 POKn interrupt.			
3	LDO12_POKn_M	1	0: Enable LDO12 POKn interrupt. 1: Mask LDO12 POKn interrupt.			
2	LDO11_POKn_M	1	0: Enable LDO11 POKn interrupt. 1: Mask LDO11 POKn interrupt.			
1	LDO10_POKn_M	1	0: Enable LDO10 POKn interrupt. 1: Mask LDO10 POKn interrupt.			
0	LDO9_POKn_M	1	0: Enable LDO9 1: Mask LDO9 P	·		

BB\_INT\_M
BUCK BOOST Interrupt Mask Register

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x07		
0x09	R/W		TIPE. O	RESET VALUE. UXU/		
BIT	NAME	POR		DESCRIPTION		
7:3	RSVD	0000 0				
2	BB_POKn_M	1	0: Enable BUCK BOOST POKn interrupt. 1: Mask BUCK BOOST POKn interrupt.			
1	BB_OVP_M	1	0: Enable BUCK BOOST OVP interrupt. 1: Mask BUCK BOOST OVP interrupt.			
0	BB_OCP_M	1	0: Enable BUCK BOOST OCP interrupt. 1: Mask BUCK BOOST OCP interrupt.			

# TOPSYS\_STAT

## **TOPSYS Status Register**

ADDRESS	MODE		TYPE: O	RESET VALUE: N/A		
0x0A	R		TIPE. O	RESET VALUE. N/A		
BIT	NAME	POR	DESCRIPTION			
7:2	RSVD	_				
1	TJCT_120C	_	0: Junction temperature (TJCT) ≤ +120°C 1: Junction temperature (TJCT) > +120°C			
0	TJCT_140C	_	0: Junction temperature (TJCT) ≤ +140°C 1: Junction temperature (TJCT) > +140°C			

#### **REG\_STAT1**

#### **Regulators Status Register 1**

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x00	
0x0B	R		TYPE: U	RESET VALUE: 0X00	
BIT	NAME	POR		DESCRIPTION	
7	LDO8_POKn	0	LDO8 POKn stat	us	
6	LDO7_POKn	0	LDO7 POKn stat	us	
5	LDO6_POKn	0	LDO6 POKn stat	us	
4	LDO5_POKn	0	LDO5 POKn stat	us	
3	LDO4_POKn	0	LDO4 POKn stat	us	
2	LDO3_POKn	0	LDO3 POKn status		
1	LDO2_POKn	0	LDO2 POKn status		
0	LDO1_POKn	0	LDO1 POKn stat	us	

#### REG\_STAT2

## **Regulators Status Register 2**

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x00	
0x0C	R		TYPE: U	RESET VALUE: 0X00	
BIT	NAME	POR		DESCRIPTION	
7	B_POKn	0	BUCK POKn sta	tus	
6	LDO15_POKn	0	LDO15 POKn status		
5	LDO14_POKn	0	LDO14 POKn sta	atus	
4	LDO13_POKn	0	LDO13 POKn sta	atus	
3	LDO12_POKn	0	LDO12 POKn sta	atus	
2	LDO11_POKn	0	LDO11 POKn status		
1	LDO10_POKn	0	LDO10 POKn status		
0	LDO9_POKn	0	LDO9 POKn stat	us	

BB\_STAT
BUCK BOOST Status Register

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x00		
0x0D	R		TIPE. O	RESET VALUE. 0X00		
BIT	NAME	POR	DESCRIPTION			
7:3	RSVD	0000 0				
2	BB_POKn	0	BUCK BOOST POKn status			
1	BB_OVP	0	BUCK BOOST OVP status			
0	BB_OCP	0	BUCK BOOST OCP status			

Note: 0x0E-0x0F: RSVD.

## LDO\_OPMD1

## **LDO Operating Mode Register 1**

ADDRESS	MODE		TVDE: O	DECET VALUE, 0, 20	
0x10	R/W		TYPE: O	RESET VALUE: 0x00	
BIT	NAME	POR		DESCRIPTION	
7	L4_EN	0	0: Output off 1: Output on		
6	L4_LPM	0	0: Normal mode 1: Low power mode		
5	L3_EN	0	0: Output off 1: Output on		
4	L3_LPM	0	0: Normal mode 1: Low power mod	le	
3	L2_EN	0	0: Output off 1: Output on		
2	L2_LPM	0	0: Normal mode 1: Low power mod	le	
1	L1_EN	0	0: Output off 1: Output on		
0	L1_LPM	0	0: Normal mode 1: Low power mode		

LDO\_OPMD2

# **LDO Operating Mode Register 2**

ADDRESS	MODE		TVPELO	DESET VALUE, 0×00		
0x11	R/W		TYPE: O RESET VALUE: 0x00			
BIT	NAME	POR		DESCRIPTION		
7	L8_EN	0	0: Output off 1: Output on			
6	L8_LPM	0	0: Normal mode 1: Low power mo	de		
5	L7_EN	0	0: Output off 1: Output on			
4	L7_LPM	0	0: Normal mode 1: Low power mo	de		
3	L6_EN	0	0: Output off 1: Output on			
2	L6_LPM	0	0: Normal mode 1: Low power mode			
1	L5_EN	0	0: Output off 1: Output on			
0	L5_LPM	0	0: Normal Mode 1: Low Power Mode			

# LDO\_OPMD3

# **LDO Operating Mode Register 3**

ADDRESS	MODE		ADDDESS	DESET VALUE, 0×00	
0x12	R/W		ADDRESS	RESET VALUE: 0x00	
BIT	NAME	POR		DESCRIPTION	
7	L12_EN	0	0: Output off 1: Output on		
6	L12_LPM	0	0: Normal mode 1: Low power mod	e	
5	L11_EN	0	0: Output off 1: Output on		
4	L11_LPM	0	0: Normal mode 1: Low power mod	e	
3	L10_EN	0	0: Output off 1: Output on		
2	L10_LPM	0	0: Normal mode 1: Low power mode		
1	L9_EN	0	0: Output off 1: Output on		
0	L9_LPM	0	0: Normal mode 1: Low power mod	e	

LDO\_OPMD4

# **LDO Operating Mode Register 4**

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x00	
0x13	R/W		1112.0	NEGET VALUE. 0X00	
BIT	NAME	POR		DESCRIPTION	
7:6	RSVD				
5	L15_EN	0	0b: Output off 1b: Output on		
4	L15_LPM	0	0b: Normal mode 1b: Low power mo	ode	
3	L14_EN	0	0b: Output off 1b: Output on		
2	L14_LPM	0	0b: Normal mode 1b: Low power mode		
1	L13_EN	0	0b: Output off 1b: Output on		
0	L13_LPM	0	0b: Normal mode 1b: Low power mode		

#### B\_BB\_OPMD

## **BUCK and BUCK BOOST Operating Mode Register**

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x00		
0x14	R/W		TTPE. O	RESET VALUE. 0X00		
BIT	NAME	POR		DESCRIPTION		
7:4	RSVD	0000				
3	BB_EN	0	0: BUCK BOOST output off 1: BUCK BOOST output on			
2	RSVD	0				
1	B_EN	0	0: BUCK output off 1: BUCK output on			
0	B_LPM	0	0: Normal mode 1: Low power mode			

Note: 0x14-0x1F: RSVD.

LDO1\_CFG
LDO1 Configuration Register

ADDRESS	MODE	_	TVDE: 0		EOFT \/ALUE: 0::A	
0x20	R/W		TYPE: O RESET VALUE: 0xA0			U
BIT	NAME	POR	DESCRIPTION			
7	L1_AD	1	Output Active Dis 0: Disable 1: Enable	scharge		
			NMOS LDO Outp	ut Voltage		
			0x00 = 0.6000V	0x20 = 1.0000V	0x40 = 1.4000V	0x60 = 1.8000V
			0x01 = 0.6125V	0x21 = 1.0125V	0x41 = 1.4125V	0x61 = 1.8125V
			0x02 = 0.6250V	0x22 = 1.0250V	0x42 = 1.4250V	0x62 = 1.8250V
			0x03 = 0.6375V	0x23 = 1.0375V	0x43 = 1.4375V	0x63 = 1.8375V
			0x04 = 0.6500V	0x24 = 1.0500V	0x44 = 1.4500V	0x64 = 1.8500V
			0x05 = 0.6625V	0x25 = 1.0625V	0x45 = 1.4625V	0x65 = 1.8625V
			0x06 = 0.6750V	0x26 = 1.0750V	0x46 = 1.4750V	0x66 = 1.8750V
			0x07 = 0.6875V	0x27 = 1.0875V	0x47 = 1.4875V	0x67 = 1.8875V
			0x08 = 0.7000V	0x28 = 1.1000V	0x48 = 1.5000V	0x68 = 1.9000V
			0x09 = 0.7125V	0x29 = 1.1125V	0x49 = 1.5125V	0x69 = 1.9125V
			0x0A = 0.7250V	0x2A = 1.1250V	0x4A = 1.5250V	0x6A = 1.9250V
			0x0B = 0.7375V	0x2B = 1.1375V	0x4B = 1.5375V	0x6B = 1.9375V
			0x0C = 0.7500V	0x2C = 1.1500V	0x4C = 1.5500V	0x6C = 1.9500V
			0x0D = 0.7625V	0x2D = 1.1625V	0x4D = 1.5625V	0x6D = 1.9625V
	L1_VOUT[6:0]		0x0E = 0.7750V	0x2E = 1.1750V	0x4E = 1.5750V	0x6E = 1.9750V
6:0		010 0000	0x0F = 0.7875V	0x2F = 1.1875V	0x4F = 1.5875V	0x6F = 1.9875V
			0x10 = 0.8000V	0x30 = 1.2000V	0x50 = 1.6000V	0x70 = 2.0000V
			0x11 = 0.8125V	0x31 = 1.2125V	0x51 = 1.6125V	0x71 = 2.0125V
			0x12 = 0.8250V	0x32 = 1.2250V	0x52 = 1.6250V	0x72 = 2.0250V
			0x13 = 0.8375V	0x33 = 1.2375V	0x53 = 1.6375V	0x73 = 2.0375V
			0x14 = 0.8500V	0x34 = 1.2500V	0x54 = 1.6500V	0x74 = 2.0500V
			0x15 = 0.8625V	0x35 = 1.2625V	0x55 = 1.6625V	0x75 = 2.0625V
			0x16 = 0.8750V	0x36 = 1.2750V	0x56 = 1.6750V	0x76 = 2.0750V
			0x17 = 0.8875V	0x37 = 1.2875V	0x57 = 1.6875V	0x77 = 2.0875V
			0x18 = 0.9000V	0x38 = 1.3000V	0x58 = 1.7000V	0x78 = 2.1000V
			0x19 = 0.9125V	0x39 = 1.3125V	0x59 = 1.7125V	0x79 = 2.1125V
			0x1A = 0.9250V	0x3A = 1.3250V	0x5A = 1.7250V	0x7A = 2.1250V
			0x1B = 0.9375V	0x3B = 1.3375V	0x5B = 1.7375V	0x7B = 2.1375V
			0x1C = 0.9500V	0x3C = 1.3500V	0x5C = 1.7500V	0x7C = 2.1500V
			0x1D = 0.9625V	0x3D = 1.3625V	0x5D = 1.7625V	0x7D = 2.1625V
			0x1E = 0.9750V	0x3E = 1.3750V	0x5E = 1.7750V	0x7E = 2.1750V
			0x1F = 0.9875V	0x3F = 1.3875V	0x5F = 1.7875V	0x7F = 2.1875V

LDO2\_CFG
LDO2 Configuration Register

ADDRESS	MODE	MODE			EOFT \/ALUE: 0::A		
0x21	R/W		TYPE: O RESET VALUE: 0xA0			J	
BIT	NAME	POR	DESCRIPTION				
7	L2_AD	1	Output Active Dis 0: Disable 1: Enable				
			NMOS LDO Outp	ut Voltage			
			0x00 = 0.6000V	0x20 = 1.0000V	0x40 = 1.4000V	0x60 = 1.8000V	
			0x01 = 0.6125V	0x21 = 1.0125V	0x41 = 1.4125V	0x61 = 1.8125V	
			0x02 = 0.6250V	0x22 = 1.0250V	0x42 = 1.4250V	0x62 = 1.8250V	
			0x03 = 0.6375V	0x23 = 1.0375V	0x43 = 1.4375V	0x63 = 1.8375V	
			0x04 = 0.6500V	0x24 = 1.0500V	0x44 = 1.4500V	0x64 = 1.8500V	
			0x05 = 0.6625V	0x25 = 1.0625V	0x45 = 1.4625V	0x65 = 1.8625V	
			0x06 = 0.6750V	0x26 = 1.0750V	0x46 = 1.4750V	0x66 = 1.8750V	
			0x07 = 0.6875V	0x27 = 1.0875V	0x47 = 1.4875V	0x67 = 1.8875V	
			0x08 = 0.7000V	0x28 = 1.1000V	0x48 = 1.5000V	0x68 = 1.9000V	
			0x09 = 0.7125V	0x29 = 1.1125V	0x49 = 1.5125V	0x69 = 1.9125V	
			0x0A = 0.7250V	0x2A = 1.1250V	0x4A = 1.5250V	0x6A = 1.9250V	
			0x0B = 0.7375V	0x2B = 1.1375V	0x4B = 1.5375V	0x6B = 1.9375V	
			0x0C = 0.7500V	0x2C = 1.1500V	0x4C = 1.5500V	0x6C = 1.9500V	
			0x0D = 0.7625V	0x2D = 1.1625V	0x4D = 1.5625V	0x6D = 1.9625V	
			0x0E = 0.7750V	0x2E = 1.1750V	0x4E = 1.5750V	0x6E = 1.9750V	
6:0	L2_VOUT[6:0]	010 0000	0x0F = 0.7875V	0x2F = 1.1875V	0x4F = 1.5875V	0x6F = 1.9875V	
			0x10 = 0.8000V	0x30 = 1.2000V	0x50 = 1.6000V	0x70 = 2.0000V	
			0x11 = 0.8125V	0x31 = 1.2125V	0x51 = 1.6125V	0x71 = 2.0125V	
			0x12 = 0.8250V	0x32 = 1.2250V	0x52 = 1.6250V	0x72 = 2.0250V	
			0x13 = 0.8375V	0x33 = 1.2375V	0x53 = 1.6375V	0x73 = 2.0375V	
			0x14 = 0.8500V	0x34 = 1.2500V	0x54 = 1.6500V	0x74 = 2.0500V	
			0x15 = 0.8625V	0x35 = 1.2625V	0x55 = 1.6625V	0x75 = 2.0625V	
			0x16 = 0.8750V	0x36 = 1.2750V	0x56 = 1.6750V	0x76 = 2.0750V	
			0x17 = 0.8875V	0x37 = 1.2875V	0x57 = 1.6875V	0x77 = 2.0875V	
			0x18 = 0.9000V	0x38 = 1.3000V	0x58 = 1.7000V	0x78 = 2.1000V	
			0x19 = 0.9125V	0x39 = 1.3125V	0x59 = 1.7125V	0x79 = 2.1125V	
			0x1A = 0.9250V	0x3A = 1.3250V	0x5A = 1.7250V	0x7A = 2.1250V	
			0x1B = 0.9375V	0x3B = 1.3375V	0x5B = 1.7375V	0x7B = 2.1375V	
			0x1C = 0.9500V	0x3C = 1.3500V	0x5C = 1.7500V	0x7C = 2.1500V	
			0x1D = 0.9625V	0x3D = 1.3625V	0x5D = 1.7625V	0x7D = 2.1625V	
			0x1E = 0.9750V	0x3E = 1.3750V	0x5E = 1.7750V	0x7E = 2.1750V	
			0x1F = 0.9875V	0x3F = 1.3875V	0x5F = 1.7875V	0x7F = 2.1875V	

LDO3\_CFG
LDO3 Configuration Register

ADDRESS	MODE	MODE			FOFT VALUE: 0 A		
0x22	R/W	R/W		TYPE: O RESET VALUE: 0xA0			
BIT	NAME	POR	DESCRIPTION				
7	L3_AD	1	Output Active Dis 0: Disable 1: Enable	scharge			
			NMOS LDO Output Voltage Table				
			0x00 = 0.6000V	0x20 = 1.0000V	0x40 = 1.4000V	0x60 = 1.8000V	
			0x01 = 0.6125V	0x21 = 1.0125V	0x41 = 1.4125V	0x61 = 1.8125V	
			0x02 = 0.6250V	0x22 = 1.0250V	0x42 = 1.4250V	0x62 = 1.8250V	
			0x03 = 0.6375V	0x23 = 1.0375V	0x43 = 1.4375V	0x63 = 1.8375V	
			0x04 = 0.6500V	0x24 = 1.0500V	0x44 = 1.4500V	0x64 = 1.8500V	
			0x05 = 0.6625V	0x25 = 1.0625V	0x45 = 1.4625V	0x65 = 1.8625V	
			0x06 = 0.6750V	0x26 = 1.0750V	0x46 = 1.4750V	0x66 = 1.8750V	
			0x07 = 0.6875V	0x27 = 1.0875V	0x47 = 1.4875V	0x67 = 1.8875V	
			0x08 = 0.7000V	0x28 = 1.1000V	0x48 = 1.5000V	0x68 = 1.9000V	
			0x09 = 0.7125V	0x29 = 1.1125V	0x49 = 1.5125V	0x69 = 1.9125V	
			0x0A = 0.7250V	0x2A = 1.1250V	0x4A = 1.5250V	0x6A = 1.9250V	
			0x0B = 0.7375V	0x2B = 1.1375V	0x4B = 1.5375V	0x6B = 1.9375V	
			0x0C = 0.7500V	0x2C = 1.1500V	0x4C = 1.5500V	0x6C = 1.9500V	
			0x0D = 0.7625V	0x2D = 1.1625V	0x4D = 1.5625V	0x6D = 1.9625V	
			0x0E = 0.7750V	0x2E = 1.1750V	0x4E = 1.5750V	0x6E = 1.9750V	
6:0	L3_VOUT[6:0]	010 0000	0x0F = 0.7875V	0x2F = 1.1875V	0x4F = 1.5875V	0x6F = 1.9875V	
			0x10 = 0.8000V	0x30 = 1.2000V	0x50 = 1.6000V	0x70 = 2.0000V	
			0x11 = 0.8125V	0x31 = 1.2125V	0x51 = 1.6125V	0x71 = 2.0125V	
			0x12 = 0.8250V	0x32 = 1.2250V	0x52 = 1.6250V	0x72 = 2.0250V	
			0x13 = 0.8375V	0x33 = 1.2375V	0x53 = 1.6375V	0x73 = 2.0375V	
			0x14 = 0.8500V	0x34 = 1.2500V	0x54 = 1.6500V	0x74 = 2.0500V	
			0x15 = 0.8625V	0x35 = 1.2625V	0x55 = 1.6625V	0x75 = 2.0625V	
			0x16 = 0.8750V	0x36 = 1.2750V	0x56 = 1.6750V	0x76 = 2.0750V	
			0x17 = 0.8875V	0x37 = 1.2875V	0x57 = 1.6875V	0x77 = 2.0875V	
			0x18 = 0.9000V	0x38 = 1.3000V	0x58 = 1.7000V	0x78 = 2.1000V	
			0x19 = 0.9125V	0x39 = 1.3125V	0x59 = 1.7125V	0x79 = 2.1125V	
			0x1A = 0.9250V	0x3A = 1.3250V	0x5A = 1.7250V	0x7A = 2.1250V	
			0x1B = 0.9375V	0x3B = 1.3375V	0x5B = 1.7375V	0x7B = 2.1375V	
			0x1C = 0.9500V	0x3C = 1.3500V	0x5C = 1.7500V	0x7C = 2.1500V	
			0x1D = 0.9625V	0x3D = 1.3625V	0x5D = 1.7625V	0x7D = 2.1625V	
			0x1E = 0.9750V	0x3E = 1.3750V	0x5E = 1.7750V	0x7E = 2.1750V	
			0x1F = 0.9875V	0x3F = 1.3875V	0x5F = 1.7875V	0x7F = 2.1875V	

LDO4\_CFG
LDO4 Configuration Register

ADDRESS	MODE			_			
0x23	R/W		TYPE: O	R	ESET VALUE: 0x90	3	
BIT	NAME	POR	DESCRIPTION				
7	L4_AD	1	Output Active Dis 0: Disable 1: Enable	charge			
			PMOSLV LDO Ou	tput Voltage Table			
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V	
6:0	L4_VOUT[6:0]	001 1100	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V	

LDO5\_CFG
LDO5 Configuration Register

ADDRESS	MODE			_				
0x24	R/W		TYPE: O	R	ESET VALUE: 0xA	3		
BIT	NAME	POR		DESCR	RIPTION			
7	L5_AD	1	Output Active Dis 0: Disable 1: Enable	scharge				
			PMOSLV LDO Ou	PMOSLV LDO Output Voltage Table				
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V		
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V		
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V		
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V		
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V		
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V		
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V		
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V		
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V		
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V		
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V		
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V		
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V		
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V		
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V		
6:0	L5_VOUT[6:0]	010 1000	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V		
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V		
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V		
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V		
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V		
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V		
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V		
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V		
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V		
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V		
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V		
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V		
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V		
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V		
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V		
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V		
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V		

LDO6\_CFG
LDO6 Configuration Register

ADDRESS	MODE		TVDE: O		ESET VALUE: 0xA	•	
0x25	R/W		TYPE: O	TIPE. O RESET VAL			
BIT	NAME POR		DESCRIPTION				
7	L6_AD	1	Output Active Dis 0: Disable 1: Enable	scharge			
			PMOSLV LDO Output Voltage				
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375\	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400\	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425\	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450\	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475\	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500\	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525\	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550\	
6:0	L6_VOUT[6:0]	010 1000	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575\	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600\	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625\	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650\	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675\	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700\	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725\	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750\	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775\	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800\	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825\	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850\	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875\	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950\	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975\	

LDO7\_CFG
LDO7 Configuration Register

ADDRESS	MODE		7/7-	_		_	
0x26	R/W		TYPE: O	R	ESET VALUE: 0xA	3	
BIT	NAME	POR	DESCRIPTION				
7	L7_AD	1	Output Active Dis 0: Disable 1: Enable	scharge			
			PMOSLV LDO Ou	tput Voltage			
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V	
6:0	L7_VOUT[6:0]	010 1000	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V	

LDO8\_CFG
LDO8 Configuration Register

ADDRESS	MODE		T)/DT 0	_			
0x27	R/W		TYPE: O	RESET VALUE: 0xA8  DESCRIPTION			
BIT	NAME	POR					
7	L8_AD	1	Output Active Dis 0: Disable 1: Enable				
			PMOSLV LDO Ou	tput Voltage			
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V	
6:0	L8_VOUT[6:0]	010 1000	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V	

LDO9\_CFG
LDO9 Configuration Register

ADDRESS	MODE	MODE			EOFT VALUE 0 - A		
0x28	R/W		TYPE: O	R	ESET VALUE: 0xA	8	
BIT	NAME	POR		DESCR			
7	L9_AD	1	Output Active Dis 0: Disable 1: Enable				
			PMOSLV LDO Ou	tput Voltage			
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V	
6:0	L9_VOUT[6:0]	010 1000	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V	

LDO10\_CFG
LDO10 Configuration Register

ADDRESS	MODE	MODE		_		_	
0x29	R/W		TYPE: O	R	ESET VALUE: 0xD	0	
BIT	NAME	POR	DESCRIPTION				
7	L10_AD	1	Output Active Discharge 0: Disable 1: Enable				
			PMOSLS LDO Output Voltage				
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V	
6:0	L10_VOUT[6:0]	101 0000	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V	

LDO11\_CFG
LDO11 Configuration Register

ADDRESS	MODE	MODE			FOET VALUE: 0:-D			
0x29	R/W		TYPE: O	K	ESET VALUE: 0xD0			
BIT	NAME	POR	DESCRIPTION					
7	L10_AD	1	Output Active Dis 0: Disable 1: Enable	scharge				
			PMOSLS LDO Output Voltage					
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V		
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V		
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V		
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V		
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V		
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V		
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V		
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V		
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V		
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V		
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V		
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V		
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V		
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V		
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V		
6:0	L10_VOUT[6:0]	101 0000	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V		
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V		
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V		
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V		
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V		
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V		
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V		
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V		
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V		
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V		
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V		
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V		
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V		
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V		
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V		
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V		
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V		

LDO12\_CFG
LDO12 Configuration Register

ADDRESS	MODE	MODE		_		_	
0x2B	R/W		TYPE: O	R	ESET VALUE: 0xE4	4	
BIT	NAME	POR	DESCRIPTION				
7	L12_AD	1	Output Active Discharge 0: Disable 1: Enable				
			PMOSLS LDO Output Voltage				
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V	
6:0	L12_VOUT[6:0]	110 0100	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V	

LDO13\_CFG
LDO13 Configuration Register

ADDRESS	MODE		TVDE: O		FORT VALUE, O.	4	
0x2C	R/W		TYPE: O	K	ESET VALUE: 0xE4	+	
BIT	NAME POR		DESCRIPTION				
7	L13_AD	1	Output Active Dis 0: Disable 1: Enable	scharge			
			PMOSLS LDO Ou	itput Voltage			
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275\	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300\	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350\	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375\	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400\	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425\	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450\	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500°	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550	
6:0	L13_VOUT[6:0]	110 0100	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575\	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600\	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650\	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675\	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700\	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725\	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750\	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775\	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800\	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825\	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850\	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950\	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975\	

LDO14\_CFG
LDO14 Configuration Register

ADDRESS	MODE	MODE		_		_	
0x2D	R/W		TYPE: O	R	ESET VALUE: 0xE4	4	
BIT	NAME	POR	DESCRIPTION				
7	L14_AD	1	Output Active Dis 0: Disable 1: Enable	scharge			
			PMOSLS LDO Output Voltage				
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V	
6:0	L14_VOUT[6:0]	110 0100	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V	

LDO15\_CFG
LDO15 Configuration Register

ADDRESS	MODE						
0x2E	R/W		TYPE: O	R	ESET VALUE: 0xE4	4	
BIT	NAME	POR	DESCRIPTION				
7	L15_AD	1	Output Active Dis 0: Disable 1: Enable	scharge			
			PMOSLS LDO Ou	tput Voltage			
			0x00 = 0.800V	0x20 = 1.600V	0x40 = 2.400V	0x60 = 3.200V	
			0x01 = 0.825V	0x21 = 1.625V	0x41 = 2.425V	0x61 = 3.225V	
			0x02 = 0.850V	0x22 = 1.650V	0x42 = 2.450V	0x62 = 3.250V	
			0x03 = 0.875V	0x23 = 1.675V	0x43 = 2.475V	0x63 = 3.275V	
			0x04 = 0.900V	0x24 = 1.700V	0x44 = 2.500V	0x64 = 3.300V	
			0x05 = 0.925V	0x25 = 1.725V	0x45 = 2.525V	0x65 = 3.325V	
			0x06 = 0.950V	0x26 = 1.750V	0x46 = 2.550V	0x66 = 3.350V	
			0x07 = 0.975V	0x27 = 1.775V	0x47 = 2.575V	0x67 = 3.375V	
			0x08 = 1.000V	0x28 = 1.800V	0x48 = 2.600V	0x68 = 3.400V	
			0x09 = 1.025V	0x29 = 1.825V	0x49 = 2.625V	0x69 = 3.425V	
			0x0A = 1.050V	0x2A = 1.850V	0x4A = 2.650V	0x6A = 3.450V	
			0x0B = 1.075V	0x2B = 1.875V	0x4B = 2.675V	0x6B = 3.475V	
			0x0C = 1.100V	0x2C = 1.900V	0x4C = 2.700V	0x6C = 3.500V	
			0x0D = 1.125V	0x2D = 1.925V	0x4D = 2.725V	0x6D = 3.525V	
			0x0E = 1.150V	0x2E = 1.950V	0x4E = 2.750V	0x6E = 3.550V	
6:0	L15_VOUT[6:0]	110 0100	0x0F = 1.175V	0x2F = 1.975V	0x4F = 2.775V	0x6F = 3.575V	
			0x10 = 1.200V	0x30 = 2.000V	0x50 = 2.800V	0x70 = 3.600V	
			0x11 = 1.225V	0x31 = 2.025V	0x51 = 2.825V	0x71 = 3.625V	
			0x12 = 1.250V	0x32 = 2.050V	0x52 = 2.850V	0x72 = 3.650V	
			0x13 = 1.275V	0x33 = 2.075V	0x53 = 2.875V	0x73 = 3.675V	
			0x14 = 1.300V	0x34 = 2.100V	0x54 = 2.900V	0x74 = 3.700V	
			0x15 = 1.325V	0x35 = 2.125V	0x55 = 2.925V	0x75 = 3.725V	
			0x16 = 1.350V	0x36 = 2.150V	0x56 = 2.950V	0x76 = 3.750V	
			0x17 = 1.375V	0x37 = 2.175V	0x57 = 2.975V	0x77 = 3.775V	
			0x18 = 1.400V	0x38 = 2.200V	0x58 = 3.000V	0x78 = 3.800V	
			0x19 = 1.425V	0x39 = 2.225V	0x59 = 3.025V	0x79 = 3.825V	
			0x1A = 1.450V	0x3A = 2.250V	0x5A = 3.050V	0x7A = 3.850V	
			0x1B = 1.475V	0x3B = 2.275V	0x5B = 3.075V	0x7B = 3.875V	
			0x1C = 1.500V	0x3C = 2.300V	0x5C = 3.100V	0x7C = 3.900V	
			0x1D = 1.525V	0x3D = 2.325V	0x5D = 3.125V	0x7D = 3.925V	
			0x1E = 1.550V	0x3E = 2.350V	0x5E = 3.150V	0x7E = 3.950V	
			0x1F = 1.575V	0x3F = 2.375V	0x5F = 3.175V	0x7F = 3.975V	

Note: 0x2F: RSVD.

BUCK\_CFG
BUCK Configuration Register

ADDRESS	MODE		TVDE: O	DESET VALUE, 0::00	
0x30	R/W		TYPE: O	RESET VALUE: 0x09	
BIT	NAME	POR		DESCRIPTION	
7:6	B_RAMP[1:0]	00	Rising Ramp Ra 00b: 12.5mV/μs 01b: 25mV/μs 10b: 50mV/μs 11b: 100mV/μs	te Control	
5:4	RSVD	00			
3	B_AD	1	Output Active Di 0: Disable 1: Enable	ischarge	
2	B_FPWM	0	Forced PWM 0: Turn off Forced (Automatic SKIP 1: Turn on Forced	mode operation under light load)	
1	RSVD	0			
0	B_FSRAD	1	Falling Slew Rate Active Discharge  0: Disable Active Discharge  BUCK is allowed to operate in SKIP mode during the time the output volta decreases (only if B3_FPWM = 0). In SKIP mode, BUCK cannot sink current from the output capacitor and the output voltage falling slew rate is a function of the external load. If the load is heavy, the output voltage fallis slew rate is limited to 6.25mV/μs. If the load is light, the output voltage fall slew rate is a function of the output capacitance and the load. Note that the internal feedback string always imposes a 2μA load on the output.  1: Enable Active Discharge		
			BUCK operates in forced PWM mode during the time the output voltage decreases. In forced PWM mode, BUCK can sink current from the output capacitor to ensure that the output voltage falls at the rate of 6.25mV/µs. To ensure a smooth output voltage ramp-down, forced PMW mode remains engaged for 50µs after the output voltage decreases to its target voltage.		

# BUCK\_VOUT

# **BUCK Output Voltage Setting Register**

ADDRESS	MODE		MODE TYPE: O		
0x31	R/W		TIPE: 0	RESET VALUE: 0x78	
BIT	NAME	POR	DESCRIPTION		
7:0	B_VOUT[7:0]	0111 1000	BUCK Output Voltage (see table immediately below)		

## **BUCK Output Voltage**

0x00 =	0x20 =	0x40 =	0x60 =	0x80 =	0xA0 =	0xC0 =	0xE0 =
0.50000V	0.70000V	0.90000V	1.10000V	1.30000V	1.50000V	1.70000V	1.80000V
0x01 =	0x21 =	0x41 =	0x61 =	0x81 =	0xA1 =	0xC1 =	0xE1 =
0.50625V	0.70625V	0.90625V	1.10625V	1.30625V	1.50625V	1.70625V	1.80000V
0x02 =	0x22 =	0x42 =	0x62 =	0x82 =	0xA2 =	0xC2 =	0xE2 =
0.51250V	0.71250V	0.91250V	1.11250V	1.31250V	1.51250V	1.71250V	1.80000V
0x03 =	0x23 =	0x43 =	0x63 =	0x83 =	0xA3 =	0xC3 =	0xE3 =
0.51875V	0.71875V	0.91875V	1.11875V	1.31875V	1.51875V	1.71875V	1.80000V
0x04 =	0x24 =	0x44 =	0x64 =	0x84 =	0xA4 =	0xC4 =	0xE4 =
0.52500V	0.72500V	0.92500V	1.12500V	1.32500V	1.52500V	1.72500V	1.80000V
0x05 =	0x25 =	0x45 =	0x65 =	0x85 =	0xA5 =	0xC5 =	0xE5 =
0.53125V	0.73125V	0.93125V	1.13125V	1.33125V	1.53125V	1.73125V	1.80000V
0x06 =	0x26 =	0x46 =	0x66 =	0x86 =	0xA6 =	0xC6 =	0xE6 =
0.53750V	0.73750V	0.93750V	1.13750V	1.33750V	1.53750V	1.73750V	1.80000V
0x07 =	0x27 =	0x47 =	0x67 =	0x87 =	0xA7 =	0xC7 =	0xE7 =
0.54375V	0.74375V	0.94375V	1.14375V	1.34375V	1.54375V	1.74375V	1.80000V
0x08 =	0x28 =	0x48 =	0x68 =	0x88 =	0xA8 =	0xC8 =	0xE8 =
0.55000V	0.75000V	0.95000V	1.15000V	1.35000V	1.55000V	1.75000V	1.80000V
0x09 =	0x29 =	0x49 =	0x69 =	0x89 =	0xA9 =	0xC9 =	0xE9 =
0.55625V	0.75625V	0.95625V	1.15625V	1.35625V	1.55625V	1.75625V	1.80000V
0x0A =	0x2A =	0x4A =	0x6A =	0x8A =	0xAA =	0xCA =	0xEA =
0.56250V	0.76250V	0.96250V	1.16250V	1.36250V	1.56250V	1.76250V	1.80000V
0x0B =	0x2B =	0x4B =	0x6B =	0x8B =	0xAB =	0xCB =	0xEB =
0.56875V	0.76875V	0.96875V	1.16875V	1.36875V	1.56875V	1.76875V	1.80000V
0x0C =	0x2C =	0x4C =	0x6C =	0x8C =	0xAC =	0xCC =	0xEC =
0.57500V	0.77500V	0.97500V	1.17500V	1.37500V	1.57500V	1.77500V	1.80000V
0x0D =	0x2D =	0x4D =	0x6D =	0x8D =	0xAD =	0xCD =	0xED =
0.58125V	0.78125V	0.98125V	1.18125V	1.38125V	1.58125V	1.78125V	1.80000V
0x0E =	0x2E =	0x4E =	0x6E =	0x8E =	0xAE =	0xCE =	0xEE =
0.58750V	0.78750V	0.98750V	1.18750V	1.38750V	1.58750V	1.78750V	1.80000V
0x0F =	0x2F =	0x4F =	0x6F =	0x8F =	0xAF =	0xCF =	0xEF =
0.59375V	0.79375V	0.99375V	1.19375V	1.39375V	1.59375V	1.79375V	1.80000V

# **BUCK Output Voltage (continued)**

0x10 =	0x30 =	0x50 =	0x70 =	0x90 =	0xB0 =	0xD0 =	0xF0 =
0.60000V	0.80000V	1.00000V	1.20000V	1.40000V	1.60000V	1.80000V	1.80000V
0x11 =	0x31 =	0x51 =	0x71 =	0x91 =	0xB1 =	0xD1 =	0xF1 =
0.60625V	0.80625V	1.00625V	1.20625V	1.40625V	1.60625V	1.80000V	1.80000V
0x12 =	0x32 =	0x52 =	0x72 =	0x92 =	0xB2 =	0xD2 =	0xF2 =
0.61250V	0.81250V	1.01250V	1.21250V	1.41250V	1.61250V	1.80000V	1.80000V
0x13 =	0x33 =	0x53 =	0x73 =	0x93 =	0xB3 =	0xD3 =	0xF3 =
0.61875V	0.81875V	1.01875V	1.21875V	1.41875V	1.61875V	1.80000V	1.80000V
0x14 =	0x34 =	0x54 =	0x74 =	0x94 =	0xB4 =	0xD4 =	0xF4 =
0.62500V	0.82500V	1.02500V	1.22500V	1.42500V	1.62500V	1.80000V	1.80000V
0x15 =	0x35 =	0x55 =	0x75 =	0x95 =	0xB5 =	0xD5 =	0xF5 =
0.63125V	0.83125V	1.03125V	1.23125V	1.43125V	1.63125V	1.80000V	1.80000V
0x16 =	0x36 =	0x56 =	0x76 =	0x96 =	0xB6 =	0xD6 =	0xF6 =
0.63750V	0.83750V	1.03750V	1.23750V	1.43750V	1.63750V	1.80000V	1.80000V
0x17 =	0x37 =	0x57 =	0x77 =	0x97 =	0xB7 =	0xD7 =	0xF7 =
0.64375V	0.84375V	1.04375V	1.24375V	1.44375V	1.64375V	1.80000V	1.80000V
0x18 =	0x38 =	0x58 =	0x78 =	0x98 =	0xB8 =	0xD8 =	0xF8 =
0.65000V	0.85000V	1.05000V	1.25000V	1.45000V	1.65000V	1.80000V	1.80000V
0x19 =	0x39 =	0x59 =	0x79 =	0x99 =	0xB9 =	0xD9 =	0xF9 =
0.65625V	0.85625V	1.05625V	1.25625V	1.45625V	1.65625V	1.80000V	1.80000V
0x1A =	0x3A =	0x5A =	0x7A =	0x9A =	0xBA =	0xDA =	0xFA =
0.66250V	0.86250V	1.06250V	1.26250V	1.46250V	1.66250V	1.80000V	1.80000V
0x1B =	0x3B =	0x5B =	0x7B =	0x9B =	0xBB =	0xDB =	0xFB =
0.66875V	0.86875V	1.06875V	1.26875V	1.46875V	1.66875V	1.80000V	1.80000V
0x1C =	0x3C =	0x5C =	0x7C =	0x9C =	0xBC =	0xDC =	0xFC =
0.67500V	0.87500V	1.07500V	1.27500V	1.47500V	1.67500V	1.80000V	1.80000V
0x1D =	0x3D =	0x5D =	0x7D =	0x9D =	0xBD =	0xDD =	0xFD =
0.68125V	0.88125V	1.08125V	1.28125V	1.48125V	1.68125V	1.80000V	1.80000V
0x1E =	0x3E =	0x5E =	0x7E =	0x9E =	0xBE =	0xDE =	0xFE =
0.68750V	0.88750V	1.08750V	1.28750V	1.48750V	1.68750V	1.80000V	1.80000V
0x1F =	0x3F =	0x5F =	0x7F =	0x9F =	0xBF =	0xDF =	0xFF =
0.69375V	0.89375V	1.09375V	1.29375V	1.49375V	1.69375V	1.80000V	1.80000V

BB\_CFG
BUCK BOOST Configuration Register

ADDRESS	MODE		TVDE	DEGET VALUE, 0.20
0x32	R/W		TYPE: O	RESET VALUE: 0x3C
BIT	NAME	POR		DESCRIPTION
7:6	RSVD	00		DESCRIPTION
5:4	BB_OVP_TH[1:0]	11	Output OVP Thres 00b: No OVP 01b: 110% of V <sub>OU</sub> - 10b: 115% of V <sub>OU</sub> - 11b: 120% of V <sub>OU</sub>	г г
3	BB_AD	1	Output Active Dis 0: Disable 1kΩ acti 1: Enable 1kΩ active	ve discharge.
2	BB_HSKIP	1	High-Skip Mode E 0: Disable high-ski 1: Enable high-sk HSKIP function	o mode.
1	BB_FPWM	0	Forced PWM Enable 0: HSKIP mode HSKIP function is active when BB_FPWM = 0 and BB_HSKIP = 0. 1: Forced PWM	
0	RSVD	0		

BB\_VOUT
BUCK BOOST Output Voltage Setting Register

ADDRESS	MODE		T)/DT 0				
0x33	R/W		TYPE: O	RESET VALUE: 0x48			
BIT	NAME	POR		DESCRIPTION			
7	RSVD	0	Write 0.				
			Write 0.  BUCK BOOST OF COMMENT O		0x40 = 3.4000V 0x41 = 3.4125V 0x42 = 3.4250V 0x43 = 3.4375V 0x44 = 3.4500V 0x45 = 3.4625V 0x46 = 3.4750V 0x47 = 3.4875V 0x48 = 3.5000V 0x49 = 3.5125V	0x60 = 3.8000V 0x61 = 3.8125V 0x62 = 3.8250V 0x63 = 3.8375V 0x64 = 3.8500V 0x65 = 3.8625V 0x66 = 3.8750V 0x67 = 3.8875V 0x68 = 3.9000V 0x69 = 3.9125V	
6:0	BB_VOUT[6:0]	100 0000	0x0A = 2.7250V 0x0B = 2.7375V 0x0C = 2.7500V 0x0D = 2.7625V 0x0E = 2.7750V 0x0F = 2.7875V 0x10 = 2.8000V 0x11 = 2.8125V 0x12 = 2.8250V 0x13 = 2.8375V 0x14 = 2.8500V 0x15 = 2.8625V 0x16 = 2.8750V	0x2A = 3.1250V 0x2B = 3.1375V 0x2C = 3.1500V 0x2D = 3.1625V 0x2E = 3.1750V 0x2F = 3.1875V 0x30 = 3.2000V 0x31 = 3.2125V 0x32 = 3.2250V 0x33 = 3.2375V 0x34 = 3.2500V 0x35 = 3.2625V 0x36 = 3.2750V	0x4A = 3.5250V 0x4B = 3.5375V 0x4C = 3.5500V 0x4D = 3.5625V 0x4E = 3.5750V 0x4F = 3.5875V 0x50 = 3.6000V 0x51 = 3.6125V 0x52 = 3.6250V 0x53 = 3.6375V 0x54 = 3.6500V 0x55 = 3.6625V 0x56 = 3.6750V	0x6A = 3.9250V 0x6B = 3.9375V 0x6C = 3.9500V 0x6D = 3.9625V 0x6E = 3.9750V 0x70 = 4.0000V 0x71 = 4.0125V 0x72 = 4.0250V 0x73 = 4.0375V 0x74 = 4.0500V 0x75 = 4.0625V 0x76 = 4.0750V	
			0x16 = 2.8750V 0x17 = 2.8875V 0x18 = 2.9000V 0x19 = 2.9125V 0x1A = 2.9250V 0x1B = 2.9375V 0x1C = 2.9500V 0x1D = 2.9625V 0x1E = 2.9750V 0x1F = 2.9875V	0x36 = 3.2750V 0x37 = 3.2875V 0x38 = 3.3000V 0x39 = 3.3125V 0x3A = 3.3250V 0x3B = 3.3375V 0x3C = 3.3500V 0x3D = 3.3625V 0x3E = 3.3750V 0x3F = 3.3875V	0x56 = 3.6750V 0x57 = 3.6875V 0x58 = 3.7000V 0x59 = 3.7125V 0x5A = 3.7250V 0x5B = 3.7375V 0x5C = 3.7500V 0x5D = 3.7625V 0x5E = 3.7750V 0x5F = 3.7875V	0x76 = 4.0750V 0x77 = 4.0875V 0x78 = 4.1000V 0x79 = 4.1125V 0x7A = 4.1250V 0x7B = 4.1375V 0x7C = 4.1500V 0x7D = 4.1625V 0x7E = 4.1750V 0x7F = 4.1875V	

Note: 0x34-0x3F: RSVD.

BUCK\_SS\_FREQ

## **BUCK Soft-Start and Switching Frequency Configuration Register**

ADDRESS	MODE		TYPE: O	RESET VALUE: 0x04
0x40	R/W		TIPE: 0	RESET VALUE: 0x04
BIT	NAME	POR		DESCRIPTION
7:5	RSVD	000	Write 0.	
4	B_SS	0	BUCK Soft-Star 0: 14mV/µs 1: 25mV/µs	t Slew Rate
3	RSVD	0	Write 0.	
2:0	B_FREQ[2:0]	100	Multiphase Curro 000b: 3.6MHz 001b: 3.2MHz 010b: 2.8MHz 011b: 2.4MHz 100b: 2.0MHz 101b: 1.6MHz 110b: 1.2MHz 111b: 0.8MHz	rent Mode BUCK Switching Frequency


## UVLO\_FALL

## **VSYS UVLO Falling Threshold Program Register**

ADDRESS	MODE R/W		TYPE: O	RESET VALUE: 0x01	
0x41			TIPE. O	RESET VALUE. 0X01	
BIT	NAME	POR	DESCRIPTION		
7:2	RSVD	0000 00	Write 0000 00.		
1:0	UVLO_F[1:0]	01	VSYS UVLO Fall 00b: Not used 01b: 2.05V 10b: 2.25V 11b: 2.45V	ling Threshold	

Note: 0x42-0xFF: RSVD.

# **Typical Application Circuit**



# **Ordering Information**

PART	TEMP RANGE	PIN-PACKAGE
MAX77826EWJ+	-40°C to +85°C	49 Bumps (7 x 7) 0.4mm Pitch

<sup>+</sup>Denotes a lead(Pb)-free/RoHS-compliant package.

#### **Chip Information**

PROCESS: S18B

## **Package Information**

For the latest package outline information and land patterns (footprints), go to <a href="www.maximintegrated.com/packages">www.maximintegrated.com/packages</a>. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE	PACKAGE	OUTLINE	LAND
TYPE	CODE	NO.	PATTERN NO.
49 WLP	W493E3+1	21-0728	Refer to Application Note 1891

## **Revision History**

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	6/15	Initial release	_
1	7/15	Corrected typos and updated notes in <i>Electrical Characteristics</i> table.	4, 7

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at www.maximintegrated.com.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.